

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928786

Luminaire Tested: DFN2DIP-HX4F0-120D050US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928786
REPORT IS A COMBINATION OF REPORTS P900854 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D050US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12347.3 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 163.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	93	89	86	83	80	78	73	71	70	65	63	62
2	94	86	80	75	88	82	77	72	73	69	66	65	62	59	58	55	53
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46
4	79	68	61	55	74	65	58	52	58	53	48	52	48	44	47	43	40
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	42	39	36
6	67	55	47	42	63	53	45	40	48	42	37	43	38	34	39	35	32
7	63	50	42	37	59	48	41	36	44	38	33	39	35	31	36	32	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	34	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	25	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3006	3006	3006
5°	3011	2958	2977
10°	2981	2900	2880
15°	2940	2805	2731
20°	2886	2673	2547
25°	2831	2525	2370
30°	2756	2373	2145
35°	2684	2210	1947
40°	2609	2042	1720
45°	2523	1854	1515
50°	2434	1665	1314
55°	2341	1463	1121
60°	2234	1252	923
65°	2110	1037	831
70°	1960	837	752
75°	1771	738	685
80°	1499	620	594
85°	1048	415	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2523 cd/sqm

TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.8	3.1
10°-20°	1040.0	8.4
20°-30°	1460.1	11.8
30°-40°	1591.6	12.9
40°-50°	1462.8	11.8
50°-60°	1148.8	9.3
60°-70°	747.8	6.1
70°-80°	384.9	3.1
80°-90°	100.7	0.8
90°-100°	45.4	0.4
100°-110°	169.1	1.4
110°-120°	448.4	3.6
120°-130°	743.6	6.0
130°-140°	789.9	6.4
140°-150°	734.1	5.9
150°-160°	590.2	4.8
160°-170°	380.3	3.1
170°-180°	130.9	1.1
0°-30°	2878.9	23.3
0°-40°	4470.4	36.2
0°-60°	7082.1	57.4
0°-90°	8315.4	67.3
90°-120°	662.8	5.4
90°-150°	2930.4	23.7
90°-180°	4032.0	32.7
0°-180°	12347.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4042	4042	4042	4042	4042	
5°	4042	4024	3976	4009	3998	383
15°	3844	3804	3680	3610	3574	1083
25°	3490	3373	3131	2981	2926	1605
35°	3007	2820	2498	2268	2187	1882
45°	2458	2213	1829	1569	1481	1898
55°	1869	1584	1189	969	900	1670
65°	1262	966	636	512	501	1251
75°	673	417	293	267	264	712
85°	157	80	69	69	69	180
90°	1	12	20	25	27	12
95°	65	32	39	44	43	77
105°	302	332	61	72	76	323
115°	572	589	614	153	82	563
125°	809	822	841	848	851	721
135°	1001	1017	1026	1036	1034	773
145°	1161	1160	1177	1184	1179	726
155°	1279	1270	1282	1288	1280	589
165°	1347	1342	1344	1351	1344	381
175°	1378	1371	1373	1380	1370	131
180°	1375	1375	1375	1375	1375	

TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4042.1	4042.1	4042.1	4042.1	4042.1
2.5°	4060.3	4042.1	4001.7	4038.6	4031.2
5°	4042.1	4023.8	3976.1	4009.1	3998.2
7.5°	4009.1	3987.3	3936.1	3950.5	3932.2
10°	3965.2	3939.6	3866.6	3855.4	3833.7
12.5°	3910.5	3877.5	3778.5	3756.8	3716.5
15°	3844.5	3804.2	3680.0	3610.4	3574.0
17.5°	3767.7	3709.1	3555.4	3475.1	3416.5
20°	3680.0	3606.6	3423.8	3332.6	3251.8
22.5°	3584.9	3500.7	3288.4	3164.2	3109.5
25°	3489.8	3372.6	3131.1	2981.4	2926.3
27.5°	3376.5	3251.8	2984.9	2813.0	2728.7
30°	3255.8	3116.5	2823.8	2637.5	2538.6
32.5°	3138.6	2970.1	2670.5	2450.9	2359.3
35°	3007.0	2820.3	2498.5	2268.1	2187.3
37.5°	2878.9	2677.5	2337.5	2084.9	1993.7
40°	2743.5	2524.2	2169.1	1909.5	1814.4
42.5°	2604.5	2370.5	2001.1	1730.2	1639.0
45°	2458.2	2213.0	1829.1	1569.1	1481.3
47.5°	2319.2	2059.7	1664.6	1404.6	1324.2
50°	2165.6	1906.0	1503.5	1250.9	1174.4
52.5°	2015.4	1741.0	1349.8	1108.4	1039.0
55°	1869.1	1583.9	1188.8	969.4	900.0
57.5°	1719.2	1426.7	1046.3	841.4	782.8
60°	1565.6	1272.9	896.1	709.9	651.3
62.5°	1415.8	1123.2	768.1	592.7	563.5
65°	1262.1	965.6	636.5	512.3	501.1
67.5°	1115.8	819.2	512.3	449.8	439.0
70°	962.1	676.9	424.2	387.7	372.9
72.5°	815.8	544.9	354.7	325.6	318.3
75°	672.9	416.8	292.7	267.0	263.5
77.5°	530.6	296.1	230.6	215.8	208.4
80°	398.6	212.3	175.4	161.0	161.0
82.5°	277.9	142.8	120.7	113.3	113.3
85°	157.2	80.4	69.4	69.4	69.4
87.5°	58.6	29.1	29.1	25.6	25.6
90°	1.0	11.9	19.9	24.9	26.8
92.5°	24.9	20.9	23.9	25.9	26.8
95°	64.6	31.8	38.8	43.8	42.8
97.5°	116.4	34.9	50.7	53.8	54.7
100°	176.2	39.9	56.7	64.6	66.7
102.5°	241.8	239.9	58.8	69.6	72.7
105°	302.5	332.4	60.7	71.6	75.6
107.5°	373.2	398.0	62.8	73.6	77.7
110°	440.9	461.7	174.2	74.7	78.6

TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.6	522.4	505.5	76.6	79.6
115°	572.2	589.1	614.0	153.3	81.7
117.5°	630.9	650.8	667.8	525.3	264.7
120°	696.6	711.5	729.4	741.4	607.0
122.5°	752.2	768.2	788.2	794.1	795.2
125°	809.0	822.0	840.9	847.8	850.9
127.5°	860.7	874.7	889.7	899.6	900.6
130°	909.5	925.5	936.4	947.4	946.5
132.5°	959.3	972.3	983.1	992.2	991.2
135°	1001.1	1017.1	1025.9	1036.0	1034.0
137.5°	1044.8	1056.8	1066.8	1076.8	1073.8
140°	1087.6	1095.7	1106.5	1115.5	1110.6
142.5°	1123.6	1130.6	1143.4	1151.4	1146.4
145°	1161.4	1160.3	1177.2	1184.2	1179.2
147.5°	1194.1	1191.1	1208.1	1213.0	1209.1
150°	1226.0	1219.1	1235.0	1240.9	1235.9
152.5°	1252.8	1244.9	1259.8	1265.9	1258.8
155°	1278.7	1269.9	1281.8	1287.7	1279.8
157.5°	1299.6	1291.7	1300.7	1307.7	1299.6
160°	1317.6	1311.6	1317.6	1323.5	1316.6
162.5°	1333.4	1327.6	1332.4	1339.5	1330.5
165°	1347.4	1341.5	1344.4	1351.4	1344.4
167.5°	1358.4	1352.3	1355.4	1362.4	1353.4
170°	1367.3	1361.3	1363.3	1370.3	1361.3
172.5°	1373.3	1367.3	1369.4	1376.3	1367.3
175°	1378.2	1371.2	1373.3	1380.2	1370.3
177.5°	1380.2	1373.3	1374.3	1381.3	1372.3
180°	1375.2	1375.2	1375.2	1375.2	1375.2

TEST NUMBER: P928786

CATALOG NUMBER: DFN2DIP-HX4F0-120D050US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	13.45	13.26	14.27	15.27	8.43	9.42	9.23	10.24	11.24
	3H	14.15	15.04	14.96	15.86	16.90	9.63	10.52	10.44	11.35	12.38
	4H	14.76	15.60	15.59	16.44	17.48	10.09	10.93	10.92	11.76	12.81
	6H	15.19	15.97	16.04	16.81	17.87	10.42	11.19	11.26	12.04	13.09
	8H	15.33	16.06	16.18	16.92	17.98	10.52	11.25	11.37	12.11	13.17
	12H	15.39	16.09	16.25	16.95	18.03	10.57	11.27	11.42	12.12	13.20
4H	2H	12.49	13.33	13.33	14.17	15.21	9.04	9.88	9.88	10.72	11.76
	3H	14.34	15.04	15.19	15.90	16.96	10.41	11.11	11.26	11.98	13.04
	4H	15.04	15.67	15.90	16.54	17.62	10.97	11.60	11.83	12.47	13.55
	6H	15.56	16.11	16.44	17.00	18.09	11.40	11.94	12.27	12.83	13.92
	8H	15.74	16.25	16.62	17.14	18.24	11.53	12.04	12.41	12.92	14.03
	12H	15.85	16.30	16.74	17.21	18.32	11.60	12.06	12.50	12.97	14.07
8H	4H	15.02	15.53	15.90	16.41	17.52	11.26	11.77	12.14	12.65	13.76
	6H	15.59	16.01	16.50	16.94	18.04	11.79	12.21	12.69	13.13	14.24
	8H	15.81	16.18	16.73	17.10	18.22	11.98	12.35	12.90	13.27	14.39
	12H	15.96	16.29	16.87	17.20	18.37	12.11	12.44	13.02	13.35	14.52
12H	4H	14.98	15.44	15.88	16.34	17.45	11.27	11.73	12.17	12.64	13.74
	6H	15.57	15.94	16.48	16.86	17.98	11.84	12.21	12.75	13.13	14.25
	8H	15.80	16.13	16.71	17.04	18.21	12.06	12.39	12.97	13.30	14.47