

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913828

Luminaire Tested: DFN2DIP-PN2F0-050D040US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913828
REPORT IS A COMBINATION OF REPORTS P899487 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-050D040US927-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6725.6 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	64	60	58	55	52	50	47	45
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3338	3338	3338
5°	3338	3284	3309
10°	3306	3233	3259
15°	3252	3173	3184
20°	3181	3092	3108
25°	3110	2996	3020
30°	3022	2907	2910
35°	2939	2803	2794
40°	2838	2697	2683
45°	2736	2591	2569
50°	2624	2479	2438
55°	2507	2350	2316
60°	2375	2198	2177
65°	2229	2039	2012
70°	2044	1846	1833
75°	1791	1614	1662
80°	1482	1318	1348
85°	1006	833	845

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2736 cd/sqm

TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.1	2.2
10°-20°	408.1	6.1
20°-30°	599.8	8.9
30°-40°	696.6	10.4
40°-50°	695.8	10.3
50°-60°	606.7	9.0
60°-70°	448.5	6.7
70°-80°	253.7	3.8
80°-90°	69.8	1.0
90°-100°	62.0	0.9
100°-110°	197.0	2.9
110°-120°	337.2	5.0
120°-130°	443.5	6.6
130°-140°	497.8	7.4
140°-150°	488.1	7.3
150°-160°	409.5	6.1
160°-170°	271.5	4.0
170°-180°	94.9	1.4
0°-30°	1153.0	17.1
0°-40°	1849.6	27.5
0°-60°	3152.1	46.9
0°-90°	3924.1	58.3
90°-120°	596.2	8.9
90°-150°	2025.6	30.1
90°-180°	2801.0	41.6
0°-180°	6725.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1531	1528	146
15°	1467	1458	1439	1445	1438	413
25°	1328	1316	1291	1294	1291	611
35°	1146	1131	1107	1098	1091	715
45°	932	922	900	883	877	719
55°	706	697	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	11	30	28	29	6
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	

TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.2	1541.2	1541.2	1541.2	1541.2
2.5°	1550.1	1542.8	1526.5	1541.2	1538.4
5°	1541.2	1535.4	1519.0	1530.8	1528.0
7.5°	1530.8	1522.0	1505.7	1517.7	1514.7
10°	1514.7	1504.3	1486.5	1498.3	1493.9
12.5°	1492.3	1483.5	1465.8	1473.1	1470.1
15°	1467.1	1458.3	1439.0	1445.0	1437.6
17.5°	1436.0	1427.2	1407.9	1415.2	1407.9
20°	1401.9	1393.1	1372.4	1376.7	1370.9
22.5°	1367.9	1354.6	1335.2	1335.2	1332.2
25°	1327.9	1316.1	1290.9	1293.7	1290.9
27.5°	1283.3	1273.0	1253.8	1249.3	1242.0
30°	1239.0	1227.1	1204.9	1200.5	1194.5
32.5°	1191.5	1182.7	1159.0	1150.0	1144.1
35°	1145.6	1130.8	1107.1	1098.1	1090.8
37.5°	1093.7	1080.4	1056.6	1046.2	1038.9
40°	1040.5	1028.5	1004.7	991.5	985.6
42.5°	988.6	976.6	953.0	938.0	929.2
45°	932.2	921.9	899.5	883.4	877.3
47.5°	877.3	867.0	843.3	826.9	818.1
50°	819.5	812.1	791.4	770.6	763.2
52.5°	763.2	752.8	733.6	717.3	706.9
55°	705.5	696.6	678.7	661.0	653.6
57.5°	647.6	640.2	620.9	603.2	597.1
60°	589.8	584.0	563.2	546.8	542.5
62.5°	533.5	523.2	508.3	493.5	487.6
65°	475.8	466.8	452.0	438.7	431.3
67.5°	416.5	409.0	395.8	385.4	379.4
70°	361.6	355.7	342.3	331.9	326.1
72.5°	305.4	299.4	292.0	281.6	277.2
75°	248.9	246.1	238.5	229.7	232.7
77.5°	198.6	192.6	189.6	185.2	180.9
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.8	100.8	99.3	93.4	93.4
85°	60.7	59.3	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5

TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1

TEST NUMBER: P913828

CATALOG NUMBER: DFN2DIP-PN2F0-050D040US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.08	13.02	12.96	13.92	15.07	11.64	12.58	12.52	13.49	14.63
	3H	13.72	14.57	14.62	15.48	16.65	13.24	14.09	14.14	15.00	16.17
	4H	14.30	15.10	15.21	16.02	17.20	13.82	14.62	14.73	15.54	16.72
	6H	14.69	15.43	15.61	16.35	17.55	14.20	14.94	15.13	15.87	17.06
	8H	14.79	15.49	15.72	16.43	17.63	14.30	15.01	15.23	15.95	17.14
	12H	14.83	15.50	15.77	16.44	17.66	14.34	15.01	15.28	15.94	17.16
4H	2H	12.54	13.34	13.45	14.26	15.44	12.19	12.99	13.10	13.91	15.09
	3H	14.39	15.06	15.31	16.00	17.20	13.99	14.66	14.91	15.60	16.80
	4H	15.09	15.70	16.03	16.64	17.86	14.68	15.29	15.61	16.23	17.45
	6H	15.59	16.12	16.54	17.08	18.31	15.17	15.70	16.12	16.66	17.89
	8H	15.73	16.22	16.68	17.18	18.42	15.31	15.80	16.26	16.76	18.00
	12H	15.80	16.24	16.77	17.22	18.46	15.37	15.81	16.34	16.79	18.03
8H	4H	15.28	15.77	16.23	16.73	17.97	14.91	15.40	15.87	16.37	17.60
	6H	15.89	16.30	16.87	17.30	18.54	15.52	15.93	16.50	16.93	18.16
	8H	16.10	16.46	17.09	17.45	18.70	15.72	16.08	16.71	17.07	18.32
	12H	16.22	16.54	17.21	17.52	18.82	15.83	16.14	16.82	17.13	18.43
12H	4H	15.27	15.71	16.24	16.69	17.93	14.91	15.35	15.88	16.33	17.57
	6H	15.92	16.28	16.90	17.27	18.52	15.56	15.92	16.54	16.91	18.16
	8H	16.15	16.46	17.14	17.45	18.75	15.78	16.10	16.77	17.08	18.38