

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928854

Luminaire Tested: DFN2DIP-HX4F0-050D040US935-RLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928854
REPORT IS A COMBINATION OF REPORTS P900822 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D040US935-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7068.8 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 73.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928854
CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P928854

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52	52	52	52
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50	45	45	45	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43	38	38	38	38
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37	33	33	33	33
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29	29	29	29
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28	25	25	25	25
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22	22	22	22
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23	20	20	20	20
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20	18	18	18	18
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19	16	16	16	16
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1323	1323	1323
5°	1325	1302	1310
10°	1312	1277	1268
15°	1294	1235	1202
20°	1270	1177	1121
25°	1246	1111	1043
30°	1213	1045	944
35°	1181	973	857
40°	1149	899	757
45°	1111	816	667
50°	1072	733	578
55°	1031	644	494
60°	983	551	406
65°	929	457	366
70°	863	368	331
75°	780	325	301
80°	660	273	262
85°	461	183	197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1111 cd/sqm



TEST NUMBER: P928854

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.8	2.4
10°-20°	457.8	6.5
20°-30°	642.7	9.1
30°-40°	700.6	9.9
40°-50°	643.9	9.1
50°-60°	505.7	7.2
60°-70°	329.2	4.7
70°-80°	169.5	2.4
80°-90°	45.3	0.6
90°-100°	38.3	0.5
100°-110°	142.9	2.0
110°-120°	378.9	5.4
120°-130°	628.5	8.9
130°-140°	667.6	9.4
140°-150°	620.5	8.8
150°-160°	498.8	7.1
160°-170°	321.4	4.5
170°-180°	110.6	1.6
0°-30°	1267.2	17.9
0°-40°	1967.8	27.8
0°-60°	3117.4	44.1
0°-90°	3661.3	51.8
90°-120°	560.1	7.9
90°-150°	2476.6	35.0
90°-180°	3407.0	48.2
0°-180°	7068.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1779	1779	1779	1779	1779	
5°	1779	1771	1750	1765	1760	169
15°	1692	1675	1620	1589	1573	477
25°	1536	1484	1378	1312	1288	706
35°	1324	1242	1100	998	963	828
45°	1082	974	805	691	652	836
55°	823	697	523	427	396	735
65°	556	425	280	226	221	551
75°	296	184	129	118	116	313
85°	69	35	31	31	31	79
90°	1	10	17	21	23	7
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P928854

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1779.3	1779.3	1779.3	1779.3	1779.3
2.5°	1787.3	1779.3	1761.5	1777.7	1774.4
5°	1779.3	1771.2	1750.2	1764.7	1760.0
7.5°	1764.7	1755.1	1732.6	1739.0	1730.9
10°	1745.4	1734.1	1702.0	1697.1	1687.5
12.5°	1721.3	1706.8	1663.3	1653.7	1635.9
15°	1692.3	1674.6	1619.9	1589.3	1573.2
17.5°	1658.5	1632.7	1565.0	1529.7	1503.8
20°	1619.9	1587.6	1507.1	1467.0	1431.4
22.5°	1578.0	1540.9	1447.5	1392.8	1368.7
25°	1536.1	1484.5	1378.3	1312.3	1288.1
27.5°	1486.3	1431.4	1313.9	1238.2	1201.2
30°	1433.1	1371.8	1243.0	1161.0	1117.4
32.5°	1381.6	1307.4	1175.5	1078.8	1038.5
35°	1323.6	1241.5	1099.8	998.3	962.9
37.5°	1267.2	1178.6	1029.0	917.7	877.6
40°	1207.6	1111.1	954.8	840.5	798.7
42.5°	1146.5	1043.4	880.8	761.6	721.4
45°	1082.1	974.1	805.1	690.7	652.0
47.5°	1020.9	906.6	732.7	618.3	582.9
50°	953.3	839.0	661.9	550.6	516.9
52.5°	887.2	766.4	594.2	487.9	457.4
55°	822.8	697.2	523.2	426.7	396.1
57.5°	756.8	628.0	460.5	370.4	344.6
60°	689.1	560.3	394.4	312.5	286.6
62.5°	623.2	494.4	338.1	260.9	248.1
65°	555.5	425.1	280.2	225.5	220.6
67.5°	491.1	360.7	225.5	198.0	193.2
70°	423.5	297.9	186.8	170.7	164.2
72.5°	359.1	239.9	156.2	143.4	140.1
75°	296.3	183.5	128.8	117.5	116.0
77.5°	233.5	130.4	101.5	95.0	91.7
80°	175.5	93.4	77.2	70.9	70.9
82.5°	122.3	62.9	53.1	49.9	49.9
85°	69.2	35.4	30.6	30.6	30.6
87.5°	25.8	12.8	12.8	11.3	11.3
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4



TEST NUMBER: P928854

CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	831.0	838.5	837.8
135°	846.1	859.6	867.1	875.6	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.5	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.5	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.4	1162.4	1162.4	1162.4	1162.4



TEST NUMBER: P928854
 CATALOG NUMBER: DFN2DIP-HX4F0-050D040US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.29	9.13	9.24	10.09	11.34	4.26	5.11	5.21	6.07	7.31
	3H	9.97	10.72	10.93	11.69	12.96	5.45	6.21	6.41	7.18	8.45
	4H	10.58	11.29	11.55	12.26	13.54	5.90	6.62	6.88	7.59	8.87
	6H	11.00	11.66	11.98	12.64	13.93	6.23	6.88	7.21	7.86	9.16
	8H	11.13	11.75	12.12	12.75	14.04	6.32	6.94	7.31	7.94	9.23
	12H	11.19	11.78	12.19	12.77	14.09	6.36	6.96	7.36	7.95	9.26
4H	2H	8.31	9.02	9.29	9.99	11.27	4.86	5.57	5.84	6.55	7.83
	3H	10.14	10.73	11.13	11.74	13.03	6.21	6.81	7.20	7.81	9.10
	4H	10.83	11.37	11.83	12.37	13.69	6.76	7.30	7.76	8.30	9.62
	6H	11.35	11.82	12.36	12.84	14.15	7.18	7.65	8.19	8.67	9.98
	8H	11.53	11.96	12.54	12.97	14.30	7.31	7.75	8.32	8.76	10.09
	12H	11.62	12.01	12.65	13.04	14.38	7.38	7.77	8.41	8.80	10.14
8H	4H	10.80	11.24	11.81	12.25	13.58	7.04	7.48	8.05	8.49	9.82
	6H	11.37	11.73	12.40	12.78	14.11	7.56	7.92	8.60	8.98	10.31
	8H	11.59	11.90	12.63	12.94	14.29	7.76	8.07	8.80	9.11	10.46
	12H	11.73	12.01	12.77	13.04	14.43	7.88	8.16	8.92	9.19	10.58
12H	4H	10.76	11.15	11.78	12.18	13.51	7.05	7.44	8.08	8.47	9.80
	6H	11.35	11.66	12.39	12.70	14.05	7.61	7.93	8.66	8.97	10.32
	8H	11.57	11.85	12.61	12.88	14.27	7.83	8.11	8.87	9.14	10.53