

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916526

Luminaire Tested: DFN2DIP-PN2F0-030D060US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916526
REPORT IS A COMBINATION OF REPORTS P899504 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D060US930-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6408.3 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 80.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2189	2189	2189
5°	2189	2150	2165
10°	2164	2103	2092
15°	2131	2029	1980
20°	2088	1929	1844
25°	2044	1818	1712
30°	1986	1704	1547
35°	1929	1582	1401
40°	1871	1456	1235
45°	1804	1318	1085
50°	1734	1178	938
55°	1661	1029	798
60°	1576	875	654
65°	1479	718	584
70°	1360	572	525
75°	1211	495	471
80°	996	403	399
85°	651	251	283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2086 cd/sqm

TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.5
10°-20°	260.1	4.1
20°-30°	365.1	5.7
30°-40°	398.0	6.2
40°-50°	365.8	5.7
50°-60°	287.3	4.5
60°-70°	187.0	2.9
70°-80°	96.3	1.5
80°-90°	29.0	0.5
90°-100°	95.7	1.5
100°-110°	304.2	4.7
110°-120°	520.6	8.1
120°-130°	684.6	10.7
130°-140°	768.4	12.0
140°-150°	753.5	11.8
150°-160°	632.1	9.9
160°-170°	419.2	6.5
170°-180°	146.5	2.3
0°-30°	720.0	11.2
0°-40°	1118.0	17.4
0°-60°	1771.2	27.6
0°-90°	2083.4	32.5
90°-120°	920.5	14.4
90°-150°	3127.0	48.8
90°-180°	4325.0	67.5
0°-180°	6408.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	1	17	46	43	44	6
95°	68	81	84	84	81	76
105°	281	284	287	290	290	296
115°	522	530	528	526	522	517
125°	760	771	768	764	762	679
135°	983	997	1000	999	995	760
145°	1193	1202	1210	1211	1206	745
155°	1364	1368	1372	1379	1374	628
165°	1484	1483	1483	1492	1486	419
175°	1544	1541	1538	1547	1539	147
180°	1547	1547	1547	1547	1547	

TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	1.4	16.8	45.7	42.9	44.3
92.5°	28.9	39.2	40.6	42.0	42.0
95°	68.1	81.1	83.5	83.5	81.1
97.5°	113.3	125.5	130.6	130.6	130.6
100°	165.6	176.3	180.0	180.0	178.6
102.5°	220.6	228.5	233.7	235.1	233.7
105°	280.8	284.5	287.3	289.7	289.7
107.5°	340.5	346.1	346.1	347.0	340.5
110°	398.4	405.8	405.8	405.8	402.0

TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.8	468.7	467.3	463.6	460.8
115°	522.4	529.9	527.5	526.1	522.4
117.5°	583.5	593.8	587.2	583.5	579.8
120°	645.1	655.3	645.1	645.1	640.8
122.5°	701.0	714.0	707.5	703.8	701.0
125°	759.8	771.4	767.7	763.5	762.1
127.5°	817.2	831.6	826.5	820.9	817.2
130°	870.8	887.6	885.3	882.5	877.3
132.5°	931.0	944.0	944.9	938.4	934.7
135°	982.8	997.2	1000.0	998.6	994.8
137.5°	1040.6	1052.2	1054.6	1053.6	1048.1
140°	1091.4	1103.1	1109.6	1109.6	1104.5
142.5°	1143.6	1155.3	1159.0	1160.4	1155.3
145°	1193.1	1202.4	1209.9	1211.3	1206.2
147.5°	1237.4	1249.0	1254.7	1256.9	1251.8
150°	1283.1	1291.0	1296.2	1300.3	1296.2
152.5°	1323.6	1331.6	1338.1	1343.3	1338.1
155°	1364.2	1368.0	1372.1	1378.8	1374.5
157.5°	1399.2	1402.1	1404.4	1413.7	1407.2
160°	1430.5	1433.3	1434.7	1442.6	1437.0
162.5°	1459.4	1459.4	1460.8	1469.7	1463.1
165°	1484.1	1482.7	1482.7	1492.1	1485.6
167.5°	1506.5	1502.4	1502.4	1511.6	1505.1
170°	1523.3	1519.6	1518.2	1527.5	1519.6
172.5°	1535.0	1531.2	1529.8	1539.1	1531.2
175°	1544.3	1540.6	1537.7	1547.1	1539.1
177.5°	1549.4	1545.7	1542.9	1550.8	1542.9
180°	1547.1	1547.1	1547.1	1547.1	1547.1

TEST NUMBER: P916526

CATALOG NUMBER: DFN2DIP-PN2F0-030D060US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.85	8.56	8.95	9.65	11.15	3.82	4.52	4.92	5.62	7.12
	3H	9.50	10.13	10.61	11.23	12.75	4.98	5.61	6.09	6.71	8.23
	4H	10.09	10.69	11.21	11.79	13.31	5.41	6.01	6.53	7.11	8.64
	6H	10.49	11.04	11.61	12.14	13.68	5.71	6.26	6.84	7.37	8.91
	8H	10.60	11.12	11.73	12.24	13.77	5.79	6.32	6.92	7.44	8.97
	12H	10.65	11.15	11.78	12.26	13.81	5.82	6.32	6.96	7.44	8.99
4H	2H	7.85	8.45	8.98	9.55	11.08	4.39	4.99	5.51	6.09	7.61
	3H	9.64	10.14	10.78	11.27	12.81	5.71	6.20	6.84	7.33	8.87
	4H	10.32	10.77	11.45	11.89	13.45	6.23	6.69	7.37	7.81	9.37
	6H	10.80	11.20	11.95	12.34	13.89	6.63	7.02	7.77	8.16	9.71
	8H	10.97	11.33	12.11	12.46	14.03	6.75	7.11	7.89	8.24	9.81
	12H	11.04	11.37	12.20	12.52	14.09	6.80	7.13	7.95	8.27	9.84
8H	4H	10.27	10.64	11.41	11.77	13.33	6.49	6.86	7.63	7.99	9.56
	6H	10.81	11.11	11.97	12.29	13.85	6.98	7.29	8.15	8.46	10.02
	8H	11.01	11.27	12.18	12.43	14.01	7.16	7.43	8.33	8.58	10.16
	12H	11.13	11.36	12.30	12.51	14.13	7.26	7.49	8.43	8.65	10.26
12H	4H	10.22	10.55	11.37	11.69	13.26	6.49	6.82	7.65	7.97	9.54
	6H	10.78	11.05	11.95	12.20	13.78	7.03	7.29	8.19	8.45	10.03
	8H	10.98	11.21	12.15	12.37	13.98	7.22	7.45	8.39	8.60	10.22