

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916554

Luminaire Tested: DFN2DIP-PN2F0-050D030US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916554
REPORT IS A COMBINATION OF REPORTS P899478 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-050D030US930-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5629.6 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 69.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3649	3649	3649
5°	3649	3583	3609
10°	3607	3505	3486
15°	3552	3382	3300
20°	3480	3215	3073
25°	3407	3029	2854
30°	3310	2840	2578
35°	3216	2637	2335
40°	3119	2427	2059
45°	3007	2196	1808
50°	2891	1963	1564
55°	2769	1716	1329
60°	2628	1458	1089
65°	2464	1197	974
70°	2267	953	874
75°	2018	825	784
80°	1661	670	664
85°	1085	416	471

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3007 cd/sqm

TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.9	2.8
10°-20°	433.5	7.7
20°-30°	608.6	10.8
30°-40°	663.4	11.8
40°-50°	609.7	10.8
50°-60°	478.8	8.5
60°-70°	311.7	5.5
70°-80°	160.4	2.8
80°-90°	43.1	0.8
90°-100°	47.9	0.9
100°-110°	152.1	2.7
110°-120°	260.3	4.6
120°-130°	342.3	6.1
130°-140°	384.2	6.8
140°-150°	376.8	6.7
150°-160°	316.1	5.6
160°-170°	209.6	3.7
170°-180°	73.3	1.3
0°-30°	1200.0	21.3
0°-40°	1863.4	33.1
0°-60°	2951.9	52.4
0°-90°	3467.2	61.6
90°-120°	460.2	8.2
90°-150°	1563.5	27.8
90°-180°	2162.0	38.4
0°-180°	5629.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1685	1677	1657	1671	1667	160
15°	1602	1586	1534	1505	1490	452
25°	1455	1406	1305	1243	1220	669
35°	1253	1176	1042	945	912	784
45°	1025	922	762	654	617	791
55°	779	660	496	404	375	696
65°	526	402	265	214	209	521
75°	280	174	122	111	110	297
85°	66	34	29	29	29	75
90°	1	8	23	21	22	6
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	

TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1684.8	1684.8	1684.8	1684.8	1684.8
2.5°	1692.4	1684.8	1668.0	1683.3	1680.2
5°	1684.8	1677.2	1657.3	1671.0	1666.6
7.5°	1671.0	1662.0	1640.6	1646.7	1639.0
10°	1652.8	1642.1	1611.7	1607.0	1597.9
12.5°	1629.9	1616.2	1575.0	1565.9	1549.1
15°	1602.5	1585.7	1533.9	1505.0	1489.7
17.5°	1570.4	1546.1	1482.0	1448.5	1424.0
20°	1533.9	1503.3	1427.1	1389.1	1355.4
22.5°	1494.3	1459.1	1370.7	1318.9	1296.1
25°	1454.6	1405.7	1305.1	1242.7	1219.7
27.5°	1407.4	1355.4	1244.1	1172.5	1137.4
30°	1357.1	1299.0	1177.0	1099.3	1058.1
32.5°	1308.2	1238.0	1113.1	1021.6	983.4
35°	1253.4	1175.6	1041.5	945.3	911.7
37.5°	1200.0	1116.1	974.4	869.0	831.0
40°	1143.5	1052.1	904.1	795.9	756.3
42.5°	1085.7	988.1	834.1	721.1	683.1
45°	1024.7	922.4	762.4	654.0	617.4
47.5°	966.7	858.5	693.8	585.5	552.0
50°	902.7	794.4	626.7	521.4	489.5
52.5°	840.1	725.7	562.6	462.0	433.1
55°	779.1	660.1	495.5	404.1	375.1
57.5°	716.6	594.7	436.1	350.7	326.3
60°	652.6	530.6	373.5	295.9	271.4
62.5°	590.1	468.1	320.2	247.0	234.9
65°	526.0	402.5	265.3	213.5	208.9
67.5°	465.0	341.5	213.5	187.5	183.0
70°	401.0	282.1	176.8	161.6	155.5
72.5°	340.1	227.1	147.9	135.7	132.6
75°	280.5	173.7	122.0	111.3	109.8
77.5°	221.1	123.4	96.1	89.9	86.8
80°	166.2	88.5	73.1	67.1	67.1
82.5°	115.9	59.5	50.3	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.5	12.1	12.1	10.7	10.7
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1

TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6

TEST NUMBER: P916554

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.55	13.48	13.40	14.35	15.45	8.51	9.45	9.37	10.32	11.42
	3H	14.21	15.05	15.08	15.93	17.06	9.69	10.53	10.56	11.41	12.54
	4H	14.81	15.60	15.70	16.49	17.62	10.14	10.92	11.02	11.82	12.95
	6H	15.22	15.95	16.12	16.84	17.99	10.45	11.17	11.35	12.07	13.22
	8H	15.34	16.03	16.25	16.95	18.09	10.53	11.22	11.44	12.14	13.29
	12H	15.40	16.06	16.31	16.96	18.14	10.57	11.23	11.48	12.14	13.31
4H	2H	12.57	13.36	13.46	14.25	15.39	9.11	9.90	10.00	10.79	11.92
	3H	14.39	15.04	15.29	15.96	17.11	10.45	11.11	11.35	12.03	13.18
	4H	15.07	15.66	15.98	16.58	17.76	10.99	11.58	11.90	12.50	13.68
	6H	15.57	16.08	16.50	17.02	18.20	11.39	11.91	12.32	12.85	14.03
	8H	15.73	16.21	16.66	17.15	18.34	11.51	11.99	12.44	12.93	14.12
	12H	15.82	16.25	16.77	17.21	18.40	11.57	12.01	12.52	12.96	14.16
8H	4H	15.04	15.52	15.97	16.45	17.64	11.26	11.74	12.19	12.68	13.87
	6H	15.59	15.98	16.54	16.96	18.15	11.76	12.16	12.72	13.14	14.33
	8H	15.79	16.14	16.76	17.11	18.32	11.94	12.29	12.91	13.26	14.47
	12H	15.92	16.23	16.89	17.19	18.44	12.05	12.36	13.02	13.32	14.58
12H	4H	14.99	15.43	15.94	16.38	17.58	11.27	11.70	12.22	12.66	13.85
	6H	15.56	15.91	16.53	16.88	18.09	11.81	12.16	12.77	13.12	14.33
	8H	15.77	16.08	16.74	17.04	18.30	12.01	12.31	12.97	13.27	14.53