

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919217

Luminaire Tested: DFN2DIP-PN2F0-020D020US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919217
REPORT IS A COMBINATION OF REPORTS P900981 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D020US935-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3409.5 lumens
Efficiency: N/A
Efficacy: 105.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1451	1451	1451
5°	1451	1428	1438
10°	1437	1406	1417
15°	1414	1379	1384
20°	1383	1344	1351
25°	1352	1303	1313
30°	1314	1264	1265
35°	1278	1218	1215
40°	1234	1173	1166
45°	1189	1126	1117
50°	1141	1078	1060
55°	1090	1022	1007
60°	1032	956	946
65°	969	887	875
70°	889	802	797
75°	778	702	723
80°	645	573	586
85°	436	362	368

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1189 cd/sqm

TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	1.8
10°-20°	177.4	5.2
20°-30°	260.8	7.6
30°-40°	302.9	8.9
40°-50°	302.5	8.9
50°-60°	263.8	7.7
60°-70°	195.0	5.7
70°-80°	110.3	3.2
80°-90°	30.1	0.9
90°-100°	19.2	0.6
100°-110°	71.4	2.1
110°-120°	189.5	5.6
120°-130°	314.2	9.2
130°-140°	333.8	9.8
140°-150°	310.2	9.1
150°-160°	249.4	7.3
160°-170°	160.7	4.7
170°-180°	55.3	1.6
0°-30°	501.3	14.7
0°-40°	804.1	23.6
0°-60°	1370.4	40.2
0°-90°	1705.8	50.0
90°-120°	280.0	8.2
90°-150°	1238.3	36.3
90°-180°	1704.0	50.0
0°-180°	3409.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	0	5	8	10	11	3
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P919217

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.45	9.31	9.41	10.29	11.56	8.02	8.88	8.97	9.85	11.12
	3H	10.09	10.87	11.06	11.85	13.14	9.61	10.39	10.58	11.37	12.66
	4H	10.67	11.40	11.65	12.38	13.69	10.19	10.92	11.17	11.90	13.20
	6H	11.05	11.73	12.04	12.72	14.03	10.57	11.24	11.56	12.23	13.54
	8H	11.15	11.79	12.15	12.80	14.11	10.66	11.30	11.66	12.31	13.62
	12H	11.19	11.80	12.19	12.80	14.14	10.70	11.31	11.70	12.31	13.64
4H	2H	8.90	9.64	9.89	10.62	11.92	8.56	9.29	9.54	10.27	11.57
	3H	10.75	11.36	11.74	12.37	13.69	10.35	10.96	11.34	11.97	13.29
	4H	11.44	12.00	12.45	13.01	14.35	11.03	11.59	12.04	12.60	13.94
	6H	11.94	12.42	12.96	13.45	14.79	11.52	12.00	12.54	13.03	14.37
	8H	12.08	12.53	13.10	13.55	14.90	11.66	12.11	12.67	13.13	14.48
	12H	12.14	12.55	13.18	13.59	14.94	11.71	12.12	12.75	13.15	14.51
8H	4H	11.63	12.08	12.65	13.10	14.45	11.26	11.71	12.28	12.73	14.09
	6H	12.24	12.61	13.28	13.67	15.02	11.86	12.23	12.91	13.30	14.65
	8H	12.44	12.77	13.49	13.82	15.19	12.06	12.39	13.11	13.44	14.81
	12H	12.56	12.85	13.62	13.90	15.31	12.17	12.45	13.22	13.50	14.91
12H	4H	11.61	12.02	12.65	13.06	14.41	11.25	11.66	12.29	12.70	14.05
	6H	12.26	12.59	13.31	13.64	15.01	11.90	12.23	12.95	13.28	14.64
	8H	12.49	12.78	13.54	13.82	15.23	12.12	12.41	13.17	13.45	14.86

END OF REPORT