

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919233

Luminaire Tested: DFN2DIP-PN2F0-020D060US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919233
REPORT IS A COMBINATION OF REPORTS P901021 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US935-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6819.1 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1451	1451	1451
5°	1451	1428	1438
10°	1437	1406	1417
15°	1414	1379	1384
20°	1383	1344	1351
25°	1352	1303	1313
30°	1314	1264	1265
35°	1278	1218	1215
40°	1234	1173	1166
45°	1189	1126	1117
50°	1141	1078	1060
55°	1090	1022	1007
60°	1032	956	946
65°	969	887	875
70°	889	802	797
75°	778	702	723
80°	645	573	586
85°	436	362	368

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1601 cd/sqm

TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	0.9
10°-20°	177.4	2.6
20°-30°	260.8	3.8
30°-40°	302.9	4.4
40°-50°	302.5	4.4
50°-60°	263.8	3.9
60°-70°	195.0	2.9
70°-80°	110.3	1.6
80°-90°	32.2	0.5
90°-100°	57.5	0.8
100°-110°	214.3	3.1
110°-120°	568.4	8.3
120°-130°	942.7	13.8
130°-140°	1001.4	14.7
140°-150°	930.7	13.6
150°-160°	748.2	11.0
160°-170°	482.1	7.1
170°-180°	165.9	2.4
0°-30°	501.3	7.4
0°-40°	804.1	11.8
0°-60°	1370.4	20.1
0°-90°	1707.8	25.0
90°-120°	840.2	12.3
90°-150°	3714.9	54.5
90°-180°	5111.0	75.0
0°-180°	6819.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	670	670	670	670	670	
5°	670	668	660	666	664	64
15°	638	634	626	628	625	180
25°	577	572	561	562	561	266
35°	498	492	481	477	474	311
45°	405	401	391	384	381	313
55°	307	303	295	287	284	274
65°	207	203	197	191	188	205
75°	108	107	104	100	101	116
85°	26	26	25	23	23	29
90°	1	15	25	32	34	6
95°	82	40	49	56	54	97
105°	384	421	77	91	96	410
115°	725	747	778	194	104	714
125°	1026	1042	1066	1075	1079	915
135°	1269	1289	1301	1313	1311	980
145°	1472	1471	1492	1501	1495	921
155°	1621	1610	1625	1632	1622	747
165°	1708	1701	1704	1713	1704	483
175°	1747	1738	1741	1750	1737	166
180°	1743	1743	1743	1743	1743	

TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	670.0	670.0	670.0	670.0	670.0
2.5°	673.9	670.7	663.6	670.0	668.8
5°	670.0	667.5	660.4	665.6	664.3
7.5°	665.6	661.7	654.6	659.8	658.5
10°	658.5	654.0	646.3	651.3	649.5
12.5°	648.8	645.0	637.2	640.4	639.1
15°	637.8	634.0	625.6	628.2	625.0
17.5°	624.3	620.5	612.1	615.3	612.1
20°	609.5	605.6	596.6	598.6	596.0
22.5°	594.7	588.9	580.5	580.5	579.2
25°	577.3	572.1	561.2	562.4	561.2
27.5°	557.9	553.4	545.1	543.2	539.9
30°	538.6	533.5	523.8	521.9	519.3
32.5°	518.0	514.2	503.9	500.0	497.4
35°	498.1	491.6	481.3	477.4	474.2
37.5°	475.5	469.7	459.3	454.9	451.6
40°	452.3	447.1	436.8	431.1	428.4
42.5°	429.7	424.6	414.3	407.9	404.0
45°	405.3	400.8	391.1	384.0	381.4
47.5°	381.4	376.9	366.6	359.5	355.7
50°	356.3	353.1	344.1	335.0	331.8
52.5°	331.8	327.3	318.9	311.9	307.4
55°	306.7	302.8	295.1	287.4	284.1
57.5°	281.5	278.4	269.9	262.3	259.6
60°	256.4	253.9	244.9	237.7	235.8
62.5°	232.0	227.4	221.0	214.6	212.0
65°	206.8	202.9	196.6	190.7	187.5
67.5°	181.1	177.8	172.0	167.6	165.0
70°	157.2	154.6	148.8	144.3	141.8
72.5°	132.8	130.2	126.9	122.4	120.5
75°	108.2	107.0	103.7	99.9	101.2
77.5°	86.4	83.8	82.4	80.5	78.6
80°	64.5	63.8	62.5	60.5	59.2
82.5°	43.8	43.8	43.2	40.6	40.6
85°	26.3	25.7	25.1	23.2	22.6
87.5°	11.6	10.3	9.0	7.1	6.5
90°	1.2	15.2	25.1	31.6	34.0
92.5°	31.6	26.5	30.2	32.8	34.0
95°	82.0	40.3	49.2	55.6	54.2
97.5°	147.6	44.2	64.2	68.2	69.4
100°	223.3	50.5	71.9	82.0	84.5
102.5°	306.5	304.1	74.5	88.3	92.1
105°	383.5	421.4	77.0	90.7	95.9
107.5°	473.1	504.5	79.6	93.3	98.4
110°	559.0	585.3	220.8	94.7	99.6

TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	639.6	662.3	640.8	97.0	101.0
115°	725.4	746.8	778.4	194.3	103.5
117.5°	799.8	825.0	846.5	666.1	335.5
120°	883.1	902.0	924.8	939.9	769.6
122.5°	953.6	973.9	999.2	1006.7	1008.1
125°	1025.6	1042.1	1066.0	1074.9	1078.6
127.5°	1091.2	1108.9	1127.9	1140.5	1141.7
130°	1153.0	1173.3	1187.1	1201.0	1199.8
132.5°	1216.2	1232.6	1246.4	1257.7	1256.5
135°	1269.2	1289.4	1300.6	1313.4	1310.8
137.5°	1324.6	1339.7	1352.5	1365.0	1361.3
140°	1378.8	1389.0	1402.8	1414.2	1407.9
142.5°	1424.3	1433.2	1449.6	1459.6	1453.3
145°	1472.3	1470.9	1492.4	1501.2	1495.0
147.5°	1513.8	1510.0	1531.5	1537.7	1532.8
150°	1554.3	1545.4	1565.6	1573.1	1566.8
152.5°	1588.3	1578.2	1597.1	1604.7	1595.9
155°	1621.1	1609.8	1625.0	1632.5	1622.4
157.5°	1647.6	1637.5	1648.9	1657.8	1647.6
160°	1670.3	1662.7	1670.3	1677.8	1669.0
162.5°	1690.4	1682.9	1689.2	1698.1	1686.7
165°	1708.1	1700.6	1704.3	1713.2	1704.3
167.5°	1722.0	1714.4	1718.3	1727.2	1715.7
170°	1733.4	1725.8	1728.4	1737.1	1725.8
172.5°	1740.9	1733.4	1735.9	1744.8	1733.4
175°	1747.2	1738.4	1740.9	1749.7	1737.1
177.5°	1749.7	1740.9	1742.2	1751.1	1739.7
180°	1743.4	1743.4	1743.4	1743.4	1743.4

TEST NUMBER: P919233

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.51	6.18	6.65	7.32	8.90	5.07	5.75	6.22	6.88	8.47
	3H	7.13	7.74	8.29	8.88	10.48	6.65	7.26	7.81	8.40	10.00
	4H	7.70	8.27	8.86	9.42	11.02	7.22	7.79	8.38	8.93	10.54
	6H	8.07	8.60	9.24	9.75	11.37	7.59	8.11	8.76	9.26	10.88
	8H	8.16	8.67	9.34	9.83	11.44	7.68	8.18	8.85	9.34	10.95
	12H	8.20	8.68	9.37	9.83	11.46	7.71	8.18	8.88	9.34	10.97
4H	2H	5.94	6.51	7.11	7.65	9.26	5.59	6.16	6.76	7.30	8.91
	3H	7.76	8.24	8.93	9.41	11.03	7.36	7.84	8.54	9.01	10.63
	4H	8.45	8.89	9.63	10.05	11.69	8.04	8.48	9.21	9.63	11.27
	6H	8.94	9.31	10.12	10.49	12.12	8.52	8.89	9.70	10.07	11.70
	8H	9.07	9.42	10.25	10.59	12.24	8.65	9.00	9.83	10.17	11.82
	12H	9.13	9.45	10.32	10.63	12.28	8.69	9.01	9.89	10.19	11.84
8H	4H	8.62	8.97	9.80	10.14	11.79	8.25	8.60	9.43	9.78	11.42
	6H	9.22	9.51	10.42	10.72	12.37	8.85	9.14	10.05	10.35	11.99
	8H	9.43	9.68	10.63	10.87	12.53	9.04	9.30	10.25	10.49	12.15
	12H	9.53	9.76	10.74	10.94	12.64	9.14	9.36	10.35	10.55	12.24
12H	4H	8.59	8.91	9.79	10.10	11.75	8.23	8.55	9.43	9.74	11.39
	6H	9.24	9.50	10.45	10.69	12.35	8.88	9.13	10.08	10.32	11.99
	8H	9.46	9.68	10.67	10.87	12.56	9.09	9.31	10.30	10.50	12.19

END OF REPORT