

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929010

Luminaire Tested: DFN2DIP-HX4F0-090D070US935-RLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929010
REPORT IS A COMBINATION OF REPORTS P900884 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D070US935-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12553.4 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929010
CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929010

CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	58	58	58	52
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	52	51	50	45
2	90	83	77	72	84	77	72	68	66	63	59	56	53	51	47	45	43	47	45	43	39
3	83	74	67	61	76	69	62	57	59	54	50	50	47	44	42	39	37	42	39	37	33
4	76	66	58	52	70	61	54	49	53	48	43	45	41	38	38	35	33	38	35	33	29
5	70	59	51	45	65	55	48	43	47	42	38	41	36	33	34	31	29	34	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	31	28	26	31	28	26	23
7	60	48	40	35	55	45	38	33	39	34	30	34	29	26	29	25	23	29	25	23	20
8	56	44	36	31	52	41	34	29	36	30	26	31	27	24	26	23	21	26	23	21	18
9	52	40	33	28	48	38	31	26	33	28	24	29	24	21	25	21	19	25	21	19	17
10	49	37	30	25	45	35	28	24	30	25	22	27	22	19	23	20	17	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2381	2381	2381
5°	2385	2344	2359
10°	2362	2298	2282
15°	2330	2222	2164
20°	2287	2118	2018
25°	2243	2001	1878
30°	2184	1881	1699
35°	2126	1751	1543
40°	2068	1618	1363
45°	1999	1469	1200
50°	1929	1319	1041
55°	1855	1159	889
60°	1770	992	732
65°	1672	822	659
70°	1553	663	596
75°	1404	585	543
80°	1188	491	471
85°	830	329	355

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1999 cd/sqm



TEST NUMBER: P929010

CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.2	2.4
10°-20°	824.0	6.6
20°-30°	1156.9	9.2
30°-40°	1261.0	10.0
40°-50°	1159.0	9.2
50°-60°	910.3	7.3
60°-70°	592.5	4.7
70°-80°	305.0	2.4
80°-90°	81.4	0.6
90°-100°	67.1	0.5
100°-110°	250.0	2.0
110°-120°	663.1	5.3
120°-130°	1099.8	8.8
130°-140°	1168.3	9.3
140°-150°	1085.8	8.6
150°-160°	872.9	7.0
160°-170°	562.5	4.5
170°-180°	193.6	1.5
0°-30°	2281.0	18.2
0°-40°	3542.1	28.2
0°-60°	5611.3	44.7
0°-90°	6590.2	52.5
90°-120°	980.3	7.8
90°-150°	4334.1	34.5
90°-180°	5963.0	47.5
0°-180°	12553.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3203	3203	3203	3203	3203	
5°	3203	3188	3150	3176	3168	304
15°	3046	3014	2916	2861	2832	858
25°	2765	2672	2481	2362	2319	1272
35°	2383	2235	1980	1797	1733	1491
45°	1948	1753	1449	1243	1174	1504
55°	1481	1255	942	768	713	1323
65°	1000	765	504	406	397	991
75°	533	330	232	212	209	564
85°	124	64	55	55	55	143
90°	1	18	29	37	40	12
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	



TEST NUMBER: P929010

CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3202.7	3202.7	3202.7	3202.7	3202.7
2.5°	3217.1	3202.7	3170.6	3199.9	3194.1
5°	3202.7	3188.2	3150.4	3176.5	3167.9
7.5°	3176.5	3159.3	3118.7	3130.1	3115.6
10°	3141.8	3121.5	3063.7	3054.7	3037.5
12.5°	3098.4	3072.3	2993.9	2976.6	2944.6
15°	3046.1	3014.2	2915.8	2860.7	2831.8
17.5°	2985.3	2938.9	2817.0	2753.4	2707.0
20°	2915.8	2857.7	2712.8	2640.5	2576.5
22.5°	2840.4	2773.7	2605.5	2507.1	2463.8
25°	2765.1	2672.2	2481.0	2362.2	2318.6
27.5°	2675.3	2576.5	2365.0	2228.8	2162.1
30°	2579.6	2469.3	2237.4	2089.8	2011.4
32.5°	2486.7	2353.3	2115.9	1941.9	1869.3
35°	2382.6	2234.6	1979.7	1797.1	1733.1
37.5°	2281.0	2121.5	1852.1	1651.9	1579.7
40°	2173.8	2000.0	1718.6	1512.9	1437.6
42.5°	2063.6	1878.3	1585.4	1370.9	1298.6
45°	1947.8	1753.4	1449.2	1243.2	1173.7
47.5°	1837.6	1631.9	1318.9	1112.8	1049.2
50°	1715.9	1510.1	1191.3	991.1	930.5
52.5°	1596.9	1379.5	1069.5	878.2	823.2
55°	1480.9	1254.9	941.8	768.2	713.1
57.5°	1362.3	1130.4	829.1	666.7	620.3
60°	1240.4	1008.6	710.1	562.4	516.0
62.5°	1121.8	889.9	608.6	469.6	446.5
65°	1000.0	765.1	504.3	405.9	397.0
67.5°	884.1	649.1	405.9	356.4	347.8
70°	762.3	536.3	336.1	307.2	295.5
72.5°	646.4	431.7	281.0	258.0	252.2
75°	533.2	330.3	231.9	211.5	208.8
77.5°	420.3	234.6	182.6	171.0	165.1
80°	315.8	168.2	139.0	127.6	127.6
82.5°	220.2	113.1	95.7	89.8	89.8
85°	124.5	63.6	55.0	55.0	55.0
87.5°	46.4	23.1	23.1	20.3	20.3
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P929010

CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.2	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.9
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.4
127.5°	1273.1	1293.7	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.3	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.2
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0



TEST NUMBER: P929010
 CATALOG NUMBER: DFN2DIP-HX4F0-090D070US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.39	11.24	11.34	12.20	13.44	6.37	7.22	7.31	8.17	9.41
	3H	12.07	12.83	13.03	13.80	15.06	7.56	8.32	8.51	9.28	10.54
	4H	12.68	13.40	13.65	14.37	15.64	8.01	8.73	8.98	9.70	10.97
	6H	13.11	13.77	14.09	14.74	16.02	8.33	9.00	9.31	9.97	11.25
	8H	13.23	13.86	14.22	14.85	16.13	8.43	9.06	9.41	10.05	11.33
	12H	13.30	13.90	14.29	14.88	16.18	8.47	9.07	9.46	10.05	11.36
4H	2H	10.41	11.13	11.39	12.10	13.37	6.97	7.68	7.94	8.65	9.92
	3H	12.25	12.84	13.23	13.84	15.13	8.32	8.92	9.30	9.91	11.20
	4H	12.94	13.49	13.93	14.48	15.78	8.87	9.41	9.86	10.41	11.71
	6H	13.46	13.93	14.46	14.94	16.25	9.29	9.76	10.29	10.77	12.08
	8H	13.63	14.07	14.64	15.08	16.40	9.42	9.86	10.43	10.87	12.19
	12H	13.73	14.13	14.75	15.15	16.47	9.49	9.88	10.51	10.91	12.23
8H	4H	12.91	13.35	13.91	14.36	15.68	9.15	9.59	10.16	10.60	11.92
	6H	13.48	13.84	14.51	14.89	16.21	9.67	10.03	10.70	11.08	12.40
	8H	13.70	14.01	14.73	15.05	16.39	9.87	10.18	10.90	11.22	12.56
	12H	13.84	14.12	14.88	15.15	16.53	9.99	10.27	11.03	11.30	12.68
12H	4H	12.86	13.26	13.89	14.28	15.61	9.16	9.55	10.18	10.58	11.90
	6H	13.45	13.77	14.49	14.81	16.14	9.72	10.04	10.76	11.08	12.41
	8H	13.68	13.96	14.72	14.99	16.37	9.94	10.22	10.98	11.25	12.63