

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919257

Luminaire Tested: DFN2DIP-PN2F0-040D020US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919257
REPORT IS A COMBINATION OF REPORTS P900985 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D020US935-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5114.3 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 55.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2902	2902	2902
5°	2902	2856	2877
10°	2874	2811	2834
15°	2827	2759	2769
20°	2765	2688	2702
25°	2704	2605	2626
30°	2628	2528	2530
35°	2555	2437	2429
40°	2467	2345	2333
45°	2379	2253	2234
50°	2282	2156	2120
55°	2180	2043	2014
60°	2065	1911	1893
65°	1938	1773	1750
70°	1777	1605	1594
75°	1557	1403	1445
80°	1288	1146	1173
85°	875	724	735

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2379 cd/sqm

TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.5
10°-20°	354.9	6.9
20°-30°	521.5	10.2
30°-40°	605.7	11.8
40°-50°	605.0	11.8
50°-60°	527.5	10.3
60°-70°	389.9	7.6
70°-80°	220.6	4.3
80°-90°	59.3	1.2
90°-100°	19.2	0.4
100°-110°	71.4	1.4
110°-120°	189.5	3.7
120°-130°	314.2	6.1
130°-140°	333.8	6.5
140°-150°	310.2	6.1
150°-160°	249.4	4.9
160°-170°	160.7	3.1
170°-180°	55.3	1.1
0°-30°	1002.5	19.6
0°-40°	1608.3	31.4
0°-60°	2740.7	53.6
0°-90°	3410.6	66.7
90°-120°	280.0	5.5
90°-150°	1238.3	24.2
90°-180°	1704.0	33.3
0°-180°	5114.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	0	5	8	10	11	5
95°	27	13	16	18	18	32
105°	128	140	26	30	32	137
115°	242	249	260	65	34	238
125°	342	347	355	358	360	305
135°	423	430	434	438	437	327
145°	491	490	498	500	498	307
155°	540	537	542	544	541	249
165°	569	567	568	571	568	161
175°	582	580	580	583	579	55
180°	581	581	581	581	581	

TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.4	5.1	8.4	10.5	11.4
92.5°	10.5	8.9	10.1	10.9	11.4
95°	27.3	13.4	16.4	18.5	18.1
97.5°	49.2	14.7	21.4	22.7	23.2
100°	74.5	16.8	23.9	27.3	28.2
102.5°	102.2	101.3	24.8	29.4	30.7
105°	127.9	140.4	25.7	30.2	31.9
107.5°	157.7	168.2	26.5	31.1	32.8
110°	186.3	195.1	73.6	31.6	33.2



TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.2	220.8	213.6	32.4	33.7
115°	241.8	248.9	259.5	64.7	34.5
117.5°	266.6	275.0	282.1	222.1	111.8
120°	294.4	300.7	308.2	313.3	256.5
122.5°	317.9	324.6	333.0	335.5	336.0
125°	341.9	347.3	355.3	358.3	359.6
127.5°	363.8	369.6	376.0	380.1	380.6
130°	384.3	391.1	395.7	400.4	399.9
132.5°	405.4	410.9	415.4	419.2	418.9
135°	423.1	429.8	433.5	437.8	437.0
137.5°	441.5	446.6	450.8	455.0	453.7
140°	459.6	463.0	467.6	471.4	469.3
142.5°	474.8	477.8	483.2	486.5	484.4
145°	490.8	490.3	497.5	500.4	498.3
147.5°	504.6	503.3	510.5	512.6	510.9
150°	518.1	515.1	521.9	524.3	522.3
152.5°	529.4	526.1	532.4	534.9	531.9
155°	540.4	536.6	541.7	544.2	540.8
157.5°	549.2	545.9	549.7	552.6	549.2
160°	556.8	554.2	556.8	559.3	556.4
162.5°	563.4	560.9	563.1	566.0	562.2
165°	569.4	566.9	568.1	571.1	568.1
167.5°	574.0	571.4	572.7	575.7	571.9
170°	577.8	575.2	576.1	579.0	575.2
172.5°	580.3	577.8	578.7	581.6	577.8
175°	582.4	579.5	580.3	583.2	579.0
177.5°	583.2	580.3	580.7	583.7	579.9
180°	581.2	581.2	581.2	581.2	581.2

TEST NUMBER: P919257

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US935-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.27	13.30	13.07	14.13	15.14	11.83	12.87	12.63	13.69	14.70
	3H	13.92	14.85	14.74	15.68	16.72	13.44	14.37	14.26	15.20	16.24
	4H	14.51	15.38	15.33	16.22	17.27	14.02	14.90	14.85	15.74	16.79
	6H	14.90	15.71	15.74	16.55	17.62	14.41	15.22	15.25	16.07	17.13
	8H	15.00	15.77	15.85	16.64	17.70	14.51	15.28	15.36	16.15	17.21
	12H	15.05	15.78	15.90	16.64	17.73	14.55	15.29	15.41	16.15	17.24
4H	2H	12.74	13.62	13.58	14.46	15.51	12.39	13.27	13.23	14.11	15.16
	3H	14.60	15.33	15.45	16.20	17.27	14.20	14.93	15.05	15.80	16.87
	4H	15.31	15.97	16.16	16.84	17.94	14.89	15.56	15.75	16.43	17.52
	6H	15.81	16.39	16.68	17.28	18.38	15.39	15.97	16.26	16.86	17.96
	8H	15.95	16.49	16.83	17.38	18.49	15.53	16.07	16.41	16.96	18.07
	12H	16.03	16.51	16.92	17.42	18.54	15.59	16.08	16.49	16.99	18.10
8H	4H	15.50	16.04	16.38	16.93	18.04	15.14	15.67	16.01	16.56	17.67
	6H	16.12	16.57	17.02	17.50	18.61	15.74	16.19	16.65	17.12	18.23
	8H	16.33	16.72	17.24	17.65	18.77	15.95	16.34	16.86	17.27	18.39
	12H	16.45	16.80	17.37	17.72	18.90	16.06	16.41	16.97	17.32	18.50
12H	4H	15.50	15.98	16.39	16.89	18.01	15.13	15.62	16.03	16.53	17.65
	6H	16.14	16.54	17.06	17.47	18.59	15.78	16.18	16.70	17.10	18.23
	8H	16.38	16.73	17.30	17.64	18.82	16.01	16.36	16.93	17.27	18.45