

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919262

Luminaire Tested: DFN2DIP-PN2F0-040D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919262
REPORT IS A COMBINATION OF REPORTS P899476 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D030US935-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5213.3 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3083	3083	3083
5°	3083	3027	3049
10°	3048	2961	2945
15°	3000	2857	2788
20°	2940	2716	2596
25°	2878	2559	2411
30°	2797	2399	2178
35°	2717	2228	1973
40°	2635	2051	1739
45°	2540	1855	1528
50°	2442	1658	1321
55°	2339	1449	1123
60°	2220	1232	920
65°	2082	1011	823
70°	1915	806	738
75°	1704	698	663
80°	1402	566	561
85°	918	353	399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2540 cd/sqm

TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	2.6
10°-20°	366.2	7.0
20°-30°	514.2	9.9
30°-40°	560.5	10.8
40°-50°	515.1	9.9
50°-60°	404.5	7.8
60°-70°	263.3	5.1
70°-80°	135.6	2.6
80°-90°	36.9	0.7
90°-100°	50.6	1.0
100°-110°	160.6	3.1
110°-120°	274.9	5.3
120°-130°	361.5	6.9
130°-140°	405.7	7.8
140°-150°	397.9	7.6
150°-160°	333.8	6.4
160°-170°	221.3	4.2
170°-180°	77.4	1.5
0°-30°	1013.8	19.4
0°-40°	1574.2	30.2
0°-60°	2493.9	47.8
0°-90°	2929.7	56.2
90°-120°	486.0	9.3
90°-150°	1651.1	31.7
90°-180°	2284.0	43.8
0°-180°	5213.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	1	9	24	23	23	5
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3



TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P919262

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.50	12.38	12.41	13.31	14.49	7.47	8.35	8.38	9.28	10.46
	3H	13.16	13.95	14.08	14.89	16.09	8.64	9.43	9.57	10.37	11.57
	4H	13.76	14.51	14.70	15.44	16.66	9.09	9.83	10.02	10.77	11.99
	6H	14.17	14.85	15.11	15.80	17.03	9.39	10.08	10.34	11.03	12.25
	8H	14.29	14.94	15.24	15.90	17.13	9.48	10.13	10.43	11.09	12.32
	12H	14.34	14.96	15.30	15.92	17.17	9.52	10.14	10.48	11.09	12.34
4H	2H	11.52	12.27	12.46	13.21	14.42	8.06	8.81	9.00	9.74	10.96
	3H	13.33	13.95	14.28	14.92	16.15	9.40	10.01	10.35	10.98	12.21
	4H	14.01	14.58	14.97	15.54	16.79	9.93	10.50	10.89	11.46	12.71
	6H	14.51	14.99	15.48	15.98	17.24	10.33	10.82	11.31	11.81	13.06
	8H	14.67	15.13	15.65	16.11	17.38	10.45	10.91	11.43	11.89	13.16
	12H	14.76	15.17	15.75	16.17	17.44	10.51	10.92	11.51	11.92	13.19
8H	4H	13.98	14.43	14.95	15.41	16.68	10.20	10.66	11.18	11.64	12.90
	6H	14.52	14.90	15.52	15.92	17.19	10.70	11.07	11.70	12.10	13.36
	8H	14.73	15.06	15.74	16.07	17.35	10.88	11.21	11.89	12.22	13.50
	12H	14.85	15.14	15.86	16.15	17.48	10.99	11.28	12.00	12.28	13.61
12H	4H	13.93	14.34	14.93	15.34	16.61	10.21	10.62	11.20	11.61	12.89
	6H	14.50	14.83	15.51	15.84	17.12	10.74	11.07	11.75	12.08	13.37
	8H	14.71	15.00	15.72	16.00	17.33	10.94	11.23	11.95	12.24	13.57

END OF REPORT