

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921944

Luminaire Tested: DFN2DIP-PN2F0-020D020US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921944
REPORT IS A COMBINATION OF REPORTS P899461 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D020US940-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3343.9 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		71	71	71		59	59	59
1	98	94	90	87		91	87	84	81		74	72	70		63	61	59		52	51	50
2	90	82	76	71		83	76	71	66		65	61	58		55	52	50		46	44	42
3	82	72	65	59		75	67	61	55		58	53	49		49	45	42		41	38	36
4	75	64	56	50		69	60	52	47		51	46	41		43	39	36		36	33	31
5	69	57	49	43		63	53	46	40		46	40	36		39	35	31		33	29	27
6	63	51	43	37		58	48	40	35		41	36	31		35	31	27		30	26	24
7	59	46	38	33		54	43	36	31		37	32	28		32	28	24		27	24	21
8	54	42	34	29		50	39	32	27		34	29	24		29	25	22		25	21	19
9	51	38	31	26		47	36	29	24		31	26	22		27	23	19		23	20	17
10	47	35	28	23		44	33	26	22		29	23	20		25	21	18		21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1503	1479	1490
10°	1488	1456	1467
15°	1464	1428	1434
20°	1432	1392	1399
25°	1400	1349	1360
30°	1361	1309	1310
35°	1324	1262	1258
40°	1277	1214	1208
45°	1232	1166	1157
50°	1182	1116	1098
55°	1129	1058	1043
60°	1069	990	980
65°	1004	918	906
70°	920	831	826
75°	806	727	749
80°	668	593	606
85°	452	374	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1232 cd/sqm

TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	2.0
10°-20°	183.8	5.5
20°-30°	270.1	8.1
30°-40°	313.7	9.4
40°-50°	313.3	9.4
50°-60°	273.2	8.2
60°-70°	201.9	6.0
70°-80°	114.2	3.4
80°-90°	31.8	1.0
90°-100°	34.9	1.0
100°-110°	110.9	3.3
110°-120°	189.8	5.7
120°-130°	249.6	7.5
130°-140°	280.2	8.4
140°-150°	274.7	8.2
150°-160°	230.4	6.9
160°-170°	152.8	4.6
170°-180°	53.4	1.6
0°-30°	519.1	15.5
0°-40°	832.8	24.9
0°-60°	1419.3	42.4
0°-90°	1767.2	52.8
90°-120°	335.6	10.0
90°-150°	1140.0	34.1
90°-180°	1577.0	47.2
0°-180°	3343.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	0	6	17	16	16	3
95°	25	30	30	30	30	28
105°	102	104	105	106	106	108
115°	190	193	192	192	190	188
125°	277	281	280	278	278	248
135°	358	364	364	364	363	277
145°	435	438	441	442	440	272
155°	497	499	500	503	501	229
165°	541	541	541	544	542	153
175°	563	562	561	564	561	53
180°	564	564	564	564	564	

TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	0.5	6.2	16.7	15.6	16.1
92.5°	10.5	14.3	14.8	15.3	15.3
95°	24.8	29.6	30.4	30.4	29.6
97.5°	41.3	45.7	47.6	47.6	47.6
100°	60.4	64.3	65.6	65.6	65.1
102.5°	80.4	83.3	85.2	85.7	85.2
105°	102.4	103.7	104.8	105.6	105.6
107.5°	124.1	126.2	126.2	126.5	124.1
110°	145.3	147.9	147.9	147.9	146.6



TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.0	170.9	170.4	169.0	168.0
115°	190.5	193.1	192.3	191.8	190.5
117.5°	212.8	216.5	214.1	212.8	211.3
120°	235.1	238.9	235.1	235.1	233.6
122.5°	255.6	260.3	258.0	256.6	255.6
125°	277.0	281.2	279.9	278.4	277.9
127.5°	297.9	303.2	301.3	299.3	297.9
130°	317.4	323.6	322.7	321.7	319.9
132.5°	339.4	344.2	344.5	342.1	340.7
135°	358.3	363.6	364.5	364.1	362.7
137.5°	379.3	383.6	384.5	384.1	382.1
140°	397.9	402.2	404.6	404.6	402.7
142.5°	417.0	421.2	422.6	423.0	421.2
145°	435.0	438.4	441.1	441.6	439.7
147.5°	451.1	455.4	457.4	458.2	456.4
150°	467.8	470.6	472.5	474.0	472.5
152.5°	482.6	485.4	487.9	489.7	487.9
155°	497.4	498.7	500.2	502.7	501.1
157.5°	510.1	511.1	512.0	515.4	513.0
160°	521.6	522.5	523.1	525.9	523.9
162.5°	532.1	532.1	532.5	535.8	533.4
165°	541.1	540.6	540.6	543.9	541.6
167.5°	549.2	547.7	547.7	551.1	548.8
170°	555.4	554.0	553.5	556.9	554.0
172.5°	559.6	558.2	557.8	561.2	558.2
175°	563.0	561.7	560.6	564.0	561.2
177.5°	564.9	563.6	562.5	565.3	562.5
180°	564.0	564.0	564.0	564.0	564.0

TEST NUMBER: P921944

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.83	9.72	9.76	10.67	11.90	8.39	9.28	9.32	10.23	11.46
	3H	10.47	11.27	11.41	12.23	13.48	9.99	10.79	10.94	11.75	13.00
	4H	11.05	11.80	12.00	12.76	14.03	10.57	11.32	11.52	12.28	13.54
	6H	11.43	12.13	12.40	13.10	14.37	10.95	11.64	11.92	12.61	13.88
	8H	11.53	12.19	12.51	13.18	14.45	11.04	11.70	12.02	12.69	13.96
	12H	11.57	12.20	12.55	13.18	14.48	11.08	11.71	12.06	12.69	13.99
4H	2H	9.28	10.04	10.25	11.00	12.26	8.93	9.69	9.90	10.65	11.91
	3H	11.13	11.76	12.10	12.75	14.03	10.73	11.36	11.70	12.35	13.63
	4H	11.83	12.40	12.81	13.39	14.69	11.41	11.99	12.40	12.98	14.28
	6H	12.33	12.82	13.32	13.83	15.13	11.90	12.40	12.90	13.41	14.71
	8H	12.47	12.93	13.46	13.93	15.25	12.04	12.50	13.04	13.51	14.82
	12H	12.53	12.95	13.55	13.97	15.29	12.10	12.51	13.11	13.53	14.85
8H	4H	12.02	12.48	13.01	13.48	14.79	11.65	12.11	12.64	13.11	14.43
	6H	12.62	13.01	13.64	14.05	15.36	12.25	12.63	13.27	13.68	14.99
	8H	12.83	13.17	13.86	14.20	15.53	12.45	12.79	13.48	13.82	15.15
	12H	12.95	13.25	13.98	14.27	15.65	12.55	12.85	13.59	13.88	15.25
12H	4H	12.00	12.42	13.01	13.44	14.76	11.64	12.06	12.65	13.08	14.39
	6H	12.65	12.99	13.68	14.02	15.35	12.29	12.62	13.31	13.66	14.99
	8H	12.88	13.17	13.91	14.20	15.57	12.51	12.80	13.54	13.83	15.20