

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921947

Luminaire Tested: DFN2DIP-PN2F0-020D020US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921947
REPORT IS A COMBINATION OF REPORTS P900982 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D020US940-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3281.5 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 32.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1596	1596	1596
5°	1596	1568	1579
10°	1578	1534	1525
15°	1554	1479	1444
20°	1522	1407	1344
25°	1490	1325	1248
30°	1448	1242	1128
35°	1407	1154	1022
40°	1364	1062	901
45°	1316	961	791
50°	1265	859	684
55°	1211	751	581
60°	1150	638	477
65°	1079	524	426
70°	992	417	382
75°	883	361	344
80°	727	294	290
85°	474	183	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1316 cd/sqm

TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	2.1
10°-20°	189.6	5.8
20°-30°	266.3	8.1
30°-40°	290.2	8.8
40°-50°	266.8	8.1
50°-60°	209.5	6.4
60°-70°	136.4	4.2
70°-80°	70.2	2.1
80°-90°	19.0	0.6
90°-100°	19.8	0.6
100°-110°	74.0	2.3
110°-120°	196.2	6.0
120°-130°	325.4	9.9
130°-140°	345.7	10.5
140°-150°	321.3	9.8
150°-160°	258.3	7.9
160°-170°	166.4	5.1
170°-180°	57.3	1.7
0°-30°	525.0	16.0
0°-40°	815.2	24.8
0°-60°	1291.4	39.4
0°-90°	1517.0	46.2
90°-120°	290.0	8.8
90°-150°	1282.5	39.1
90°-180°	1765.0	53.8
0°-180°	3281.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	737	737	737	737	737	
5°	737	734	725	731	729	70
15°	701	694	671	658	652	198
25°	636	615	571	544	534	293
35°	548	514	456	414	399	343
45°	448	404	334	286	270	346
55°	341	289	217	177	164	305
65°	230	176	116	94	91	228
75°	123	76	53	49	48	130
85°	29	15	13	13	13	33
90°	0	5	9	11	12	3
95°	28	14	17	19	19	33
105°	132	145	27	31	33	141
115°	250	258	269	67	36	247
125°	354	360	368	371	372	316
135°	438	445	449	453	452	338
145°	508	508	515	518	516	318
155°	560	556	561	564	560	258
165°	590	587	588	592	588	167
175°	603	600	601	604	600	57
180°	602	602	602	602	602	

TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	737.1	737.1	737.1	737.1	737.1
2.5°	740.4	737.1	729.7	736.5	735.1
5°	737.1	733.8	725.0	731.1	729.1
7.5°	731.1	727.1	717.7	720.4	717.0
10°	723.1	718.4	705.1	703.0	699.1
12.5°	713.1	707.0	689.0	685.1	677.7
15°	701.1	693.7	671.0	658.3	651.8
17.5°	687.1	676.4	648.4	633.6	623.0
20°	671.0	657.6	624.4	607.7	593.0
22.5°	653.7	638.4	599.7	577.0	567.0
25°	636.4	615.0	571.0	543.7	533.6
27.5°	615.7	593.0	544.3	512.9	497.6
30°	593.7	568.3	515.0	481.0	462.9
32.5°	572.3	541.6	487.0	446.9	430.3
35°	548.3	514.3	455.7	413.6	398.9
37.5°	524.9	488.2	426.2	380.2	363.6
40°	500.2	460.3	395.6	348.2	330.8
42.5°	474.9	432.3	364.9	315.5	298.9
45°	448.3	403.5	333.6	286.1	270.1
47.5°	422.9	375.6	303.5	256.1	241.5
50°	394.9	347.6	274.2	228.1	214.2
52.5°	367.5	317.4	246.1	202.2	189.5
55°	340.8	288.8	216.8	176.8	164.1
57.5°	313.5	260.1	190.8	153.5	142.8
60°	285.5	232.1	163.5	129.5	118.8
62.5°	258.2	204.8	140.1	108.1	102.7
65°	230.2	176.1	116.1	93.5	91.4
67.5°	203.5	149.4	93.5	82.0	80.1
70°	175.4	123.4	77.3	70.7	68.0
72.5°	148.7	99.3	64.6	59.4	58.1
75°	122.7	76.0	53.3	48.7	48.1
77.5°	96.8	54.0	42.0	39.3	38.0
80°	72.7	38.7	32.0	29.3	29.3
82.5°	50.6	26.0	22.0	20.7	20.7
85°	28.6	14.6	12.7	12.7	12.7
87.5°	10.7	5.4	5.4	4.6	4.6
90°	0.4	5.3	8.6	10.9	11.8
92.5°	10.9	9.2	10.4	11.3	11.8
95°	28.3	13.9	16.9	19.2	18.7
97.5°	50.9	15.2	22.2	23.5	24.0
100°	77.1	17.4	24.8	28.3	29.2
102.5°	105.8	105.0	25.7	30.5	31.8
105°	132.4	145.4	26.6	31.3	33.1
107.5°	163.4	174.2	27.5	32.2	34.0
110°	193.0	202.1	76.2	32.7	34.4

TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	220.8	228.6	221.2	33.5	34.9
115°	250.4	257.8	268.8	67.1	35.8
117.5°	276.1	284.8	292.2	230.0	115.8
120°	304.9	311.4	319.2	324.5	265.6
122.5°	329.2	336.2	344.9	347.5	348.0
125°	354.1	359.7	368.0	371.0	372.4
127.5°	376.7	382.8	389.4	393.7	394.1
130°	398.1	405.0	409.8	414.6	414.2
132.5°	419.8	425.5	430.3	434.2	433.8
135°	438.2	445.1	449.0	453.4	452.5
137.5°	457.3	462.5	466.9	471.3	469.9
140°	476.0	479.6	484.3	488.2	486.1
142.5°	491.7	494.8	500.4	503.9	501.7
145°	508.3	507.8	515.2	518.3	516.1
147.5°	522.6	521.3	528.7	530.8	529.1
150°	536.5	533.5	540.5	543.1	540.9
152.5°	548.3	544.8	551.3	554.0	550.9
155°	559.6	555.7	561.0	563.6	560.1
157.5°	568.8	565.3	569.3	572.3	568.8
160°	576.7	574.0	576.7	579.3	576.2
162.5°	583.5	580.9	583.2	586.2	582.3
165°	589.7	587.1	588.4	591.5	588.4
167.5°	594.5	591.8	593.2	596.3	592.3
170°	598.4	595.8	596.6	599.7	595.8
172.5°	601.0	598.4	599.3	602.4	598.4
175°	603.2	600.1	601.0	604.0	599.7
177.5°	604.0	601.0	601.5	604.5	600.6
180°	601.9	601.9	601.9	601.9	601.9

TEST NUMBER: P921947

CATALOG NUMBER: DFN2DIP-PN2F0-020D020US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.29	9.09	9.29	10.09	11.42	4.26	5.06	5.26	6.07	7.39
	3H	9.95	10.66	10.95	11.67	13.02	5.43	6.15	6.44	7.16	8.51
	4H	10.54	11.22	11.56	12.23	13.59	5.87	6.55	6.89	7.56	8.92
	6H	10.94	11.57	11.97	12.59	13.95	6.17	6.80	7.20	7.82	9.18
	8H	11.06	11.65	12.09	12.69	14.05	6.25	6.85	7.29	7.88	9.25
	12H	11.11	11.68	12.15	12.70	14.09	6.29	6.85	7.33	7.88	9.27
4H	2H	8.30	8.98	9.33	9.99	11.35	4.84	5.52	5.87	6.54	7.89
	3H	10.11	10.67	11.14	11.71	13.08	6.17	6.73	7.20	7.78	9.15
	4H	10.78	11.29	11.82	12.33	13.72	6.70	7.22	7.74	8.25	9.64
	6H	11.27	11.72	12.32	12.77	14.16	7.10	7.54	8.15	8.60	9.99
	8H	11.44	11.85	12.49	12.90	14.30	7.22	7.63	8.27	8.68	10.09
	12H	11.52	11.89	12.59	12.96	14.36	7.27	7.65	8.34	8.71	10.12
8H	4H	10.74	11.15	11.79	12.20	13.61	6.97	7.38	8.02	8.43	9.83
	6H	11.28	11.62	12.36	12.72	14.12	7.46	7.80	8.53	8.89	10.29
	8H	11.49	11.79	12.57	12.86	14.28	7.64	7.94	8.72	9.01	10.43
	12H	11.61	11.87	12.69	12.94	14.40	7.74	8.01	8.83	9.08	10.54
12H	4H	10.69	11.06	11.76	12.13	13.54	6.97	7.34	8.04	8.41	9.81
	6H	11.26	11.56	12.34	12.63	14.05	7.50	7.80	8.59	8.88	10.30
	8H	11.46	11.73	12.55	12.80	14.26	7.70	7.96	8.78	9.03	10.49

END OF REPORT