

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P919209

Luminaire Tested: DFN2DIP-HX4F0-120D090US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P919209
REPORT IS A COMBINATION OF REPORTS P899406 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D090US935-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15640.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 177.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3175	3175	3175
5°	3180	3125	3145
10°	3149	3064	3043
15°	3106	2963	2885
20°	3049	2824	2691
25°	2991	2668	2503
30°	2912	2507	2266
35°	2835	2335	2057
40°	2757	2157	1817
45°	2666	1959	1600
50°	2572	1759	1388
55°	2473	1546	1185
60°	2360	1323	975
65°	2229	1095	878
70°	2071	884	795
75°	1872	780	724
80°	1583	655	628
85°	1107	439	473

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2666 cd/sqm

TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	400.2	2.6
10°-20°	1098.7	7.0
20°-30°	1542.5	9.9
30°-40°	1681.4	10.8
40°-50°	1545.4	9.9
50°-60°	1213.7	7.8
60°-70°	790.0	5.1
70°-80°	406.7	2.6
80°-90°	110.8	0.7
90°-100°	151.6	1.0
100°-110°	481.8	3.1
110°-120°	824.6	5.3
120°-130°	1084.4	6.9
130°-140°	1217.2	7.8
140°-150°	1193.6	7.6
150°-160°	1001.3	6.4
160°-170°	664.0	4.2
170°-180°	232.1	1.5
0°-30°	3041.3	19.4
0°-40°	4722.7	30.2
0°-60°	7481.7	47.8
0°-90°	8789.1	56.2
90°-120°	1458.0	9.3
90°-150°	4953.4	31.7
90°-180°	6851.0	43.8
0°-180°	15640.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4270	4270	4270	4270	4270	
5°	4270	4251	4200	4235	4224	405
15°	4062	4019	3888	3814	3776	1144
25°	3687	3563	3308	3150	3091	1696
35°	3177	2980	2640	2396	2311	1988
45°	2597	2338	1932	1658	1565	2006
55°	1975	1673	1256	1024	951	1764
65°	1333	1020	672	541	529	1322
75°	711	440	309	282	278	752
85°	166	85	73	73	73	191
90°	2	27	72	68	70	15
95°	108	128	132	132	128	120
105°	445	451	455	459	459	469
115°	828	839	836	833	828	818
125°	1204	1222	1216	1209	1207	1076
135°	1557	1580	1584	1582	1576	1203
145°	1890	1905	1916	1919	1911	1181
155°	2161	2167	2174	2184	2177	995
165°	2351	2349	2349	2364	2353	663
175°	2446	2440	2436	2451	2438	232
180°	2451	2451	2451	2451	2451	

TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4270.2	4270.2	4270.2	4270.2	4270.2
2.5°	4289.5	4270.2	4227.6	4266.5	4258.7
5°	4270.2	4250.9	4200.5	4235.3	4223.9
7.5°	4235.3	4212.3	4158.3	4173.4	4154.1
10°	4189.0	4162.0	4084.8	4073.0	4050.0
12.5°	4131.2	4096.4	3991.8	3968.9	3926.2
15°	4061.5	4018.9	3887.7	3814.2	3775.7
17.5°	3980.3	3918.4	3756.0	3671.2	3609.3
20°	3887.7	3810.2	3617.1	3520.7	3435.4
22.5°	3787.2	3698.2	3474.0	3342.7	3285.0
25°	3686.8	3562.9	3307.9	3149.6	3091.4
27.5°	3567.0	3435.4	3153.3	2971.7	2882.7
30°	3439.5	3292.4	2983.2	2786.4	2681.8
32.5°	3315.7	3137.7	2821.2	2589.2	2492.4
35°	3176.7	2979.5	2639.6	2396.1	2310.7
37.5°	3041.4	2828.6	2469.4	2202.5	2106.2
40°	2898.3	2666.7	2291.5	2017.2	1916.8
42.5°	2751.5	2504.3	2114.0	1827.8	1731.5
45°	2596.9	2337.9	1932.3	1657.7	1564.9
47.5°	2450.1	2175.9	1758.5	1483.8	1398.9
50°	2287.8	2013.5	1588.4	1321.5	1240.7
52.5°	2129.2	1839.3	1426.0	1171.0	1097.6
55°	1974.6	1673.3	1255.9	1024.2	950.8
57.5°	1816.3	1507.2	1105.3	888.9	827.0
60°	1654.0	1344.8	946.7	749.9	688.0
62.5°	1495.7	1186.5	811.4	626.1	595.3
65°	1333.3	1020.1	672.4	541.2	529.3
67.5°	1178.8	865.5	541.2	475.2	463.7
70°	1016.4	715.1	448.1	409.6	394.0
72.5°	861.9	575.7	374.7	344.0	336.2
75°	710.9	440.3	309.2	282.1	278.4
77.5°	560.5	312.8	243.6	228.0	220.2
80°	421.1	224.3	185.3	170.1	170.1
82.5°	293.6	150.8	127.5	119.7	119.7
85°	166.1	84.9	73.4	73.4	73.4
87.5°	61.9	30.7	30.7	27.0	27.0
90°	2.2	26.6	72.4	67.9	70.2
92.5°	45.8	62.1	64.3	66.5	66.5
95°	107.9	128.5	132.2	132.2	128.5
97.5°	179.5	198.7	206.9	206.9	206.9
100°	262.3	279.3	285.2	285.2	283.0
102.5°	349.5	362.0	370.1	372.4	370.1
105°	444.8	450.6	455.1	458.8	458.8
107.5°	539.3	548.2	548.2	549.7	539.3
110°	630.9	642.8	642.8	642.8	636.9

TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	730.0	742.5	740.3	734.4	730.0
115°	827.5	839.3	835.6	833.4	827.5
117.5°	924.3	940.6	930.2	924.3	918.3
120°	1021.8	1038.0	1021.8	1021.8	1015.1
122.5°	1110.4	1131.2	1120.8	1114.9	1110.4
125°	1203.6	1222.0	1216.2	1209.4	1207.3
127.5°	1294.4	1317.3	1309.2	1300.4	1294.4
130°	1379.4	1406.0	1402.3	1397.8	1389.7
132.5°	1474.7	1495.4	1496.8	1486.5	1480.7
135°	1556.7	1579.6	1584.1	1581.8	1576.0
137.5°	1648.3	1666.8	1670.5	1669.0	1660.2
140°	1728.9	1747.3	1757.6	1757.6	1749.5
142.5°	1811.6	1830.1	1836.0	1838.2	1830.1
145°	1890.0	1904.7	1916.5	1918.7	1910.6
147.5°	1960.1	1978.6	1987.4	1991.1	1983.1
150°	2032.6	2045.1	2053.2	2059.9	2053.2
152.5°	2096.8	2109.4	2119.7	2127.9	2119.7
155°	2161.1	2167.0	2173.7	2184.0	2177.4
157.5°	2216.5	2220.9	2224.6	2239.4	2229.0
160°	2266.0	2270.5	2272.7	2285.2	2276.3
162.5°	2311.8	2311.8	2314.0	2328.1	2317.7
165°	2351.0	2348.7	2348.7	2363.5	2353.2
167.5°	2386.4	2379.8	2379.8	2394.5	2384.2
170°	2413.0	2407.1	2404.9	2419.7	2407.1
172.5°	2431.5	2425.6	2423.4	2438.2	2425.6
175°	2446.3	2440.3	2435.9	2450.7	2438.2
177.5°	2454.4	2448.5	2444.0	2456.6	2444.0
180°	2450.7	2450.7	2450.7	2450.7	2450.7

TEST NUMBER: P919209

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	12.60	12.63	13.53	14.71	7.69	8.58	8.60	9.50	10.68
	3H	13.40	14.19	14.32	15.13	16.33	8.89	9.68	9.81	10.61	11.82
	4H	14.02	14.76	14.95	15.70	16.92	9.34	10.09	10.28	11.03	12.24
	6H	14.44	15.13	15.39	16.07	17.30	9.67	10.35	10.62	11.30	12.53
	8H	14.57	15.22	15.52	16.18	17.41	9.76	10.41	10.72	11.37	12.60
	12H	14.63	15.25	15.59	16.21	17.46	9.81	10.43	10.77	11.38	12.63
4H	2H	11.75	12.49	12.69	13.43	14.65	8.30	9.04	9.24	9.98	11.20
	3H	13.58	14.20	14.53	15.17	16.40	9.65	10.27	10.60	11.24	12.47
	4H	14.28	14.84	15.24	15.80	17.06	10.21	10.77	11.17	11.73	12.99
	6H	14.80	15.28	15.77	16.27	17.52	10.63	11.12	11.60	12.10	13.36
	8H	14.97	15.43	15.95	16.41	17.67	10.76	11.21	11.74	12.19	13.46
	12H	15.07	15.48	16.06	16.48	17.75	10.83	11.24	11.82	12.23	13.51
8H	4H	14.25	14.70	15.22	15.68	16.95	10.49	10.94	11.47	11.92	13.19
	6H	14.82	15.19	15.82	16.21	17.48	11.01	11.39	12.01	12.41	13.68
	8H	15.04	15.37	16.04	16.38	17.66	11.20	11.54	12.21	12.55	13.83
	12H	15.18	15.47	16.19	16.47	17.80	11.33	11.62	12.34	12.62	13.95
12H	4H	14.20	14.61	15.20	15.61	16.88	10.50	10.91	11.49	11.90	13.18
	6H	14.79	15.12	15.80	16.13	17.42	11.06	11.39	12.07	12.40	13.69
	8H	15.02	15.31	16.03	16.31	17.64	11.28	11.57	12.29	12.57	13.90

END OF REPORT