

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921961

Luminaire Tested: DFN2DIP-PN2F0-020D060US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921961
REPORT IS A COMBINATION OF REPORTS P901021 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US940-FLLONL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7062.3 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1503	1503	1503
5°	1503	1479	1490
10°	1488	1456	1467
15°	1464	1428	1434
20°	1432	1392	1399
25°	1400	1349	1360
30°	1361	1309	1310
35°	1324	1262	1258
40°	1277	1214	1208
45°	1232	1166	1157
50°	1182	1116	1098
55°	1129	1058	1043
60°	1069	990	980
65°	1004	918	906
70°	920	831	826
75°	806	727	749
80°	668	593	606
85°	452	374	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1658 cd/sqm

TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	0.9
10°-20°	183.8	2.6
20°-30°	270.1	3.8
30°-40°	313.7	4.4
40°-50°	313.3	4.4
50°-60°	273.2	3.9
60°-70°	201.9	2.9
70°-80°	114.2	1.6
80°-90°	33.3	0.5
90°-100°	59.5	0.8
100°-110°	222.0	3.1
110°-120°	588.7	8.3
120°-130°	976.3	13.8
130°-140°	1037.1	14.7
140°-150°	963.9	13.6
150°-160°	774.9	11.0
160°-170°	499.3	7.1
170°-180°	171.9	2.4
0°-30°	519.1	7.4
0°-40°	832.8	11.8
0°-60°	1419.3	20.1
0°-90°	1768.8	25.0
90°-120°	870.2	12.3
90°-150°	3847.4	54.5
90°-180°	5294.0	75.0
0°-180°	7062.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	694	691	684	689	688	66
15°	661	657	648	651	647	186
25°	598	592	581	582	581	275
35°	516	509	498	494	491	322
45°	420	415	405	398	395	324
55°	318	314	306	298	294	284
65°	214	210	204	198	194	212
75°	112	111	107	103	105	120
85°	27	27	26	24	23	30
90°	1	16	26	33	35	6
95°	85	42	51	58	56	101
105°	397	436	80	94	99	424
115°	751	774	806	201	107	740
125°	1062	1079	1104	1113	1117	947
135°	1314	1335	1347	1360	1358	1015
145°	1525	1523	1546	1555	1548	954
155°	1679	1667	1683	1691	1680	774
165°	1769	1761	1765	1774	1765	500
175°	1810	1800	1803	1812	1799	172
180°	1806	1806	1806	1806	1806	

TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	693.9	693.9	693.9	693.9	693.9
2.5°	697.9	694.6	687.2	693.9	692.7
5°	693.9	691.3	683.9	689.3	688.0
7.5°	689.3	685.3	678.0	683.3	682.0
10°	682.0	677.3	669.3	674.6	672.6
12.5°	671.9	668.0	660.0	663.3	661.9
15°	660.6	656.7	647.9	650.6	647.3
17.5°	646.6	642.7	633.9	637.2	633.9
20°	631.2	627.2	617.9	619.9	617.2
22.5°	615.9	609.9	601.2	601.2	599.9
25°	597.9	592.5	581.2	582.5	581.2
27.5°	577.8	573.2	564.5	562.6	559.2
30°	557.9	552.5	542.5	540.6	537.8
32.5°	536.5	532.5	521.8	517.8	515.1
35°	515.9	509.2	498.5	494.5	491.1
37.5°	492.5	486.4	475.7	471.1	467.7
40°	468.4	463.1	452.4	446.5	443.7
42.5°	445.1	439.7	429.1	422.4	418.4
45°	419.7	415.1	405.0	397.7	395.0
47.5°	395.0	390.4	379.7	372.3	368.4
50°	369.0	365.7	356.3	347.0	343.7
52.5°	343.7	338.9	330.3	323.0	318.3
55°	317.6	313.6	305.6	297.7	294.3
57.5°	291.6	288.3	279.6	271.6	268.9
60°	265.6	263.0	253.6	246.2	244.2
62.5°	240.2	235.5	228.9	222.2	219.5
65°	214.2	210.2	203.6	197.5	194.2
67.5°	187.5	184.1	178.2	173.5	170.9
70°	162.8	160.2	154.1	149.5	146.9
72.5°	137.5	134.8	131.4	126.8	124.8
75°	112.1	110.8	107.4	103.4	104.8
77.5°	89.4	86.8	85.3	83.4	81.4
80°	66.8	66.1	64.7	62.7	61.3
82.5°	45.4	45.4	44.8	42.1	42.1
85°	27.3	26.7	26.0	24.0	23.4
87.5°	12.0	10.7	9.4	7.4	6.7
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.8	45.7	66.5	70.6	71.9
100°	231.3	52.3	74.5	84.9	87.5
102.5°	317.4	315.0	77.1	91.4	95.4
105°	397.2	436.4	79.7	94.0	99.3
107.5°	490.0	522.5	82.4	96.7	101.9
110°	578.9	606.2	228.7	98.1	103.2

TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.5	685.9	663.7	100.5	104.6
115°	751.3	773.5	806.2	201.3	107.2
117.5°	828.3	854.4	876.7	689.8	347.5
120°	914.6	934.2	957.8	973.4	797.0
122.5°	987.7	1008.6	1034.8	1042.6	1044.0
125°	1062.2	1079.2	1104.0	1113.2	1117.0
127.5°	1130.2	1148.4	1168.1	1181.2	1182.4
130°	1194.2	1215.1	1229.4	1243.8	1242.6
132.5°	1259.5	1276.6	1290.8	1302.6	1301.4
135°	1314.5	1335.4	1347.0	1360.2	1357.5
137.5°	1371.8	1387.5	1400.7	1413.7	1409.9
140°	1428.0	1438.6	1452.9	1464.6	1458.1
142.5°	1475.2	1484.3	1501.3	1511.6	1505.1
145°	1524.8	1523.4	1545.6	1554.8	1548.3
147.5°	1567.8	1563.9	1586.1	1592.6	1587.5
150°	1609.7	1600.5	1621.5	1629.2	1622.7
152.5°	1644.9	1634.5	1654.0	1662.0	1652.8
155°	1678.9	1667.2	1682.9	1690.7	1680.2
157.5°	1706.4	1695.9	1707.7	1716.9	1706.4
160°	1729.9	1722.0	1729.9	1737.7	1728.6
162.5°	1750.7	1742.9	1749.4	1758.6	1746.9
165°	1769.1	1761.3	1765.1	1774.3	1765.1
167.5°	1783.4	1775.6	1779.6	1788.8	1776.9
170°	1795.3	1787.3	1790.0	1799.1	1787.3
172.5°	1803.0	1795.3	1797.9	1807.1	1795.3
175°	1809.5	1800.4	1803.0	1812.1	1799.1
177.5°	1812.1	1803.0	1804.4	1813.6	1801.8
180°	1805.6	1805.6	1805.6	1805.6	1805.6

TEST NUMBER: P921961

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.63	6.30	6.77	7.44	9.03	5.19	5.87	6.34	7.00	8.59
	3H	7.25	7.86	8.41	9.00	10.60	6.78	7.38	7.93	8.52	10.12
	4H	7.82	8.39	8.98	9.54	11.14	7.34	7.91	8.50	9.06	10.66
	6H	8.19	8.72	9.36	9.87	11.49	7.71	8.24	8.88	9.38	11.00
	8H	8.29	8.79	9.46	9.95	11.56	7.80	8.30	8.97	9.46	11.07
	12H	8.32	8.80	9.50	9.95	11.58	7.83	8.30	9.00	9.46	11.09
4H	2H	6.06	6.63	7.23	7.77	9.38	5.71	6.28	6.88	7.42	9.03
	3H	7.88	8.36	9.06	9.53	11.15	7.48	7.96	8.66	9.13	10.75
	4H	8.57	9.01	9.75	10.17	11.81	8.16	8.60	9.33	9.76	11.39
	6H	9.06	9.43	10.24	10.61	12.24	8.64	9.01	9.82	10.19	11.82
	8H	9.19	9.55	10.37	10.72	12.36	8.77	9.12	9.95	10.29	11.94
	12H	9.25	9.57	10.44	10.75	12.40	8.81	9.13	10.01	10.31	11.96
8H	4H	8.74	9.09	9.92	10.27	11.91	8.37	8.73	9.55	9.90	11.54
	6H	9.34	9.63	10.54	10.85	12.49	8.97	9.26	10.17	10.47	12.11
	8H	9.55	9.80	10.75	10.99	12.65	9.17	9.42	10.37	10.61	12.27
	12H	9.66	9.88	10.86	11.07	12.76	9.26	9.48	10.47	10.67	12.36
12H	4H	8.72	9.04	9.91	10.22	11.87	8.36	8.68	9.55	9.86	11.51
	6H	9.37	9.62	10.57	10.81	12.47	9.00	9.25	10.21	10.45	12.11
	8H	9.58	9.80	10.79	10.99	12.69	9.21	9.44	10.42	10.62	12.32

END OF REPORT