

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929152

Luminaire Tested: DFN2DIP-HX4F0-040D070US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929152
REPORT IS A COMBINATION OF REPORTS P900873 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D070US940-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9713.9 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929152
CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929152

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36				36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31				31
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31	26				26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22				22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19				19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16				16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14				14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13				13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11				11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10				10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1032	1032	1032
5°	1034	1018	1025
10°	1026	1004	1011
15°	1011	988	989
20°	990	965	967
25°	970	938	942
30°	945	912	909
35°	921	882	875
40°	891	852	842
45°	862	821	808
50°	830	790	769
55°	796	753	734
60°	758	709	693
65°	717	663	645
70°	664	608	593
75°	590	542	545
80°	502	457	453
85°	365	312	301

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1082 cd/sqm



TEST NUMBER: P929152

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	1.3
10°-20°	367.6	3.8
20°-30°	540.3	5.6
30°-40°	627.5	6.5
40°-50°	626.8	6.5
50°-60°	546.5	5.6
60°-70°	404.0	4.2
70°-80°	228.6	2.4
80°-90°	64.0	0.7
90°-100°	69.5	0.7
100°-110°	259.0	2.7
110°-120°	687.0	7.1
120°-130°	1139.4	11.7
130°-140°	1210.3	12.5
140°-150°	1124.9	11.6
150°-160°	904.4	9.3
160°-170°	582.7	6.0
170°-180°	200.6	2.1
0°-30°	1038.6	10.7
0°-40°	1666.2	17.2
0°-60°	2839.4	29.2
0°-90°	3536.1	36.4
90°-120°	1015.5	10.5
90°-150°	4490.2	46.2
90°-180°	6178.0	63.6
0°-180°	9713.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	61
90°	1	18	30	38	41	9
95°	99	49	59	67	66	117
105°	464	509	93	110	116	495
115°	877	903	941	235	125	863
125°	1240	1260	1288	1299	1304	1106
135°	1534	1558	1572	1587	1584	1185
145°	1780	1778	1804	1814	1807	1113
155°	1959	1946	1964	1973	1961	903
165°	2064	2056	2060	2071	2060	583
175°	2112	2101	2104	2115	2100	201
180°	2107	2107	2107	2107	2107	



TEST NUMBER: P929152

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.2	65.6
97.5°	178.3	53.4	77.7	82.4	83.8
100°	270.0	61.0	86.9	99.0	102.1
102.5°	370.4	367.6	90.0	106.7	111.3
105°	463.6	509.3	93.0	109.7	115.9
107.5°	571.8	609.9	96.2	112.8	119.0
110°	675.6	707.4	266.9	114.4	120.4



TEST NUMBER: P929152

CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	773.2	800.5	774.6	117.3	122.0
115°	876.7	902.6	940.8	234.9	125.1
117.5°	966.7	997.2	1023.2	805.0	405.6
120°	1067.4	1090.2	1117.8	1136.1	930.2
122.5°	1152.6	1177.1	1207.8	1216.8	1218.4
125°	1239.6	1259.5	1288.5	1299.2	1303.7
127.5°	1318.9	1340.2	1363.2	1378.5	1379.9
130°	1393.7	1418.1	1434.8	1451.6	1450.2
132.5°	1469.9	1489.8	1506.5	1520.2	1518.8
135°	1534.0	1558.4	1572.1	1587.4	1584.4
137.5°	1601.0	1619.3	1634.7	1649.9	1645.4
140°	1666.5	1678.8	1695.5	1709.3	1701.7
142.5°	1721.6	1732.3	1752.0	1764.1	1756.5
145°	1779.5	1777.9	1803.8	1814.5	1806.9
147.5°	1829.7	1825.2	1851.1	1858.7	1852.7
150°	1878.6	1867.9	1892.4	1901.4	1893.8
152.5°	1919.7	1907.5	1930.4	1939.6	1929.0
155°	1959.4	1945.7	1964.0	1973.1	1961.0
157.5°	1991.4	1979.3	1993.0	2003.7	1991.4
160°	2019.0	2009.7	2019.0	2028.0	2017.3
162.5°	2043.2	2034.1	2041.7	2052.4	2038.7
165°	2064.5	2055.5	2060.0	2070.7	2060.0
167.5°	2081.4	2072.1	2076.8	2087.5	2073.8
170°	2095.1	2085.9	2089.0	2099.7	2085.9
172.5°	2104.2	2095.1	2098.3	2108.9	2095.1
175°	2111.8	2101.1	2104.2	2114.8	2099.7
177.5°	2114.8	2104.2	2105.8	2116.5	2102.7
180°	2107.3	2107.3	2107.3	2107.3	2107.3



TEST NUMBER: P929152
 CATALOG NUMBER: DFN2DIP-HX4F0-040D070US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.98	6.73	7.04	7.80	9.25	5.54	6.30	6.61	7.36	8.82
	3H	7.63	8.30	8.70	9.38	10.85	7.16	7.83	8.23	8.91	10.38
	4H	8.21	8.85	9.30	9.93	11.41	7.74	8.38	8.83	9.46	10.93
	6H	8.61	9.20	9.70	10.28	11.77	8.13	8.72	9.23	9.80	11.29
	8H	8.71	9.27	9.81	10.37	11.85	8.23	8.79	9.33	9.89	11.37
	12H	8.75	9.29	9.86	10.38	11.88	8.27	8.80	9.38	9.90	11.40
4H	2H	6.43	7.06	7.52	8.14	9.62	6.08	6.72	7.17	7.80	9.27
	3H	8.28	8.82	9.38	9.92	11.41	7.89	8.42	8.99	9.53	11.02
	4H	8.99	9.48	10.10	10.58	12.09	8.59	9.08	9.69	10.17	11.68
	6H	9.50	9.92	10.62	11.04	12.54	9.09	9.51	10.21	10.63	12.13
	8H	9.65	10.04	10.76	11.15	12.67	9.24	9.63	10.35	10.74	12.26
	12H	9.72	10.07	10.85	11.20	12.72	9.30	9.65	10.43	10.77	12.30
8H	4H	9.18	9.57	10.29	10.68	12.20	8.82	9.21	9.93	10.32	11.84
	6H	9.81	10.13	10.94	11.29	12.80	9.45	9.77	10.58	10.92	12.44
	8H	10.03	10.31	11.17	11.45	12.98	9.66	9.94	10.80	11.08	12.61
	12H	10.16	10.41	11.30	11.54	13.11	9.77	10.02	10.92	11.15	12.72
12H	4H	9.16	9.52	10.29	10.64	12.17	8.81	9.16	9.94	10.29	11.81
	6H	9.84	10.12	10.98	11.26	12.79	9.49	9.77	10.63	10.90	12.44
	8H	10.08	10.33	11.22	11.45	13.03	9.72	9.97	10.86	11.10	12.67