

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922008

Luminaire Tested: DFN2DIP-PN2F0-050D030US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922008
REPORT IS A COMBINATION OF REPORTS P899477 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-050D030US940-FLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6781.5 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 69.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922008
CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P922008

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	70	70	70	65
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59	62	60	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	48	45	42	39
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37	43	40	37	33
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28	35	31	28	26
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25	32	28	25	23
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	27	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3757	3757	3757
5°	3757	3697	3725
10°	3721	3639	3669
15°	3660	3571	3584
20°	3580	3480	3498
25°	3501	3373	3399
30°	3402	3272	3276
35°	3308	3155	3145
40°	3194	3036	3020
45°	3080	2916	2892
50°	2954	2791	2744
55°	2823	2645	2607
60°	2673	2474	2450
65°	2509	2295	2264
70°	2301	2078	2064
75°	2016	1817	1871
80°	1668	1484	1518
85°	1132	938	951

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3080 cd/sqm



TEST NUMBER: P922008

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	2.4
10°-20°	459.4	6.8
20°-30°	675.2	10.0
30°-40°	784.2	11.6
40°-50°	783.2	11.5
50°-60°	682.9	10.1
60°-70°	504.8	7.4
70°-80°	285.6	4.2
80°-90°	77.8	1.1
90°-100°	52.3	0.8
100°-110°	166.3	2.5
110°-120°	284.7	4.2
120°-130°	374.4	5.5
130°-140°	420.2	6.2
140°-150°	412.1	6.1
150°-160°	345.7	5.1
160°-170°	229.2	3.4
170°-180°	80.1	1.2
0°-30°	1297.9	19.1
0°-40°	2082.0	30.7
0°-60°	3548.1	52.3
0°-90°	4416.4	65.1
90°-120°	503.4	7.4
90°-150°	1710.0	25.2
90°-180°	2365.0	34.9
0°-180°	6781.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	1	9	25	24	24	7
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	



TEST NUMBER: P922008

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9



TEST NUMBER: P922008

CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1



TEST NUMBER: P922008
 CATALOG NUMBER: DFN2DIP-PN2F0-050D030US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.04	14.06	13.86	14.90	15.94	12.61	13.62	13.42	14.46	15.50
	3H	14.70	15.61	15.52	16.46	17.52	14.21	15.13	15.04	15.97	17.04
	4H	15.28	16.14	16.12	16.99	18.07	14.79	15.66	15.64	16.51	17.59
	6H	15.67	16.46	16.53	17.33	18.42	15.18	15.98	16.04	16.84	17.93
	8H	15.77	16.53	16.64	17.41	18.50	15.28	16.04	16.15	16.92	18.01
	12H	15.82	16.54	16.69	17.41	18.53	15.32	16.04	16.19	16.92	18.03
4H	2H	13.51	14.37	14.36	15.23	16.31	13.16	14.02	14.01	14.88	15.96
	3H	15.37	16.09	16.23	16.98	18.07	14.97	15.69	15.83	16.58	17.67
	4H	16.07	16.73	16.95	17.61	18.73	15.66	16.32	16.53	17.20	18.32
	6H	16.58	17.15	17.47	18.05	19.18	16.16	16.73	17.05	17.63	18.76
	8H	16.72	17.25	17.61	18.15	19.29	16.30	16.83	17.19	17.73	18.87
	12H	16.79	17.27	17.70	18.19	19.33	16.36	16.84	17.27	17.76	18.90
8H	4H	16.27	16.80	17.16	17.71	18.84	15.90	16.43	16.79	17.34	18.47
	6H	16.88	17.32	17.80	18.27	19.40	16.51	16.95	17.43	17.90	19.03
	8H	17.09	17.48	18.02	18.42	19.57	16.71	17.10	17.64	18.04	19.19
	12H	17.22	17.56	18.15	18.49	19.69	16.82	17.16	17.75	18.09	19.30
12H	4H	16.26	16.74	17.17	17.66	18.80	15.90	16.38	16.81	17.30	18.44
	6H	16.91	17.30	17.84	18.24	19.39	16.55	16.94	17.48	17.88	19.03
	8H	17.14	17.49	18.08	18.42	19.62	16.78	17.12	17.71	18.05	19.25