

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921797

Luminaire Tested: DFN2DIP-HX4F0-040D110US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921797
REPORT IS A COMBINATION OF REPORTS P899426 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US940-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11712.6 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 98.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		90	90	90	90		70	70	70		51	51	51		34	34	34
1	93	89	85	82		82	79	76	73		62	60	58		45	44	43		30	30	29
2	85	78	72	67		75	69	65	61		54	51	48		40	38	36		27	26	25
3	77	68	61	56		69	61	55	51		48	44	41		36	33	31		24	23	21
4	71	61	53	47		63	54	48	43		43	38	35		32	29	27		22	20	19
5	65	54	46	41		58	48	42	37		38	34	30		29	26	23		20	18	16
6	60	48	41	35		53	43	37	32		34	30	26		26	23	20		18	16	15
7	55	43	36	31		49	39	33	28		31	26	23		24	20	18		16	14	13
8	51	39	32	27		46	36	29	25		28	24	20		21	18	16		15	13	12
9	47	36	29	24		42	32	26	22		26	21	18		20	17	14		14	12	11
10	44	33	26	21		40	30	24	20		24	19	16		18	15	13		13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1096	1096	1096
5°	1098	1079	1086
10°	1087	1058	1050
15°	1072	1023	996
20°	1053	975	929
25°	1032	921	864
30°	1005	866	782
35°	979	806	710
40°	952	745	627
45°	920	676	553
50°	888	607	479
55°	854	534	409
60°	815	457	337
65°	769	378	303
70°	715	305	274
75°	646	269	250
80°	546	226	217
85°	382	151	163

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2338 cd/sqm

TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	1.2
10°-20°	379.3	3.2
20°-30°	532.5	4.5
30°-40°	580.5	5.0
40°-50°	533.5	4.6
50°-60°	419.0	3.6
60°-70°	272.7	2.3
70°-80°	140.4	1.2
80°-90°	44.7	0.4
90°-100°	192.0	1.6
100°-110°	609.9	5.2
110°-120°	1043.8	8.9
120°-130°	1372.7	11.7
130°-140°	1540.8	13.2
140°-150°	1511.0	12.9
150°-160°	1267.5	10.8
160°-170°	840.6	7.2
170°-180°	293.8	2.5
0°-30°	1049.9	9.0
0°-40°	1630.4	13.9
0°-60°	2582.9	22.1
0°-90°	3040.6	26.0
90°-120°	1845.7	15.8
90°-150°	6270.1	53.5
90°-180°	8672.0	74.0
0°-180°	11712.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	3	34	92	86	89	12
95°	136	163	167	167	163	152
105°	563	570	576	581	581	594
115°	1048	1062	1058	1055	1048	1036
125°	1524	1547	1539	1531	1528	1361
135°	1970	2000	2005	2002	1995	1523
145°	2392	2411	2426	2429	2418	1495
155°	2736	2743	2752	2765	2756	1259
165°	2976	2973	2973	2992	2979	840
175°	3097	3089	3083	3102	3086	294
180°	3102	3102	3102	3102	3102	

TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	2.8	33.7	91.7	86.1	88.8
92.5°	58.0	78.6	81.3	84.2	84.2
95°	136.5	162.7	167.4	167.4	162.7
97.5°	227.3	251.6	261.9	261.9	261.9
100°	332.0	353.5	361.0	361.0	358.2
102.5°	442.4	458.2	468.6	471.4	468.6
105°	563.0	570.5	576.1	580.8	580.8
107.5°	682.7	693.9	693.9	695.8	682.7
110°	798.7	813.7	813.7	813.7	806.2

TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	924.0	939.9	937.1	929.6	924.0
115°	1047.5	1062.4	1057.7	1055.0	1047.5
117.5°	1170.0	1190.5	1177.4	1170.0	1162.5
120°	1293.4	1314.0	1293.4	1293.4	1285.0
122.5°	1405.7	1431.8	1418.7	1411.2	1405.7
125°	1523.5	1546.8	1539.4	1531.0	1528.1
127.5°	1638.5	1667.5	1657.2	1646.0	1638.5
130°	1746.1	1779.8	1775.0	1769.4	1759.2
132.5°	1866.7	1892.9	1894.8	1881.7	1874.2
135°	1970.5	1999.5	2005.1	2002.3	1994.8
137.5°	2086.5	2109.9	2114.5	2112.6	2101.5
140°	2188.4	2211.8	2224.9	2224.9	2214.7
142.5°	2293.2	2316.6	2324.1	2326.8	2316.6
145°	2392.3	2411.0	2426.0	2428.8	2418.5
147.5°	2481.2	2504.5	2515.8	2520.4	2510.2
150°	2572.9	2588.7	2599.0	2607.5	2599.0
152.5°	2654.2	2670.0	2683.2	2693.5	2683.2
155°	2735.6	2743.0	2751.5	2764.6	2756.1
157.5°	2805.7	2811.3	2815.9	2834.7	2821.5
160°	2868.4	2874.0	2876.7	2892.7	2881.5
162.5°	2926.3	2926.3	2929.2	2946.9	2933.8
165°	2975.9	2973.1	2973.1	2991.8	2978.7
167.5°	3020.8	3012.4	3012.4	3031.1	3018.0
170°	3054.5	3047.0	3044.2	3062.8	3047.0
172.5°	3077.8	3070.3	3067.6	3086.3	3070.3
175°	3096.6	3089.1	3083.4	3102.2	3086.3
177.5°	3106.8	3099.3	3093.7	3109.7	3093.7
180°	3102.2	3102.2	3102.2	3102.2	3102.2

TEST NUMBER: P921797

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.64	5.31	5.79	6.44	8.02	0.61	1.28	1.76	2.41	3.99
	3H	6.31	6.90	7.46	8.04	9.64	1.79	2.39	2.94	3.53	5.12
	4H	6.91	7.48	8.07	8.61	10.21	2.24	2.80	3.40	3.94	5.54
	6H	7.32	7.84	8.49	8.98	10.60	2.55	3.07	3.72	4.21	5.82
	8H	7.45	7.94	8.62	9.10	10.70	2.64	3.13	3.81	4.29	5.89
	12H	7.50	7.97	8.68	9.12	10.75	2.68	3.15	3.85	4.30	5.92
4H	2H	4.64	5.21	5.81	6.34	7.94	1.19	1.76	2.36	2.89	4.49
	3H	6.46	6.93	7.63	8.09	9.70	2.53	3.00	3.70	4.16	5.77
	4H	7.14	7.58	8.32	8.73	10.36	3.07	3.50	4.24	4.66	6.29
	6H	7.65	8.02	8.83	9.20	10.82	3.48	3.85	4.66	5.03	6.65
	8H	7.82	8.17	9.00	9.33	10.97	3.61	3.96	4.79	5.12	6.76
	12H	7.91	8.22	9.10	9.40	11.04	3.67	3.98	4.86	5.16	6.80
8H	4H	7.10	7.44	8.28	8.61	10.25	3.34	3.68	4.52	4.85	6.49
	6H	7.66	7.94	8.86	9.15	10.79	3.85	4.14	5.05	5.35	6.98
	8H	7.88	8.12	9.08	9.31	10.96	4.05	4.29	5.25	5.48	7.13
	12H	8.01	8.23	9.21	9.41	11.10	4.16	4.38	5.36	5.56	7.25
12H	4H	7.04	7.36	8.24	8.53	10.18	3.34	3.65	4.53	4.83	6.47
	6H	7.63	7.88	8.84	9.07	10.72	3.90	4.15	5.11	5.34	6.99
	8H	7.85	8.07	9.05	9.25	10.94	4.11	4.33	5.31	5.51	7.20

END OF REPORT