

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929214

Luminaire Tested: DFN2DIP-HX4F0-060D040US940-RLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P929214  
REPORT IS A COMBINATION OF REPORTS P900824 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-060D040US940-RLONL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8081.5 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 84.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.099  
Total Harmonic Distortion (THDi): 0.979  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P929214  
CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P929214

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53	49	49	49	49
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46	42	42	42	42
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31	27	27	27	27
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24	24	24	24
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1645	1645	1645
5°	1648	1619	1629
10°	1631	1587	1576
15°	1609	1535	1494
20°	1579	1463	1394
25°	1549	1382	1297
30°	1508	1299	1174
35°	1469	1210	1065
40°	1428	1117	941
45°	1381	1015	829
50°	1332	911	719
55°	1281	801	614
60°	1222	685	505
65°	1155	567	455
70°	1073	458	412
75°	970	404	375
80°	820	339	325
85°	573	227	245

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1381 cd/sqm



TEST NUMBER: P929214

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.3	2.6
10°-20°	569.1	7.0
20°-30°	799.0	9.9
30°-40°	871.0	10.8
40°-50°	800.5	9.9
50°-60°	628.7	7.8
60°-70°	409.2	5.1
70°-80°	210.6	2.6
80°-90°	55.9	0.7
90°-100°	39.7	0.5
100°-110°	148.0	1.8
110°-120°	392.6	4.9
120°-130°	651.1	8.1
130°-140°	691.6	8.6
140°-150°	642.8	8.0
150°-160°	516.8	6.4
160°-170°	333.0	4.1
170°-180°	114.6	1.4
0°-30°	1575.4	19.5
0°-40°	2446.4	30.3
0°-60°	3875.6	48.0
0°-90°	4551.3	56.3
90°-120°	580.3	7.2
90°-150°	2565.8	31.7
90°-180°	3530.0	43.7
0°-180°	8081.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2212	2212	2212	2212	2212	
5°	2212	2202	2176	2194	2188	210
15°	2104	2082	2014	1976	1956	593
25°	1910	1846	1714	1632	1601	878
35°	1646	1543	1367	1241	1197	1030
45°	1345	1211	1001	859	811	1039
55°	1023	867	650	531	492	914
65°	691	528	348	280	274	685
75°	368	228	160	146	144	390
85°	86	44	38	38	38	99
90°	1	10	17	22	24	8
95°	57	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	538	134	72	493
125°	708	720	736	742	745	632
135°	877	891	898	907	905	677
145°	1017	1016	1031	1037	1032	636
155°	1120	1112	1122	1128	1120	516
165°	1180	1175	1177	1183	1177	333
175°	1207	1201	1202	1208	1200	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P929214

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2212.0	2212.0	2212.0	2212.0	2212.0
2.5°	2222.0	2212.0	2189.9	2210.0	2206.0
5°	2212.0	2202.0	2175.9	2194.0	2188.0
7.5°	2194.0	2182.0	2154.0	2161.9	2151.9
10°	2169.9	2155.9	2116.0	2109.8	2097.9
12.5°	2140.0	2121.9	2067.7	2055.9	2033.8
15°	2103.9	2081.7	2013.8	1975.8	1955.8
17.5°	2061.9	2029.7	1945.6	1901.7	1869.6
20°	2013.8	1973.6	1873.6	1823.7	1779.5
22.5°	1961.8	1915.7	1799.5	1731.6	1701.6
25°	1909.8	1845.6	1713.5	1631.6	1601.4
27.5°	1847.8	1779.5	1633.4	1539.3	1493.3
30°	1781.7	1705.4	1545.3	1443.3	1389.2
32.5°	1717.5	1625.4	1461.5	1341.2	1291.1
35°	1645.6	1543.4	1367.3	1241.1	1197.0
37.5°	1575.5	1465.2	1279.2	1141.0	1091.0
40°	1501.3	1381.4	1187.0	1044.9	992.9
42.5°	1425.3	1297.2	1095.0	946.8	896.9
45°	1345.2	1211.0	1001.0	858.6	810.6
47.5°	1269.2	1127.1	910.9	768.6	724.7
50°	1185.1	1043.0	822.8	684.5	642.7
52.5°	1102.9	952.7	738.7	606.6	568.6
55°	1022.9	866.8	650.5	530.6	492.5
57.5°	940.9	780.7	572.6	460.5	428.3
60°	856.8	696.7	490.4	388.5	356.4
62.5°	774.8	614.7	420.3	324.3	308.4
65°	690.7	528.4	348.3	280.4	274.2
67.5°	610.6	448.3	280.4	246.2	240.2
70°	526.5	370.4	232.1	212.2	204.1
72.5°	446.4	298.2	194.1	178.2	174.1
75°	368.3	228.1	160.1	146.1	144.2
77.5°	290.3	162.1	126.1	118.1	114.1
80°	218.1	116.1	96.0	88.1	88.1
82.5°	152.1	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	0.8	10.4	17.4	21.9	23.5
92.5°	21.9	18.3	20.9	22.7	23.5
95°	56.6	27.8	33.9	38.4	37.5
97.5°	102.0	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.6	58.3
102.5°	211.7	210.1	51.4	60.9	63.6
105°	264.8	291.1	53.2	62.7	66.2
107.5°	326.7	348.5	54.9	64.5	68.0
110°	386.1	404.3	152.5	65.4	68.8



TEST NUMBER: P929214

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	441.8	457.4	442.6	67.1	69.8
115°	500.9	515.8	537.6	134.2	71.5
117.5°	552.4	569.8	584.7	460.0	231.7
120°	609.9	623.0	638.7	649.2	531.5
122.5°	658.7	672.7	690.1	695.3	696.2
125°	708.3	719.8	736.3	742.4	745.0
127.5°	753.7	765.9	779.0	787.7	788.5
130°	796.4	810.4	819.8	829.5	828.7
132.5°	839.9	851.3	860.9	868.7	867.9
135°	876.6	890.6	898.3	907.1	905.4
137.5°	914.8	925.3	934.1	942.8	940.2
140°	952.3	959.3	968.9	976.7	972.4
142.5°	983.8	989.9	1001.2	1008.0	1003.8
145°	1016.9	1016.0	1030.7	1036.9	1032.5
147.5°	1045.5	1042.9	1057.7	1062.1	1058.7
150°	1073.4	1067.4	1081.4	1086.5	1082.2
152.5°	1097.0	1090.0	1103.0	1108.3	1102.2
155°	1119.6	1111.9	1122.3	1127.5	1120.5
157.5°	1137.9	1131.0	1138.9	1145.0	1137.9
160°	1153.6	1148.4	1153.6	1158.8	1152.7
162.5°	1167.5	1162.4	1166.7	1172.8	1165.0
165°	1179.8	1174.6	1177.2	1183.2	1177.2
167.5°	1189.4	1184.0	1186.8	1192.9	1185.0
170°	1197.2	1192.0	1193.7	1199.8	1192.0
172.5°	1202.4	1197.2	1199.0	1205.1	1197.2
175°	1206.7	1200.6	1202.4	1208.5	1199.8
177.5°	1208.5	1202.4	1203.3	1209.5	1201.6
180°	1204.2	1204.2	1204.2	1204.2	1204.2



TEST NUMBER: P929214  
 CATALOG NUMBER: DFN2DIP-HX4F0-060D040US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.45	10.33	10.36	11.25	12.44	5.42	6.31	6.33	7.23	8.41
	3H	11.13	11.92	12.05	12.85	14.06	6.62	7.41	7.54	8.34	9.54
	4H	11.74	12.49	12.68	13.43	14.64	7.07	7.82	8.00	8.75	9.97
	6H	12.17	12.85	13.11	13.80	15.02	7.40	8.08	8.34	9.03	10.25
	8H	12.30	12.95	13.25	13.91	15.13	7.49	8.14	8.44	9.10	10.33
	12H	12.36	12.98	13.32	13.93	15.18	7.53	8.16	8.49	9.11	10.36
4H	2H	9.47	10.22	10.41	11.16	12.37	6.02	6.77	6.96	7.71	8.92
	3H	11.31	11.93	12.26	12.90	14.12	7.38	8.00	8.33	8.97	10.20
	4H	12.00	12.57	12.96	13.53	14.78	7.93	8.50	8.89	9.46	10.71
	6H	12.52	13.01	13.49	13.99	15.25	8.36	8.84	9.33	9.83	11.08
	8H	12.70	13.15	13.67	14.13	15.40	8.49	8.94	9.46	9.92	11.19
	12H	12.80	13.21	13.79	14.20	15.47	8.56	8.97	9.55	9.96	11.23
8H	4H	11.98	12.43	12.95	13.41	14.68	8.22	8.67	9.19	9.65	10.92
	6H	12.54	12.92	13.54	13.94	15.21	8.74	9.11	9.74	10.14	11.40
	8H	12.76	13.09	13.77	14.10	15.39	8.93	9.26	9.94	10.27	11.56
	12H	12.90	13.20	13.91	14.20	15.53	9.05	9.35	10.07	10.35	11.68
12H	4H	11.93	12.34	12.92	13.33	14.61	8.22	8.63	9.22	9.63	10.90
	6H	12.52	12.85	13.53	13.86	15.14	8.79	9.12	9.80	10.13	11.41
	8H	12.74	13.04	13.75	14.04	15.37	9.00	9.29	10.01	10.30	11.63