

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929274

Luminaire Tested: DFN2DIP-HX4F0-070D100US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929274
REPORT IS A COMBINATION OF REPORTS P900934 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D100US940-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14138.2 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 142.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929274
CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929274

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38			38
1	95	91	88	84	86	83	80	77	67	65	63	53	52	51	40	39	38	32			32
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28			28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	28	24			24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21			21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18			18
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16			16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15			15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16	13			13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12			12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1919	1919	1919
5°	1922	1889	1901
10°	1903	1852	1839
15°	1877	1791	1743
20°	1843	1707	1626
25°	1807	1612	1513
30°	1760	1515	1369
35°	1713	1411	1243
40°	1666	1303	1098
45°	1611	1184	967
50°	1554	1063	839
55°	1495	934	716
60°	1426	799	590
65°	1347	662	531
70°	1251	534	480
75°	1131	471	437
80°	957	396	379
85°	669	265	286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1611 cd/sqm



TEST NUMBER: P929274

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.9	1.7
10°-20°	664.0	4.7
20°-30°	932.2	6.6
30°-40°	1016.1	7.2
40°-50°	933.9	6.6
50°-60°	733.5	5.2
60°-70°	477.4	3.4
70°-80°	245.7	1.7
80°-90°	68.0	0.5
90°-100°	99.3	0.7
100°-110°	370.0	2.6
110°-120°	981.4	6.9
120°-130°	1627.8	11.5
130°-140°	1729.1	12.2
140°-150°	1607.0	11.4
150°-160°	1292.0	9.1
160°-170°	832.5	5.9
170°-180°	286.5	2.0
0°-30°	1838.0	13.0
0°-40°	2854.1	20.2
0°-60°	4521.5	32.0
0°-90°	5312.7	37.6
90°-120°	1450.7	10.3
90°-150°	6414.5	45.4
90°-180°	8826.0	62.4
0°-180°	14138.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2581	2581	2581	2581	2581	
5°	2581	2569	2538	2560	2553	245
15°	2454	2429	2349	2305	2282	692
25°	2228	2153	1999	1903	1868	1025
35°	1920	1801	1595	1448	1396	1202
45°	1570	1413	1168	1002	946	1212
55°	1193	1011	759	619	575	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	2	26	43	55	59	13
95°	142	70	85	96	94	168
105°	662	728	133	157	166	708
115°	1252	1290	1344	336	179	1233
125°	1771	1799	1841	1856	1862	1579
135°	2192	2226	2246	2268	2263	1693
145°	2542	2540	2577	2592	2581	1590
155°	2799	2780	2806	2819	2801	1290
165°	2949	2936	2943	2958	2943	833
175°	3017	3002	3006	3021	3000	287
180°	3010	3010	3010	3010	3010	



TEST NUMBER: P929274

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2580.6	2580.6	2580.6	2580.6	2580.6
2.5°	2592.2	2580.6	2554.9	2578.4	2573.7
5°	2580.6	2569.0	2538.5	2559.6	2552.6
7.5°	2559.6	2545.7	2513.0	2522.1	2510.5
10°	2531.6	2515.3	2468.6	2461.5	2447.6
12.5°	2496.6	2475.6	2412.4	2398.5	2372.7
15°	2454.5	2428.7	2349.4	2305.1	2281.8
17.5°	2405.5	2368.1	2270.0	2218.6	2181.2
20°	2349.4	2302.6	2185.9	2127.7	2076.1
22.5°	2288.8	2235.0	2099.4	2020.1	1985.2
25°	2228.0	2153.2	1999.1	1903.4	1868.3
27.5°	2155.7	2076.1	1905.7	1796.0	1742.2
30°	2078.6	1989.7	1802.8	1683.9	1620.8
32.5°	2003.8	1896.3	1705.0	1564.7	1506.2
35°	1919.8	1800.6	1595.3	1448.1	1396.5
37.5°	1838.1	1709.4	1492.4	1331.0	1272.9
40°	1751.5	1611.6	1384.8	1219.1	1158.4
42.5°	1662.9	1513.5	1277.5	1104.6	1046.4
45°	1569.5	1412.8	1167.8	1001.8	945.8
47.5°	1480.7	1315.0	1062.7	896.7	845.4
50°	1382.6	1216.9	959.9	798.6	749.8
52.5°	1286.7	1111.5	861.8	707.6	663.3
55°	1193.3	1011.2	758.9	619.0	574.6
57.5°	1097.7	910.8	668.0	537.2	499.8
60°	999.6	812.7	572.1	453.2	415.8
62.5°	903.9	717.1	490.3	378.4	359.7
65°	805.7	616.5	406.4	327.1	319.9
67.5°	712.4	523.1	327.1	287.1	280.3
70°	614.2	432.1	270.8	247.5	238.1
72.5°	520.8	347.9	226.5	207.9	203.2
75°	429.7	266.1	186.8	170.5	168.2
77.5°	338.7	189.0	147.2	137.7	133.1
80°	254.5	135.5	112.0	102.8	102.8
82.5°	177.4	91.2	77.1	72.3	72.3
85°	100.4	51.3	44.3	44.3	44.3
87.5°	37.4	18.6	18.6	16.3	16.3
90°	2.1	26.1	43.4	54.6	58.7
92.5°	54.6	45.8	52.3	56.6	58.7
95°	141.5	69.6	84.8	96.0	93.7
97.5°	254.8	76.3	111.0	117.7	119.8
100°	385.7	87.1	124.2	141.5	145.9
102.5°	529.2	525.1	128.5	152.4	159.0
105°	662.2	727.6	133.0	156.7	165.6
107.5°	816.9	871.2	137.4	161.2	169.9
110°	965.1	1010.6	381.2	163.5	172.0



TEST NUMBER: P929274

CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1104.5	1143.5	1106.6	167.6	174.4
115°	1252.5	1289.5	1344.1	335.5	178.8
117.5°	1381.0	1424.5	1461.7	1150.1	579.4
120°	1524.9	1557.4	1596.8	1622.9	1328.8
122.5°	1646.7	1681.6	1725.3	1738.2	1740.6
125°	1770.9	1799.3	1840.7	1856.0	1862.4
127.5°	1884.2	1914.7	1947.5	1969.3	1971.3
130°	1990.9	2025.9	2049.7	2073.7	2071.7
132.5°	2099.9	2128.3	2152.1	2171.8	2169.7
135°	2191.5	2226.3	2245.8	2267.7	2263.4
137.5°	2287.2	2313.3	2335.3	2357.0	2350.5
140°	2380.7	2398.4	2422.1	2441.8	2431.0
142.5°	2459.4	2474.7	2502.9	2520.2	2509.4
145°	2542.2	2539.9	2576.9	2592.2	2581.3
147.5°	2613.8	2607.4	2644.3	2655.2	2646.7
150°	2683.7	2668.4	2703.4	2716.3	2705.4
152.5°	2742.4	2725.1	2757.7	2770.8	2755.6
155°	2799.1	2779.7	2805.8	2818.7	2801.4
157.5°	2844.9	2827.6	2847.2	2862.4	2844.9
160°	2884.2	2871.0	2884.2	2897.1	2881.9
162.5°	2918.8	2905.9	2916.8	2932.0	2912.4
165°	2949.3	2936.4	2942.9	2958.1	2942.9
167.5°	2973.4	2960.2	2967.0	2982.2	2962.5
170°	2993.0	2979.9	2984.3	2999.5	2979.9
172.5°	3006.0	2993.0	2997.5	3012.7	2993.0
175°	3016.8	3001.6	3006.0	3021.3	2999.5
177.5°	3021.3	3006.0	3008.4	3023.6	3003.9
180°	3010.4	3010.4	3010.4	3010.4	3010.4



TEST NUMBER: P929274
 CATALOG NUMBER: DFN2DIP-HX4F0-070D100US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.13	8.87	9.19	9.93	11.37	4.10	4.84	5.17	5.90	7.34
	3H	9.80	10.46	10.87	11.53	12.99	5.29	5.95	6.36	7.02	8.48
	4H	10.41	11.03	11.49	12.10	13.57	5.73	6.36	6.82	7.43	8.90
	6H	10.82	11.40	11.92	12.47	13.95	6.05	6.63	7.14	7.70	9.18
	8H	10.95	11.49	12.04	12.59	14.06	6.14	6.69	7.24	7.78	9.25
	12H	11.01	11.53	12.11	12.61	14.11	6.18	6.70	7.28	7.79	9.28
4H	2H	8.14	8.76	9.23	9.83	11.30	4.69	5.31	5.78	6.38	7.85
	3H	9.96	10.48	11.06	11.58	13.06	6.03	6.55	7.13	7.65	9.13
	4H	10.65	11.12	11.75	12.21	13.71	6.58	7.05	7.68	8.14	9.64
	6H	11.16	11.57	12.27	12.68	14.17	6.99	7.40	8.10	8.51	10.01
	8H	11.33	11.71	12.44	12.82	14.33	7.12	7.50	8.23	8.61	10.11
	12H	11.42	11.77	12.55	12.89	14.40	7.18	7.53	8.31	8.64	10.16
8H	4H	10.61	10.99	11.72	12.10	13.60	6.85	7.23	7.96	8.34	9.84
	6H	11.17	11.49	12.30	12.63	14.14	7.37	7.68	8.50	8.83	10.33
	8H	11.39	11.67	12.53	12.79	14.32	7.56	7.83	8.70	8.96	10.49
	12H	11.53	11.77	12.67	12.89	14.45	7.68	7.92	8.82	9.04	10.60
12H	4H	10.56	10.90	11.68	12.02	13.53	6.85	7.20	7.98	8.31	9.83
	6H	11.15	11.42	12.29	12.55	14.08	7.42	7.69	8.55	8.82	10.34
	8H	11.37	11.61	12.51	12.73	14.29	7.62	7.87	8.76	8.99	10.55