

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929278

Luminaire Tested: DFN2DIP-HX4F0-070D110US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929278
REPORT IS A COMBINATION OF REPORTS P900952 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D110US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15021.2 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 153.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37
2	87	80	74	69	78	72	67	63	58	55	52	46	44	41	34	33	31
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27
4	73	62	55	49	65	57	50	45	46	42	38	36	33	31	27	25	24
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21
6	61	50	42	37	55	46	39	34	37	32	29	30	26	24	23	20	18
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1919	1919	1919
5°	1922	1889	1901
10°	1903	1852	1839
15°	1877	1791	1743
20°	1843	1707	1626
25°	1807	1612	1513
30°	1760	1515	1369
35°	1713	1411	1243
40°	1666	1303	1098
45°	1611	1184	967
50°	1554	1063	839
55°	1495	934	716
60°	1426	799	590
65°	1347	662	531
70°	1251	534	480
75°	1131	471	437
80°	957	396	379
85°	669	265	286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1701 cd/sqm

TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.9	1.6
10°-20°	664.0	4.4
20°-30°	932.2	6.2
30°-40°	1016.1	6.8
40°-50°	933.9	6.2
50°-60°	733.5	4.9
60°-70°	477.4	3.2
70°-80°	245.7	1.6
80°-90°	68.5	0.5
90°-100°	109.2	0.7
100°-110°	407.0	2.7
110°-120°	1079.6	7.2
120°-130°	1790.5	11.9
130°-140°	1902.0	12.7
140°-150°	1767.7	11.8
150°-160°	1421.2	9.5
160°-170°	915.7	6.1
170°-180°	315.2	2.1
0°-30°	1838.0	12.2
0°-40°	2854.1	19.0
0°-60°	4521.5	30.1
0°-90°	5313.2	35.4
90°-120°	1595.8	10.6
90°-150°	7055.9	47.0
90°-180°	9708.0	64.6
0°-180°	15021.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2581	2581	2581	2581	2581	
5°	2581	2569	2538	2560	2553	245
15°	2454	2429	2349	2305	2282	692
25°	2228	2153	1999	1903	1868	1025
35°	1920	1801	1595	1448	1396	1202
45°	1570	1413	1168	1002	946	1212
55°	1193	1011	759	619	575	1066
65°	806	616	406	327	320	799
75°	430	266	187	170	168	454
85°	100	51	44	44	44	115
90°	2	29	48	60	65	14
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1378	1418	1478	369	197	1356
125°	1948	1979	2025	2042	2049	1737
135°	2411	2449	2470	2495	2490	1862
145°	2796	2794	2834	2851	2839	1749
155°	3079	3058	3086	3101	3082	1419
165°	3244	3230	3237	3254	3237	917
175°	3318	3302	3307	3323	3300	316
180°	3312	3312	3312	3312	3312	

TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2580.6	2580.6	2580.6	2580.6	2580.6
2.5°	2592.2	2580.6	2554.9	2578.4	2573.7
5°	2580.6	2569.0	2538.5	2559.6	2552.6
7.5°	2559.6	2545.7	2513.0	2522.1	2510.5
10°	2531.6	2515.3	2468.6	2461.5	2447.6
12.5°	2496.6	2475.6	2412.4	2398.5	2372.7
15°	2454.5	2428.7	2349.4	2305.1	2281.8
17.5°	2405.5	2368.1	2270.0	2218.6	2181.2
20°	2349.4	2302.6	2185.9	2127.7	2076.1
22.5°	2288.8	2235.0	2099.4	2020.1	1985.2
25°	2228.0	2153.2	1999.1	1903.4	1868.3
27.5°	2155.7	2076.1	1905.7	1796.0	1742.2
30°	2078.6	1989.7	1802.8	1683.9	1620.8
32.5°	2003.8	1896.3	1705.0	1564.7	1506.2
35°	1919.8	1800.6	1595.3	1448.1	1396.5
37.5°	1838.1	1709.4	1492.4	1331.0	1272.9
40°	1751.5	1611.6	1384.8	1219.1	1158.4
42.5°	1662.9	1513.5	1277.5	1104.6	1046.4
45°	1569.5	1412.8	1167.8	1001.8	945.8
47.5°	1480.7	1315.0	1062.7	896.7	845.4
50°	1382.6	1216.9	959.9	798.6	749.8
52.5°	1286.7	1111.5	861.8	707.6	663.3
55°	1193.3	1011.2	758.9	619.0	574.6
57.5°	1097.7	910.8	668.0	537.2	499.8
60°	999.6	812.7	572.1	453.2	415.8
62.5°	903.9	717.1	490.3	378.4	359.7
65°	805.7	616.5	406.4	327.1	319.9
67.5°	712.4	523.1	327.1	287.1	280.3
70°	614.2	432.1	270.8	247.5	238.1
72.5°	520.8	347.9	226.5	207.9	203.2
75°	429.7	266.1	186.8	170.5	168.2
77.5°	338.7	189.0	147.2	137.7	133.1
80°	254.5	135.5	112.0	102.8	102.8
82.5°	177.4	91.2	77.1	72.3	72.3
85°	100.4	51.3	44.3	44.3	44.3
87.5°	37.4	18.6	18.6	16.3	16.3
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.4	64.6
95°	155.7	76.5	93.3	105.5	103.0
97.5°	280.3	83.9	122.0	129.4	131.7
100°	424.2	95.9	136.6	155.7	160.5
102.5°	582.1	577.6	141.4	167.6	175.0
105°	728.4	800.4	146.3	172.4	182.1
107.5°	898.6	958.3	151.1	177.2	187.0
110°	1061.6	1111.7	419.4	179.8	189.2

TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1215.0	1257.9	1217.2	184.4	191.8
115°	1377.7	1418.4	1478.5	369.0	196.6
117.5°	1519.2	1567.0	1607.9	1265.0	637.3
120°	1677.3	1713.2	1756.4	1785.2	1461.6
122.5°	1811.4	1849.7	1897.8	1912.1	1914.7
125°	1947.9	1979.3	2024.8	2041.5	2048.7
127.5°	2072.6	2106.1	2142.2	2166.1	2168.5
130°	2190.0	2228.5	2254.6	2281.1	2278.9
132.5°	2309.8	2341.1	2367.4	2389.0	2386.7
135°	2410.6	2449.0	2470.3	2494.6	2489.7
137.5°	2515.9	2544.6	2568.8	2592.7	2585.6
140°	2618.9	2638.2	2664.4	2686.0	2674.0
142.5°	2705.3	2722.1	2753.2	2772.2	2760.3
145°	2796.4	2793.8	2834.5	2851.4	2839.4
147.5°	2875.3	2868.1	2908.8	2920.8	2911.4
150°	2952.1	2935.3	2973.7	2987.9	2976.0
152.5°	3016.7	2997.6	3033.4	3048.0	3031.2
155°	3079.0	3057.6	3086.3	3100.6	3081.5
157.5°	3129.3	3110.2	3131.9	3148.7	3129.3
160°	3172.6	3158.0	3172.6	3186.8	3170.0
162.5°	3210.7	3196.5	3208.4	3225.2	3203.6
165°	3244.3	3230.0	3237.2	3253.9	3237.2
167.5°	3270.7	3256.2	3263.6	3280.4	3258.8
170°	3292.4	3277.8	3282.6	3299.5	3277.8
172.5°	3306.6	3292.4	3297.2	3314.0	3292.4
175°	3318.5	3301.7	3306.6	3323.4	3299.5
177.5°	3323.4	3306.6	3309.1	3325.9	3304.3
180°	3311.5	3311.5	3311.5	3311.5	3311.5

TEST NUMBER: P929278

CATALOG NUMBER: DFN2DIP-HX4F0-070D110US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.87	8.59	8.95	9.67	11.14	3.84	4.57	4.92	5.64	7.11
	3H	9.54	10.19	10.63	11.27	12.76	5.03	5.67	6.11	6.76	8.24
	4H	10.14	10.76	11.24	11.84	13.34	5.47	6.09	6.57	7.17	8.66
	6H	10.56	11.13	11.67	12.21	13.72	5.79	6.35	6.90	7.44	8.95
	8H	10.69	11.22	11.80	12.33	13.82	5.88	6.41	6.99	7.52	9.02
	12H	10.74	11.25	11.86	12.35	13.87	5.92	6.43	7.03	7.53	9.05
4H	2H	7.88	8.49	8.98	9.57	11.07	4.43	5.04	5.53	6.12	7.62
	3H	9.70	10.21	10.81	11.32	12.82	5.77	6.28	6.88	7.39	8.90
	4H	10.38	10.85	11.50	11.96	13.48	6.31	6.78	7.43	7.88	9.41
	6H	10.90	11.30	12.02	12.42	13.94	6.73	7.13	7.85	8.25	9.77
	8H	11.07	11.44	12.19	12.56	14.09	6.86	7.23	7.98	8.35	9.88
	12H	11.16	11.50	12.30	12.63	14.17	6.92	7.26	8.06	8.39	9.92
8H	4H	10.35	10.72	11.47	11.84	13.37	6.59	6.96	7.71	8.08	9.61
	6H	10.91	11.22	12.05	12.38	13.91	7.10	7.41	8.25	8.57	10.10
	8H	11.13	11.39	12.28	12.53	14.08	7.29	7.56	8.44	8.70	10.25
	12H	11.26	11.50	12.41	12.63	14.22	7.41	7.65	8.56	8.78	10.37
12H	4H	10.29	10.63	11.43	11.76	13.30	6.59	6.93	7.73	8.05	9.59
	6H	10.88	11.15	12.03	12.29	13.84	7.15	7.42	8.30	8.56	10.11
	8H	11.10	11.34	12.25	12.47	14.06	7.36	7.60	8.51	8.73	10.32

END OF REPORT