

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902964

Luminaire Tested: DFN2DIP-PN3F0-030D070US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902964
REPORT IS A COMBINATION OF REPORTS P899567 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D070US830-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8638.4 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	47	35	34	34
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	30	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	28	26	24
4	71	61	53	47	64	55	48	43	44	39	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	55	43	36	30	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1286	1286	1286
5°	1287	1267	1276
10°	1276	1249	1258
15°	1257	1228	1231
20°	1231	1198	1203
25°	1205	1163	1170
30°	1172	1131	1129
35°	1141	1092	1085
40°	1104	1053	1044
45°	1066	1014	1002
50°	1025	973	953
55°	982	926	907
60°	932	870	855
65°	879	811	794
70°	811	740	728
75°	717	655	667
80°	602	546	550
85°	426	361	358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2069 cd/sqm

TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	1.2
10°-20°	291.4	3.4
20°-30°	428.2	5.0
30°-40°	497.3	5.8
40°-50°	496.7	5.8
50°-60°	433.1	5.0
60°-70°	320.2	3.7
70°-80°	181.1	2.1
80°-90°	53.7	0.6
90°-100°	129.1	1.5
100°-110°	410.3	4.7
110°-120°	702.1	8.1
120°-130°	923.3	10.7
130°-140°	1036.4	12.0
140°-150°	1016.3	11.8
150°-160°	852.6	9.9
160°-170°	565.4	6.5
170°-180°	197.6	2.3
0°-30°	823.1	9.5
0°-40°	1320.4	15.3
0°-60°	2250.3	26.0
0°-90°	2805.3	32.5
90°-120°	1241.5	14.4
90°-150°	4217.6	48.8
90°-180°	5833.0	67.5
0°-180°	8638.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1100	1100	1100	1100	1100	
5°	1100	1096	1084	1093	1091	104
15°	1047	1041	1027	1032	1026	295
25°	948	940	922	924	922	436
35°	818	807	790	784	779	511
45°	666	658	642	631	626	514
55°	504	497	485	472	467	450
65°	340	333	323	313	308	336
75°	178	176	170	164	166	190
85°	43	42	41	38	37	48
90°	2	23	62	58	60	8
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1100.2	1100.2	1100.2	1100.2	1100.2
2.5°	1106.6	1101.4	1089.7	1100.2	1098.3
5°	1100.2	1096.1	1084.4	1092.9	1090.8
7.5°	1092.9	1086.6	1074.9	1083.5	1081.3
10°	1081.3	1073.8	1061.2	1069.6	1066.5
12.5°	1065.4	1059.0	1046.4	1051.6	1049.5
15°	1047.4	1041.1	1027.3	1031.5	1026.2
17.5°	1025.1	1018.9	1005.0	1010.3	1005.0
20°	1000.8	994.5	979.7	982.8	978.6
22.5°	976.6	967.0	953.2	953.2	951.0
25°	947.9	939.5	921.5	923.6	921.5
27.5°	916.2	908.7	895.0	891.9	886.6
30°	884.5	876.0	860.2	857.0	852.7
32.5°	850.6	844.3	827.4	821.0	816.7
35°	817.8	807.3	790.3	783.9	778.6
37.5°	780.8	771.3	754.3	746.9	741.6
40°	742.7	734.2	717.3	707.8	703.6
42.5°	705.7	697.2	680.3	669.7	663.4
45°	665.5	658.1	642.2	630.6	626.3
47.5°	626.3	619.0	602.0	590.3	584.0
50°	585.0	579.8	565.0	550.2	544.9
52.5°	544.9	537.4	523.8	512.1	504.6
55°	503.7	497.3	484.6	471.9	466.7
57.5°	462.3	457.0	443.3	430.6	426.3
60°	421.0	416.9	402.1	390.4	387.3
62.5°	380.9	373.4	362.9	352.3	348.1
65°	339.7	333.3	322.7	313.2	307.9
67.5°	297.4	292.0	282.5	275.1	270.9
70°	258.2	253.9	244.4	237.0	232.8
72.5°	218.0	213.7	208.4	201.0	197.9
75°	177.7	175.7	170.3	164.0	166.2
77.5°	141.8	137.5	135.3	132.2	129.1
80°	105.8	104.7	102.5	99.4	97.4
82.5°	71.9	71.9	71.0	66.6	66.6
85°	43.4	42.3	41.3	38.1	37.0
87.5°	19.0	17.0	14.8	11.7	10.6
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P902964

CATALOG NUMBER: DFN2DIP-PN3F0-030D070US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.22	6.94	7.31	8.03	9.53	5.78	6.50	6.87	7.59	9.10
	3H	7.86	8.51	8.96	9.61	11.13	7.38	8.03	8.48	9.13	10.65
	4H	8.44	9.05	9.55	10.16	11.68	7.95	8.57	9.07	9.67	11.19
	6H	8.83	9.39	9.95	10.50	12.03	8.34	8.90	9.46	10.01	11.54
	8H	8.92	9.46	10.05	10.58	12.11	8.43	8.97	9.56	10.09	11.62
	12H	8.97	9.48	10.10	10.59	12.14	8.47	8.98	9.60	10.09	11.65
4H	2H	6.66	7.27	7.78	8.37	9.90	6.31	6.92	7.43	8.02	9.55
	3H	8.50	9.02	9.63	10.15	11.68	8.10	8.62	9.23	9.74	11.28
	4H	9.21	9.68	10.34	10.80	12.35	8.79	9.26	9.92	10.38	11.94
	6H	9.71	10.11	10.85	11.25	12.80	9.29	9.69	10.42	10.83	12.38
	8H	9.85	10.23	10.99	11.36	12.93	9.43	9.80	10.56	10.94	12.50
	12H	9.92	10.26	11.07	11.40	12.97	9.48	9.82	10.63	10.97	12.53
8H	4H	9.39	9.77	10.53	10.90	12.46	9.02	9.40	10.16	10.53	12.09
	6H	10.01	10.32	11.16	11.49	13.05	9.63	9.94	10.79	11.12	12.68
	8H	10.22	10.49	11.39	11.65	13.23	9.84	10.11	11.00	11.27	12.85
	12H	10.34	10.58	11.51	11.73	13.35	9.94	10.18	11.11	11.33	12.95
12H	4H	9.37	9.71	10.52	10.85	12.42	9.01	9.35	10.16	10.49	12.06
	6H	10.03	10.31	11.20	11.46	13.04	9.67	9.94	10.83	11.10	12.68
	8H	10.26	10.50	11.43	11.65	13.27	9.89	10.13	11.06	11.28	12.90

END OF REPORT