

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902974

Luminaire Tested: DFN2DIP-PN3F0-030D090US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902974
REPORT IS A COMBINATION OF REPORTS P899596 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D090US830-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9910.8 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1366	1366	1366
5°	1368	1344	1352
10°	1353	1316	1308
15°	1334	1272	1239
20°	1308	1211	1155
25°	1282	1143	1074
30°	1247	1073	972
35°	1213	998	882
40°	1179	921	778
45°	1138	835	685
50°	1097	749	594
55°	1053	657	506
60°	1002	561	416
65°	944	463	374
70°	873	371	337
75°	784	325	306
80°	657	270	263
85°	445	176	194

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2657 cd/sqm

TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.5	1.1
10°-20°	300.7	3.0
20°-30°	422.1	4.3
30°-40°	460.2	4.6
40°-50°	422.9	4.3
50°-60°	332.2	3.4
60°-70°	216.2	2.2
70°-80°	111.3	1.1
80°-90°	36.0	0.4
90°-100°	166.0	1.7
100°-110°	527.5	5.3
110°-120°	902.7	9.1
120°-130°	1187.2	12.0
130°-140°	1332.5	13.4
140°-150°	1306.7	13.2
150°-160°	1096.1	11.1
160°-170°	726.9	7.3
170°-180°	254.1	2.6
0°-30°	832.3	8.4
0°-40°	1292.5	13.0
0°-60°	2047.6	20.7
0°-90°	2411.1	24.3
90°-120°	1596.2	16.1
90°-150°	5422.6	54.7
90°-180°	7500.0	75.7
0°-180°	9910.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1169	1169	1169	1169	1169	
5°	1169	1163	1150	1159	1156	111
15°	1112	1100	1064	1044	1033	313
25°	1009	975	905	862	846	464
35°	869	815	722	656	632	544
45°	711	640	529	454	428	549
55°	540	458	344	280	260	483
65°	365	279	184	148	145	362
75°	194	121	85	77	76	206
85°	45	23	20	20	20	52
90°	2	29	79	74	77	10
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2380	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2667	2683	2669	254
180°	2683	2683	2683	2683	2683	

TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.7	1168.7	1168.7	1168.7	1168.7
2.5°	1173.9	1168.7	1157.0	1167.6	1165.5
5°	1168.7	1163.4	1149.6	1159.1	1155.9
7.5°	1159.1	1152.8	1138.0	1142.2	1136.9
10°	1146.4	1139.1	1117.9	1114.7	1108.4
12.5°	1130.6	1121.1	1092.5	1086.2	1074.5
15°	1111.5	1099.9	1063.9	1043.9	1033.3
17.5°	1089.3	1072.4	1027.9	1004.8	987.8
20°	1063.9	1042.7	989.9	963.6	940.2
22.5°	1036.5	1012.1	950.7	914.8	899.0
25°	1009.0	975.1	905.3	862.0	846.0
27.5°	976.2	940.2	863.0	813.3	788.9
30°	941.3	901.1	816.4	762.6	734.0
32.5°	907.4	858.8	772.1	708.6	682.1
35°	869.4	815.4	722.4	655.7	632.4
37.5°	832.4	774.1	675.8	602.8	576.5
40°	793.2	729.8	627.2	552.0	524.6
42.5°	753.0	685.4	578.5	500.2	473.8
45°	710.8	639.8	528.9	453.6	428.3
47.5°	670.5	595.5	481.3	406.0	382.9
50°	626.1	551.0	434.7	361.7	339.5
52.5°	582.7	503.4	390.3	320.5	300.4
55°	540.4	457.9	343.7	280.3	260.2
57.5°	497.1	412.5	302.6	243.3	226.3
60°	452.6	368.1	259.1	205.2	188.3
62.5°	409.3	324.7	222.1	171.4	163.0
65°	364.9	279.2	184.0	148.1	144.9
67.5°	322.6	236.9	148.1	130.1	126.9
70°	278.1	195.7	122.6	112.1	107.8
72.5°	235.8	157.5	102.5	94.2	92.0
75°	194.5	120.6	84.6	77.2	76.2
77.5°	153.4	85.6	66.6	62.4	60.2
80°	115.3	61.4	50.7	46.6	46.6
82.5°	80.3	41.3	34.9	32.8	32.8
85°	45.4	23.2	20.1	20.1	20.1
87.5°	17.0	8.4	8.4	7.4	7.4
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.8	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2

TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.9	918.8	914.7	912.4	905.9
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.3
122.5°	1215.6	1238.3	1227.0	1220.5	1215.6
125°	1317.6	1337.8	1331.3	1324.0	1321.6
127.5°	1417.0	1442.1	1433.2	1423.5	1417.0
130°	1510.0	1539.2	1535.1	1530.2	1521.4
132.5°	1614.4	1637.0	1638.6	1627.3	1620.9
135°	1704.1	1729.2	1734.1	1731.6	1725.2
137.5°	1804.4	1824.7	1828.7	1827.1	1817.4
140°	1892.6	1912.8	1924.1	1924.1	1915.2
142.5°	1983.2	2003.4	2009.9	2012.3	2003.4
145°	2069.0	2085.1	2098.0	2100.5	2091.6
147.5°	2145.8	2166.0	2175.7	2179.7	2170.9
150°	2225.1	2238.8	2247.7	2254.9	2247.7
152.5°	2295.4	2309.1	2320.4	2329.4	2320.4
155°	2365.8	2372.2	2379.5	2390.9	2383.6
157.5°	2426.4	2431.3	2435.3	2451.5	2440.1
160°	2480.6	2485.5	2487.9	2501.6	2491.9
162.5°	2530.7	2530.7	2533.2	2548.5	2537.2
165°	2573.6	2571.2	2571.2	2587.4	2576.1
167.5°	2612.4	2605.2	2605.2	2621.3	2610.0
170°	2641.6	2635.1	2632.7	2648.8	2635.1
172.5°	2661.7	2655.3	2652.9	2669.1	2655.3
175°	2678.0	2671.4	2666.6	2682.9	2669.1
177.5°	2686.8	2680.4	2675.5	2689.3	2675.5
180°	2682.9	2682.9	2682.9	2682.9	2682.9

TEST NUMBER: P902974

CATALOG NUMBER: DFN2DIP-PN3F0-030D090US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.11	5.76	6.26	6.90	8.50	1.07	1.73	2.23	2.87	4.47
	3H	6.77	7.35	7.93	8.50	10.11	2.24	2.83	3.40	3.98	5.59
	4H	7.36	7.92	8.53	9.07	10.68	2.68	3.24	3.85	4.39	6.00
	6H	7.77	8.28	8.95	9.43	11.06	2.99	3.50	4.17	4.65	6.28
	8H	7.89	8.38	9.07	9.54	11.16	3.07	3.56	4.25	4.72	6.34
	12H	7.94	8.40	9.12	9.56	11.20	3.11	3.57	4.29	4.73	6.37
4H	2H	5.10	5.66	6.28	6.81	8.42	1.64	2.20	2.82	3.35	4.97
	3H	6.91	7.37	8.09	8.55	10.17	2.97	3.44	4.15	4.61	6.24
	4H	7.59	8.02	8.77	9.18	10.83	3.51	3.94	4.69	5.10	6.74
	6H	8.09	8.45	9.28	9.64	11.28	3.91	4.28	5.10	5.46	7.10
	8H	8.26	8.60	9.44	9.77	11.43	4.03	4.37	5.22	5.55	7.20
	12H	8.34	8.65	9.54	9.84	11.49	4.09	4.40	5.29	5.58	7.24
8H	4H	7.54	7.88	8.73	9.06	10.71	3.77	4.11	4.96	5.29	6.94
	6H	8.10	8.38	9.30	9.59	11.24	4.27	4.56	5.48	5.77	7.42
	8H	8.31	8.55	9.52	9.75	11.42	4.46	4.71	5.67	5.90	7.57
	12H	8.43	8.65	9.65	9.84	11.54	4.57	4.78	5.78	5.97	7.68
12H	4H	7.49	7.80	8.69	8.98	10.64	3.77	4.08	4.97	5.26	6.92
	6H	8.07	8.31	9.28	9.51	11.18	4.32	4.57	5.53	5.76	7.43
	8H	8.28	8.49	9.49	9.68	11.39	4.52	4.73	5.73	5.93	7.63

END OF REPORT