

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929348

Luminaire Tested: DFN2DIP-HX4F0-090D110US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929348
REPORT IS A COMBINATION OF REPORTS P900955 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D110US940-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17661.6 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52
1	97	92	89	85	88	85	82	79	71	68	66	58	56	54	46	45	44
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	52	44	39	43	38	34	36	32	29	29	26	23
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2323	2323	2323
5°	2327	2291	2306
10°	2308	2260	2275
15°	2274	2223	2226
20°	2229	2171	2176
25°	2183	2110	2119
30°	2126	2053	2045
35°	2072	1985	1968
40°	2006	1917	1894
45°	1939	1848	1819
50°	1867	1776	1731
55°	1791	1693	1651
60°	1705	1595	1559
65°	1612	1493	1450
70°	1493	1368	1334
75°	1328	1219	1226
80°	1130	1029	1020
85°	820	702	678

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1939 cd/sqm

TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.0	1.7
10°-20°	827.2	4.7
20°-30°	1215.7	6.9
30°-40°	1412.0	8.0
40°-50°	1410.2	8.0
50°-60°	1229.7	7.0
60°-70°	909.0	5.1
70°-80°	514.3	2.9
80°-90°	141.6	0.8
90°-100°	109.2	0.6
100°-110°	407.0	2.3
110°-120°	1079.6	6.1
120°-130°	1790.5	10.1
130°-140°	1902.0	10.8
140°-150°	1767.7	10.0
150°-160°	1421.2	8.0
160°-170°	915.7	5.2
170°-180°	315.2	1.8
0°-30°	2336.9	13.2
0°-40°	3748.9	21.2
0°-60°	6388.7	36.2
0°-90°	7953.6	45.0
90°-120°	1595.8	9.0
90°-150°	7055.9	40.0
90°-180°	9708.0	55.0
0°-180°	17661.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3112	3079	3103	3097	297
15°	2974	2956	2917	2929	2914	837
25°	2691	2667	2616	2622	2616	1238
35°	2322	2292	2244	2226	2211	1450
45°	1889	1868	1823	1790	1778	1458
55°	1430	1412	1376	1340	1325	1278
65°	964	946	916	889	874	953
75°	504	499	484	466	472	539
85°	123	120	117	108	105	137
90°	2	29	48	60	65	16
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1378	1418	1478	369	197	1356
125°	1948	1979	2025	2042	2049	1737
135°	2411	2449	2470	2495	2490	1862
145°	2796	2794	2834	2851	2839	1749
155°	3079	3058	3086	3101	3082	1419
165°	3244	3230	3237	3254	3237	917
175°	3318	3302	3307	3323	3300	316
180°	3312	3312	3312	3312	3312	

TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3123.7	3123.7	3123.7	3123.7	3123.7
2.5°	3141.9	3126.9	3093.8	3123.7	3118.0
5°	3123.7	3111.9	3078.8	3102.7	3096.9
7.5°	3102.7	3084.9	3051.7	3076.0	3069.9
10°	3069.9	3048.9	3012.8	3036.7	3027.8
12.5°	3024.6	3006.8	2970.8	2985.7	2979.7
15°	2973.7	2955.8	2916.6	2928.7	2913.7
17.5°	2910.5	2892.7	2853.5	2868.5	2853.5
20°	2841.4	2823.5	2781.4	2790.4	2778.6
22.5°	2772.5	2745.5	2706.2	2706.2	2700.2
25°	2691.3	2667.3	2616.4	2622.1	2616.4
27.5°	2601.1	2580.0	2541.2	2532.3	2517.3
30°	2511.2	2487.0	2442.0	2433.1	2421.1
32.5°	2415.0	2397.2	2349.0	2330.9	2318.8
35°	2322.0	2292.0	2243.8	2225.7	2210.7
37.5°	2216.8	2189.7	2141.5	2120.6	2105.6
40°	2108.7	2084.5	2036.3	2009.6	1997.5
42.5°	2003.5	1979.3	1931.5	1901.3	1883.5
45°	1889.4	1868.5	1823.2	1790.3	1778.3
47.5°	1778.3	1757.2	1709.1	1676.0	1658.1
50°	1661.0	1646.0	1603.9	1561.9	1546.9
52.5°	1546.9	1525.9	1487.0	1453.9	1432.8
55°	1430.0	1411.8	1375.7	1339.8	1324.8
57.5°	1312.7	1297.7	1258.5	1222.5	1210.4
60°	1195.4	1183.6	1141.5	1108.4	1099.5
62.5°	1081.3	1060.2	1030.3	1000.4	988.2
65°	964.3	946.1	916.2	889.1	874.2
67.5°	844.2	828.9	802.1	781.1	769.0
70°	733.0	720.8	693.8	672.7	661.0
72.5°	618.9	606.7	591.8	570.8	561.9
75°	504.5	498.7	483.5	465.6	471.7
77.5°	402.5	390.4	384.4	375.4	366.5
80°	300.5	297.3	291.2	282.3	276.3
82.5°	204.3	204.3	201.4	189.3	189.3
85°	123.0	120.2	117.3	108.0	105.2
87.5°	54.1	48.1	42.1	33.2	30.0
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.4	64.6
95°	155.7	76.5	93.3	105.5	103.0
97.5°	280.3	83.9	122.0	129.4	131.7
100°	424.2	95.9	136.6	155.7	160.5
102.5°	582.1	577.6	141.4	167.6	175.0
105°	728.4	800.4	146.3	172.4	182.1
107.5°	898.6	958.3	151.1	177.2	187.0
110°	1061.6	1111.7	419.4	179.8	189.2

TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1215.0	1257.9	1217.2	184.4	191.8
115°	1377.7	1418.4	1478.5	369.0	196.6
117.5°	1519.2	1567.0	1607.9	1265.0	637.3
120°	1677.3	1713.2	1756.4	1785.2	1461.6
122.5°	1811.4	1849.7	1897.8	1912.1	1914.7
125°	1947.9	1979.3	2024.8	2041.5	2048.7
127.5°	2072.6	2106.1	2142.2	2166.1	2168.5
130°	2190.0	2228.5	2254.6	2281.1	2278.9
132.5°	2309.8	2341.1	2367.4	2389.0	2386.7
135°	2410.6	2449.0	2470.3	2494.6	2489.7
137.5°	2515.9	2544.6	2568.8	2592.7	2585.6
140°	2618.9	2638.2	2664.4	2686.0	2674.0
142.5°	2705.3	2722.1	2753.2	2772.2	2760.3
145°	2796.4	2793.8	2834.5	2851.4	2839.4
147.5°	2875.3	2868.1	2908.8	2920.8	2911.4
150°	2952.1	2935.3	2973.7	2987.9	2976.0
152.5°	3016.7	2997.6	3033.4	3048.0	3031.2
155°	3079.0	3057.6	3086.3	3100.6	3081.5
157.5°	3129.3	3110.2	3131.9	3148.7	3129.3
160°	3172.6	3158.0	3172.6	3186.8	3170.0
162.5°	3210.7	3196.5	3208.4	3225.2	3203.6
165°	3244.3	3230.0	3237.2	3253.9	3237.2
167.5°	3270.7	3256.2	3263.6	3280.4	3258.8
170°	3292.4	3277.8	3282.6	3299.5	3277.8
172.5°	3306.6	3292.4	3297.2	3314.0	3292.4
175°	3318.5	3301.7	3306.6	3323.4	3299.5
177.5°	3323.4	3306.6	3309.1	3325.9	3304.3
180°	3311.5	3311.5	3311.5	3311.5	3311.5

TEST NUMBER: P929348

CATALOG NUMBER: DFN2DIP-HX4F0-090D110US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.72	10.54	10.72	11.55	12.89	9.29	10.11	10.29	11.12	12.46
	3H	11.38	12.12	12.39	13.13	14.49	10.91	11.64	11.92	12.66	14.02
	4H	11.97	12.66	12.99	13.68	15.05	11.49	12.19	12.52	13.21	14.58
	6H	12.37	13.01	13.40	14.03	15.41	11.89	12.53	12.92	13.56	14.94
	8H	12.47	13.08	13.51	14.12	15.50	11.99	12.60	13.03	13.65	15.02
	12H	12.52	13.10	13.56	14.13	15.53	12.04	12.62	13.08	13.65	15.05
4H	2H	10.18	10.88	11.21	11.90	13.27	9.84	10.53	10.86	11.55	12.92
	3H	12.04	12.62	13.08	13.67	15.06	11.65	12.23	12.69	13.28	14.66
	4H	12.76	13.29	13.80	14.33	15.73	12.35	12.88	13.39	13.92	15.33
	6H	13.27	13.73	14.32	14.79	16.19	12.86	13.32	13.91	14.38	15.78
	8H	13.42	13.85	14.47	14.90	16.32	13.01	13.43	14.06	14.49	15.91
	12H	13.49	13.88	14.56	14.95	16.37	13.07	13.45	14.14	14.53	15.95
8H	4H	12.95	13.38	14.01	14.44	15.85	12.59	13.02	13.64	14.07	15.49
	6H	13.58	13.93	14.66	15.03	16.45	13.22	13.57	14.30	14.67	16.08
	8H	13.80	14.11	14.89	15.20	16.63	13.43	13.74	14.52	14.83	16.26
	12H	13.93	14.21	15.02	15.28	16.76	13.55	13.82	14.64	14.90	16.37
12H	4H	12.93	13.32	14.01	14.39	15.81	12.58	12.97	13.65	14.04	15.46
	6H	13.61	13.92	14.70	15.00	16.44	13.26	13.57	14.34	14.65	16.08
	8H	13.85	14.13	14.94	15.20	16.68	13.49	13.77	14.58	14.85	16.32