

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929356

Luminaire Tested: DFN2DIP-HX4F0-100D040US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929356
REPORT IS A COMBINATION OF REPORTS P900831 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D040US940-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12363.1 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 129.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	98	94	90	97	93	90	86	84	81	78	75	73	71	67	66	64
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	44	52	45	40	47	42	38	42	38	35
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	31
7	61	49	40	35	58	47	39	34	42	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	35	30	26	32	28	24
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2581	2581	2581
5°	2585	2545	2562
10°	2564	2511	2528
15°	2527	2470	2473
20°	2476	2413	2418
25°	2426	2344	2354
30°	2362	2281	2273
35°	2302	2205	2186
40°	2229	2130	2104
45°	2155	2054	2021
50°	2074	1974	1924
55°	1990	1881	1834
60°	1895	1772	1732
65°	1791	1659	1611
70°	1659	1520	1482
75°	1476	1355	1362
80°	1256	1144	1133
85°	911	780	754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2155 cd/sqm

TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.7	2.6
10°-20°	919.1	7.4
20°-30°	1350.8	10.9
30°-40°	1568.8	12.7
40°-50°	1566.9	12.7
50°-60°	1366.3	11.1
60°-70°	1010.0	8.2
70°-80°	571.4	4.6
80°-90°	152.9	1.2
90°-100°	39.7	0.3
100°-110°	148.0	1.2
110°-120°	392.6	3.2
120°-130°	651.1	5.3
130°-140°	691.6	5.6
140°-150°	642.8	5.2
150°-160°	516.8	4.2
160°-170°	333.0	2.7
170°-180°	114.6	0.9
0°-30°	2596.6	21.0
0°-40°	4165.4	33.7
0°-60°	7098.5	57.4
0°-90°	8832.9	71.4
90°-120°	580.3	4.7
90°-150°	2565.8	20.8
90°-180°	3530.0	28.6
0°-180°	12363.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3471	3471	3471	3471	3471	
5°	3471	3458	3421	3448	3441	329
15°	3304	3284	3241	3254	3238	931
25°	2990	2964	2907	2914	2907	1376
35°	2580	2547	2493	2473	2456	1611
45°	2099	2076	2026	1989	1976	1620
55°	1589	1569	1529	1489	1472	1420
65°	1072	1051	1018	988	971	1059
75°	560	554	537	517	524	598
85°	137	134	130	120	117	152
90°	1	10	17	22	24	11
95°	57	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	538	134	72	493
125°	708	720	736	742	745	632
135°	877	891	898	907	905	677
145°	1017	1016	1031	1037	1032	636
155°	1120	1112	1122	1128	1120	516
165°	1180	1175	1177	1183	1177	333
175°	1207	1201	1202	1208	1200	115
180°	1204	1204	1204	1204	1204	

TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3470.9	3470.9	3470.9	3470.9	3470.9
2.5°	3491.0	3474.3	3437.5	3470.9	3464.4
5°	3470.9	3457.7	3420.9	3447.5	3441.1
7.5°	3447.5	3427.6	3390.8	3417.7	3411.0
10°	3411.0	3387.6	3347.6	3374.2	3364.3
12.5°	3360.7	3340.9	3300.8	3317.5	3310.7
15°	3304.1	3284.3	3240.6	3254.1	3237.5
17.5°	3233.9	3214.1	3170.5	3187.2	3170.5
20°	3157.1	3137.3	3090.5	3100.4	3087.3
22.5°	3080.6	3050.6	3006.9	3006.9	3000.2
25°	2990.3	2963.8	2907.1	2913.5	2907.1
27.5°	2890.1	2866.7	2823.5	2813.6	2797.0
30°	2790.3	2763.3	2713.4	2703.5	2690.0
32.5°	2683.3	2663.5	2610.0	2589.8	2576.4
35°	2579.9	2546.7	2493.1	2473.0	2456.3
37.5°	2463.1	2432.9	2379.5	2356.1	2339.4
40°	2343.0	2316.1	2262.6	2232.9	2219.5
42.5°	2226.2	2199.2	2146.2	2112.5	2092.7
45°	2099.4	2076.0	2025.7	1989.2	1975.9
47.5°	1975.9	1952.5	1899.0	1862.1	1842.3
50°	1845.5	1828.9	1782.1	1735.4	1718.8
52.5°	1718.8	1695.4	1652.2	1615.4	1592.0
55°	1588.8	1568.7	1528.6	1488.6	1472.0
57.5°	1458.5	1441.8	1398.3	1358.3	1344.9
60°	1328.2	1315.1	1268.3	1231.5	1221.6
62.5°	1201.4	1178.1	1144.8	1111.5	1098.1
65°	1071.5	1051.3	1018.0	987.9	971.3
67.5°	938.0	921.0	891.3	867.9	854.4
70°	814.4	800.9	770.9	747.5	734.4
72.5°	687.6	674.2	657.6	634.2	624.2
75°	560.5	554.2	537.2	517.4	524.0
77.5°	447.2	433.8	427.0	417.1	407.2
80°	333.9	330.4	323.6	313.7	307.0
82.5°	227.0	227.0	223.8	210.3	210.3
85°	136.7	133.5	130.3	120.1	116.9
87.5°	60.2	53.4	46.7	36.8	33.3
90°	0.8	10.4	17.4	21.9	23.5
92.5°	21.9	18.3	20.9	22.7	23.5
95°	56.6	27.8	33.9	38.4	37.5
97.5°	102.0	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.6	58.3
102.5°	211.7	210.1	51.4	60.9	63.6
105°	264.8	291.1	53.2	62.7	66.2
107.5°	326.7	348.5	54.9	64.5	68.0
110°	386.1	404.3	152.5	65.4	68.8



TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.8	457.4	442.6	67.1	69.8
115°	500.9	515.8	537.6	134.2	71.5
117.5°	552.4	569.8	584.7	460.0	231.7
120°	609.9	623.0	638.7	649.2	531.5
122.5°	658.7	672.7	690.1	695.3	696.2
125°	708.3	719.8	736.3	742.4	745.0
127.5°	753.7	765.9	779.0	787.7	788.5
130°	796.4	810.4	819.8	829.5	828.7
132.5°	839.9	851.3	860.9	868.7	867.9
135°	876.6	890.6	898.3	907.1	905.4
137.5°	914.8	925.3	934.1	942.8	940.2
140°	952.3	959.3	968.9	976.7	972.4
142.5°	983.8	989.9	1001.2	1008.0	1003.8
145°	1016.9	1016.0	1030.7	1036.9	1032.5
147.5°	1045.5	1042.9	1057.7	1062.1	1058.7
150°	1073.4	1067.4	1081.4	1086.5	1082.2
152.5°	1097.0	1090.0	1103.0	1108.3	1102.2
155°	1119.6	1111.9	1122.3	1127.5	1120.5
157.5°	1137.9	1131.0	1138.9	1145.0	1137.9
160°	1153.6	1148.4	1153.6	1158.8	1152.7
162.5°	1167.5	1162.4	1166.7	1172.8	1165.0
165°	1179.8	1174.6	1177.2	1183.2	1177.2
167.5°	1189.4	1184.0	1186.8	1192.9	1185.0
170°	1197.2	1192.0	1193.7	1199.8	1192.0
172.5°	1202.4	1197.2	1199.0	1205.1	1197.2
175°	1206.7	1200.6	1202.4	1208.5	1199.8
177.5°	1208.5	1202.4	1203.3	1209.5	1201.6
180°	1204.2	1204.2	1204.2	1204.2	1204.2

TEST NUMBER: P929356

CATALOG NUMBER: DFN2DIP-HX4F0-100D040US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.35	13.44	13.09	14.21	15.14	11.91	13.01	12.66	13.78	14.71
	3H	14.02	15.01	14.79	15.79	16.75	13.55	14.53	14.31	15.31	16.27
	4H	14.62	15.55	15.40	16.34	17.31	14.15	15.08	14.93	15.87	16.84
	6H	15.04	15.89	15.83	16.69	17.67	14.56	15.42	15.35	16.21	17.20
	8H	15.15	15.96	15.95	16.78	17.77	14.67	15.49	15.47	16.30	17.29
	12H	15.20	15.98	16.01	16.79	17.80	14.72	15.50	15.53	16.31	17.32
4H	2H	12.84	13.76	13.62	14.55	15.52	12.49	13.42	13.27	14.21	15.18
	3H	14.72	15.50	15.52	16.32	17.31	14.33	15.11	15.13	15.93	16.92
	4H	15.45	16.15	16.26	16.98	17.99	15.04	15.75	15.85	16.57	17.59
	6H	15.98	16.59	16.80	17.44	18.46	15.57	16.18	16.39	17.03	18.05
	8H	16.13	16.70	16.96	17.55	18.58	15.72	16.29	16.55	17.13	18.17
	12H	16.22	16.73	17.07	17.60	18.63	15.80	16.31	16.65	17.17	18.21
8H	4H	15.66	16.23	16.49	17.08	18.11	15.30	15.87	16.13	16.72	17.75
	6H	16.31	16.78	17.17	17.66	18.70	15.94	16.42	16.80	17.30	18.33
	8H	16.53	16.95	17.40	17.83	18.88	16.16	16.58	17.03	17.46	18.51
	12H	16.67	17.04	17.55	17.91	19.02	16.29	16.66	17.16	17.53	18.64
12H	4H	15.66	16.17	16.51	17.04	18.08	15.31	15.82	16.16	16.69	17.72
	6H	16.34	16.76	17.21	17.64	18.69	15.99	16.41	16.86	17.29	18.34
	8H	16.59	16.96	17.47	17.83	18.94	16.24	16.61	17.11	17.48	18.58

END OF REPORT