

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929366

Luminaire Tested: DFN2DIP-HX4F0-100D060US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929366
REPORT IS A COMBINATION OF REPORTS P900868 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D060US940-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12880.4 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 143.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929366
CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P929366
 CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59		
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51		
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43		
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37		
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33		
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29		
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26		
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23		
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21		
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19		
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2741	2741	2741
5°	2746	2698	2715
10°	2719	2645	2627
15°	2682	2558	2490
20°	2632	2438	2323
25°	2582	2303	2161
30°	2514	2165	1956
35°	2448	2016	1776
40°	2380	1862	1569
45°	2301	1691	1382
50°	2220	1519	1199
55°	2135	1334	1023
60°	2037	1142	842
65°	1924	946	758
70°	1788	763	686
75°	1616	673	625
80°	1367	566	542
85°	955	379	408

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2301 cd/sqm



TEST NUMBER: P929366

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.5	2.7
10°-20°	948.5	7.4
20°-30°	1331.7	10.3
30°-40°	1451.6	11.3
40°-50°	1334.2	10.4
50°-60°	1047.8	8.1
60°-70°	682.0	5.3
70°-80°	351.1	2.7
80°-90°	92.8	0.7
90°-100°	59.5	0.5
100°-110°	222.0	1.7
110°-120°	588.9	4.6
120°-130°	976.7	7.6
130°-140°	1037.4	8.1
140°-150°	964.2	7.5
150°-160°	775.2	6.0
160°-170°	499.5	3.9
170°-180°	171.9	1.3
0°-30°	2625.7	20.4
0°-40°	4077.3	31.7
0°-60°	6459.3	50.1
0°-90°	7585.1	58.9
90°-120°	870.4	6.8
90°-150°	3848.7	29.9
90°-180°	5295.0	41.1
0°-180°	12880.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3687	3687	3687	3687	3687	
5°	3687	3670	3626	3657	3647	350
15°	3506	3470	3356	3293	3260	988
25°	3183	3076	2856	2719	2669	1464
35°	2742	2572	2279	2069	1995	1717
45°	2242	2018	1668	1431	1351	1731
55°	1705	1445	1084	884	821	1523
65°	1151	881	580	467	457	1141
75°	614	380	267	244	240	649
85°	143	73	63	63	63	165
90°	1	16	26	33	35	12
95°	85	42	51	58	56	101
105°	397	436	80	94	99	425
115°	752	774	806	201	107	740
125°	1063	1080	1104	1114	1117	948
135°	1315	1336	1348	1361	1358	1016
145°	1525	1524	1546	1555	1549	954
155°	1680	1668	1684	1691	1681	774
165°	1770	1762	1766	1775	1766	500
175°	1810	1801	1804	1813	1800	172
180°	1806	1806	1806	1806	1806	



TEST NUMBER: P929366

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3686.6	3686.6	3686.6	3686.6	3686.6
2.5°	3703.2	3686.6	3649.8	3683.4	3676.7
5°	3686.6	3670.0	3626.4	3656.6	3646.6
7.5°	3656.6	3636.7	3589.9	3603.1	3586.5
10°	3616.5	3593.2	3526.6	3516.4	3496.6
12.5°	3566.7	3536.5	3446.2	3426.4	3389.6
15°	3506.5	3469.6	3356.3	3293.0	3259.7
17.5°	3436.3	3382.9	3242.8	3169.5	3116.0
20°	3356.3	3289.4	3122.7	3039.6	2965.9
22.5°	3269.6	3192.8	2999.2	2886.0	2836.0
25°	3182.9	3076.1	2855.8	2719.2	2669.0
27.5°	3079.5	2965.9	2722.4	2565.6	2488.8
30°	2969.5	2842.4	2575.5	2405.6	2315.4
32.5°	2862.6	2708.9	2435.7	2235.4	2151.8
35°	2742.5	2572.3	2278.9	2068.6	1995.0
37.5°	2625.8	2442.0	2132.0	1901.6	1818.3
40°	2502.2	2302.3	1978.4	1741.5	1654.8
42.5°	2375.5	2162.0	1825.1	1578.0	1494.8
45°	2242.0	2018.3	1668.3	1431.1	1351.1
47.5°	2115.4	1878.6	1518.2	1281.0	1207.8
50°	1975.2	1738.3	1371.3	1140.9	1071.1
52.5°	1838.1	1587.9	1231.1	1010.9	947.6
55°	1704.7	1444.6	1084.2	884.2	820.8
57.5°	1568.1	1301.2	954.4	767.4	714.0
60°	1427.9	1161.0	817.3	647.4	594.0
62.5°	1291.3	1024.4	700.5	540.6	514.0
65°	1151.1	880.7	580.5	467.2	457.0
67.5°	1017.7	747.2	467.2	410.2	400.3
70°	877.5	617.4	386.9	353.6	340.2
72.5°	744.0	496.9	323.5	296.9	290.3
75°	613.8	380.2	266.9	243.5	240.3
77.5°	483.9	270.1	210.2	196.8	190.1
80°	363.5	193.7	160.0	146.9	146.9
82.5°	253.4	130.2	110.1	103.4	103.4
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.9	45.8	66.5	70.6	71.9
100°	231.4	52.3	74.5	84.9	87.5
102.5°	317.6	315.1	77.2	91.4	95.4
105°	397.3	436.5	79.7	94.0	99.4
107.5°	490.2	522.7	82.4	96.7	102.0
110°	579.1	606.4	228.8	98.1	103.2



TEST NUMBER: P929366

CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.7	686.1	663.9	100.5	104.6
115°	751.5	773.7	806.5	201.3	107.2
117.5°	828.6	854.7	877.0	690.1	347.6
120°	914.9	934.5	958.1	973.7	797.3
122.5°	988.0	1008.9	1035.2	1042.9	1044.4
125°	1062.6	1079.6	1104.4	1113.6	1117.4
127.5°	1130.5	1148.8	1168.5	1181.5	1182.8
130°	1194.6	1215.5	1229.8	1244.3	1243.0
132.5°	1260.0	1277.0	1291.3	1303.0	1301.8
135°	1314.9	1335.9	1347.5	1360.7	1358.0
137.5°	1372.3	1388.0	1401.2	1414.2	1410.3
140°	1428.4	1439.1	1453.3	1465.1	1458.6
142.5°	1475.6	1484.8	1501.8	1512.1	1505.6
145°	1525.3	1523.9	1546.1	1555.3	1548.8
147.5°	1568.3	1564.4	1586.6	1593.1	1588.0
150°	1610.2	1601.1	1622.0	1629.8	1623.3
152.5°	1645.5	1635.0	1654.6	1662.5	1653.3
155°	1679.5	1667.8	1683.5	1691.2	1680.8
157.5°	1706.9	1696.5	1708.3	1717.5	1706.9
160°	1730.5	1722.5	1730.5	1738.2	1729.1
162.5°	1751.3	1743.5	1750.0	1759.2	1747.4
165°	1769.6	1761.9	1765.7	1774.9	1765.7
167.5°	1784.0	1776.2	1780.2	1789.4	1777.5
170°	1795.9	1787.9	1790.6	1799.7	1787.9
172.5°	1803.6	1795.9	1798.5	1807.6	1795.9
175°	1810.1	1800.9	1803.6	1812.7	1799.7
177.5°	1812.7	1803.6	1805.0	1814.1	1802.4
180°	1806.2	1806.2	1806.2	1806.2	1806.2



TEST NUMBER: P929366
 CATALOG NUMBER: DFN2DIP-HX4F0-100D060US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.44	12.35	12.33	13.25	14.39	7.42	8.32	8.30	9.22	10.37
	3H	13.13	13.94	14.02	14.85	16.02	8.61	9.43	9.51	10.33	11.50
	4H	13.74	14.51	14.65	15.42	16.60	9.07	9.83	9.98	10.75	11.93
	6H	14.17	14.87	15.09	15.79	16.98	9.39	10.10	10.32	11.02	12.21
	8H	14.30	14.97	15.23	15.91	17.09	9.49	10.16	10.42	11.10	12.29
	12H	14.36	15.00	15.30	15.93	17.14	9.54	10.17	10.47	11.11	12.32
4H	2H	11.47	12.24	12.39	13.15	14.33	8.02	8.79	8.94	9.70	10.88
	3H	13.31	13.95	14.24	14.89	16.08	9.38	10.02	10.31	10.96	12.15
	4H	14.01	14.59	14.94	15.53	16.74	9.93	10.51	10.87	11.45	12.67
	6H	14.53	15.03	15.48	15.99	17.21	10.36	10.86	11.31	11.82	13.04
	8H	14.70	15.17	15.66	16.13	17.36	10.49	10.96	11.44	11.92	13.15
	12H	14.80	15.22	15.77	16.20	17.43	10.56	10.98	11.53	11.96	13.19
8H	4H	13.98	14.45	14.93	15.40	16.63	10.22	10.69	11.17	11.64	12.88
	6H	14.55	14.93	15.53	15.93	17.16	10.74	11.13	11.72	12.13	13.36
	8H	14.77	15.11	15.75	16.10	17.34	10.94	11.28	11.92	12.27	13.51
	12H	14.91	15.21	15.90	16.19	17.49	11.06	11.36	12.05	12.34	13.64
12H	4H	13.93	14.35	14.91	15.33	16.57	10.23	10.65	11.20	11.62	12.86
	6H	14.52	14.87	15.51	15.85	17.10	10.79	11.13	11.78	12.12	13.37
	8H	14.75	15.05	15.74	16.03	17.33	11.01	11.31	12.00	12.29	13.59