

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903055

Luminaire Tested: DFN2DIP-PN3F0-060D080US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903055
REPORT IS A COMBINATION OF REPORTS P901108 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-060D080US830-RLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12271.9 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 118.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903055
CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P903055
 CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19			
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15			
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2732	2732	2732
5°	2735	2687	2705
10°	2706	2632	2616
15°	2667	2543	2479
20°	2617	2422	2311
25°	2564	2286	2149
30°	2495	2146	1943
35°	2427	1997	1763
40°	2357	1842	1557
45°	2277	1671	1370
50°	2193	1498	1187
55°	2106	1314	1012
60°	2005	1121	832
65°	1889	926	747
70°	1747	743	675
75°	1570	651	611
80°	1312	540	526
85°	892	352	389

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2277 cd/sqm



TEST NUMBER: P903055

CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	1.8
10°-20°	601.3	4.9
20°-30°	844.3	6.9
30°-40°	920.3	7.5
40°-50°	845.9	6.9
50°-60°	664.3	5.4
60°-70°	432.4	3.5
70°-80°	222.6	1.8
80°-90°	61.3	0.5
90°-100°	83.9	0.7
100°-110°	312.8	2.5
110°-120°	829.6	6.8
120°-130°	1376.0	11.2
130°-140°	1461.6	11.9
140°-150°	1358.4	11.1
150°-160°	1092.1	8.9
160°-170°	703.7	5.7
170°-180°	242.2	2.0
0°-30°	1664.7	13.6
0°-40°	2585.0	21.1
0°-60°	4095.1	33.4
0°-90°	4811.4	39.2
90°-120°	1226.4	10.0
90°-150°	5422.4	44.2
90°-180°	7460.0	60.8
0°-180°	12271.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	2	22	37	46	50	11
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2501	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P903055

CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.2	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.8	134.5
105°	559.8	615.1	112.4	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.9	854.3	322.3	138.2	145.4



TEST NUMBER: P903055

CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	933.7	966.7	935.5	141.7	147.4
115°	1058.8	1090.1	1136.1	283.6	151.1
117.5°	1167.4	1204.2	1235.7	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.9	1123.2
122.5°	1391.9	1421.5	1458.5	1469.4	1471.4
125°	1496.9	1521.0	1555.9	1568.9	1574.3
127.5°	1592.7	1618.5	1646.3	1664.6	1666.4
130°	1683.0	1712.5	1732.7	1753.0	1751.2
132.5°	1775.1	1799.1	1819.3	1835.9	1834.1
135°	1852.5	1882.0	1898.4	1917.0	1913.3
137.5°	1933.4	1955.5	1974.1	1992.4	1987.0
140°	2012.5	2027.4	2047.6	2064.2	2054.9
142.5°	2079.1	2091.9	2115.7	2130.4	2121.2
145°	2149.0	2147.0	2178.3	2191.2	2182.0
147.5°	2209.6	2204.1	2235.3	2244.6	2237.3
150°	2268.6	2255.7	2285.2	2296.1	2287.0
152.5°	2318.3	2303.6	2331.1	2342.3	2329.4
155°	2366.2	2349.8	2371.8	2382.7	2368.1
157.5°	2404.8	2390.2	2406.8	2419.7	2404.8
160°	2438.1	2427.0	2438.1	2449.0	2436.1
162.5°	2467.4	2456.5	2465.6	2478.5	2461.9
165°	2493.2	2482.3	2487.7	2500.6	2487.7
167.5°	2513.5	2502.4	2508.0	2520.9	2504.3
170°	2530.2	2518.9	2522.7	2535.6	2518.9
172.5°	2541.1	2530.2	2533.8	2546.7	2530.2
175°	2550.2	2537.3	2541.1	2553.9	2535.6
177.5°	2553.9	2541.1	2543.0	2555.9	2539.3
180°	2544.8	2544.8	2544.8	2544.8	2544.8



TEST NUMBER: P903055
 CATALOG NUMBER: DFN2DIP-PN3F0-060D080US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.50	10.25	10.55	11.30	12.72	5.47	6.22	6.52	7.27	8.69
	3H	11.17	11.84	12.23	12.90	14.34	6.64	7.31	7.70	8.37	9.81
	4H	11.77	12.40	12.84	13.46	14.91	7.09	7.72	8.16	8.78	10.23
	6H	12.18	12.76	13.26	13.83	15.29	7.40	7.98	8.48	9.05	10.50
	8H	12.30	12.86	13.39	13.94	15.39	7.48	8.04	8.57	9.12	10.57
	12H	12.36	12.89	13.45	13.96	15.44	7.52	8.05	8.61	9.12	10.60
4H	2H	9.51	10.14	10.59	11.20	12.65	6.05	6.68	7.13	7.75	9.19
	3H	11.32	11.85	12.41	12.94	14.40	7.39	7.91	8.47	9.00	10.46
	4H	12.01	12.49	13.10	13.57	15.05	7.93	8.41	9.02	9.49	10.97
	6H	12.51	12.93	13.61	14.03	15.50	8.33	8.75	9.43	9.85	11.32
	8H	12.68	13.07	13.78	14.16	15.65	8.46	8.84	9.56	9.94	11.43
	12H	12.77	13.12	13.89	14.23	15.72	8.52	8.87	9.63	9.97	11.47
8H	4H	11.97	12.35	13.07	13.45	14.94	8.20	8.58	9.29	9.68	11.17
	6H	12.52	12.84	13.64	13.98	15.47	8.70	9.02	9.82	10.16	11.65
	8H	12.74	13.02	13.86	14.13	15.64	8.89	9.17	10.02	10.29	11.79
	12H	12.87	13.11	14.00	14.23	15.77	9.00	9.25	10.13	10.36	11.90
12H	4H	11.92	12.27	13.03	13.37	14.87	8.20	8.55	9.31	9.65	11.15
	6H	12.50	12.78	13.63	13.90	15.40	8.75	9.03	9.88	10.15	11.65
	8H	12.71	12.96	13.84	14.07	15.61	8.95	9.20	10.08	10.31	11.86