

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929384

Luminaire Tested: DFN2DIP-HX4F0-100D110US940-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929384
REPORT IS A COMBINATION OF REPORTS P900957 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D110US940-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18544.6 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2581	2581	2581
5°	2585	2545	2562
10°	2564	2511	2528
15°	2527	2470	2473
20°	2476	2413	2418
25°	2426	2344	2354
30°	2362	2281	2273
35°	2302	2205	2186
40°	2229	2130	2104
45°	2155	2054	2021
50°	2074	1974	1924
55°	1990	1881	1834
60°	1895	1772	1732
65°	1791	1659	1611
70°	1659	1520	1482
75°	1476	1355	1362
80°	1256	1144	1133
85°	911	780	754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2155 cd/sqm

TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.7	1.8
10°-20°	919.1	5.0
20°-30°	1350.8	7.3
30°-40°	1568.8	8.5
40°-50°	1566.9	8.4
50°-60°	1366.3	7.4
60°-70°	1010.0	5.4
70°-80°	571.4	3.1
80°-90°	156.6	0.8
90°-100°	109.2	0.6
100°-110°	407.0	2.2
110°-120°	1079.6	5.8
120°-130°	1790.5	9.7
130°-140°	1902.0	10.3
140°-150°	1767.7	9.5
150°-160°	1421.2	7.7
160°-170°	915.7	4.9
170°-180°	315.2	1.7
0°-30°	2596.6	14.0
0°-40°	4165.4	22.5
0°-60°	7098.5	38.3
0°-90°	8836.6	47.7
90°-120°	1595.8	8.6
90°-150°	7055.9	38.0
90°-180°	9708.0	52.3
0°-180°	18544.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3471	3471	3471	3471	3471	
5°	3471	3458	3421	3448	3441	329
15°	3304	3284	3241	3254	3238	931
25°	2990	2964	2907	2914	2907	1376
35°	2580	2547	2493	2473	2456	1611
45°	2099	2076	2026	1989	1976	1620
55°	1589	1569	1529	1489	1472	1420
65°	1072	1051	1018	988	971	1059
75°	560	554	537	517	524	598
85°	137	134	130	120	117	152
90°	2	29	48	60	65	17
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1378	1418	1478	369	197	1356
125°	1948	1979	2025	2042	2049	1737
135°	2411	2449	2470	2495	2490	1862
145°	2796	2794	2834	2851	2839	1749
155°	3079	3058	3086	3101	3082	1419
165°	3244	3230	3237	3254	3237	917
175°	3318	3302	3307	3323	3300	316
180°	3312	3312	3312	3312	3312	

TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3470.9	3470.9	3470.9	3470.9	3470.9
2.5°	3491.0	3474.3	3437.5	3470.9	3464.4
5°	3470.9	3457.7	3420.9	3447.5	3441.1
7.5°	3447.5	3427.6	3390.8	3417.7	3411.0
10°	3411.0	3387.6	3347.6	3374.2	3364.3
12.5°	3360.7	3340.9	3300.8	3317.5	3310.7
15°	3304.1	3284.3	3240.6	3254.1	3237.5
17.5°	3233.9	3214.1	3170.5	3187.2	3170.5
20°	3157.1	3137.3	3090.5	3100.4	3087.3
22.5°	3080.6	3050.6	3006.9	3006.9	3000.2
25°	2990.3	2963.8	2907.1	2913.5	2907.1
27.5°	2890.1	2866.7	2823.5	2813.6	2797.0
30°	2790.3	2763.3	2713.4	2703.5	2690.0
32.5°	2683.3	2663.5	2610.0	2589.8	2576.4
35°	2579.9	2546.7	2493.1	2473.0	2456.3
37.5°	2463.1	2432.9	2379.5	2356.1	2339.4
40°	2343.0	2316.1	2262.6	2232.9	2219.5
42.5°	2226.2	2199.2	2146.2	2112.5	2092.7
45°	2099.4	2076.0	2025.7	1989.2	1975.9
47.5°	1975.9	1952.5	1899.0	1862.1	1842.3
50°	1845.5	1828.9	1782.1	1735.4	1718.8
52.5°	1718.8	1695.4	1652.2	1615.4	1592.0
55°	1588.8	1568.7	1528.6	1488.6	1472.0
57.5°	1458.5	1441.8	1398.3	1358.3	1344.9
60°	1328.2	1315.1	1268.3	1231.5	1221.6
62.5°	1201.4	1178.1	1144.8	1111.5	1098.1
65°	1071.5	1051.3	1018.0	987.9	971.3
67.5°	938.0	921.0	891.3	867.9	854.4
70°	814.4	800.9	770.9	747.5	734.4
72.5°	687.6	674.2	657.6	634.2	624.2
75°	560.5	554.2	537.2	517.4	524.0
77.5°	447.2	433.8	427.0	417.1	407.2
80°	333.9	330.4	323.6	313.7	307.0
82.5°	227.0	227.0	223.8	210.3	210.3
85°	136.7	133.5	130.3	120.1	116.9
87.5°	60.2	53.4	46.7	36.8	33.3
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.4	64.6
95°	155.7	76.5	93.3	105.5	103.0
97.5°	280.3	83.9	122.0	129.4	131.7
100°	424.2	95.9	136.6	155.7	160.5
102.5°	582.1	577.6	141.4	167.6	175.0
105°	728.4	800.4	146.3	172.4	182.1
107.5°	898.6	958.3	151.1	177.2	187.0
110°	1061.6	1111.7	419.4	179.8	189.2

TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1215.0	1257.9	1217.2	184.4	191.8
115°	1377.7	1418.4	1478.5	369.0	196.6
117.5°	1519.2	1567.0	1607.9	1265.0	637.3
120°	1677.3	1713.2	1756.4	1785.2	1461.6
122.5°	1811.4	1849.7	1897.8	1912.1	1914.7
125°	1947.9	1979.3	2024.8	2041.5	2048.7
127.5°	2072.6	2106.1	2142.2	2166.1	2168.5
130°	2190.0	2228.5	2254.6	2281.1	2278.9
132.5°	2309.8	2341.1	2367.4	2389.0	2386.7
135°	2410.6	2449.0	2470.3	2494.6	2489.7
137.5°	2515.9	2544.6	2568.8	2592.7	2585.6
140°	2618.9	2638.2	2664.4	2686.0	2674.0
142.5°	2705.3	2722.1	2753.2	2772.2	2760.3
145°	2796.4	2793.8	2834.5	2851.4	2839.4
147.5°	2875.3	2868.1	2908.8	2920.8	2911.4
150°	2952.1	2935.3	2973.7	2987.9	2976.0
152.5°	3016.7	2997.6	3033.4	3048.0	3031.2
155°	3079.0	3057.6	3086.3	3100.6	3081.5
157.5°	3129.3	3110.2	3131.9	3148.7	3129.3
160°	3172.6	3158.0	3172.6	3186.8	3170.0
162.5°	3210.7	3196.5	3208.4	3225.2	3203.6
165°	3244.3	3230.0	3237.2	3253.9	3237.2
167.5°	3270.7	3256.2	3263.6	3280.4	3258.8
170°	3292.4	3277.8	3282.6	3299.5	3277.8
172.5°	3306.6	3292.4	3297.2	3314.0	3292.4
175°	3318.5	3301.7	3306.6	3323.4	3299.5
177.5°	3323.4	3306.6	3309.1	3325.9	3304.3
180°	3311.5	3311.5	3311.5	3311.5	3311.5

TEST NUMBER: P929384

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.35	11.19	11.32	12.18	13.48	9.91	10.75	10.89	11.74	13.05
	3H	12.01	12.76	12.99	13.76	15.08	11.53	12.29	12.52	13.29	14.61
	4H	12.59	13.31	13.59	14.31	15.64	12.12	12.83	13.12	13.84	15.17
	6H	12.99	13.65	14.00	14.66	16.00	12.52	13.17	13.53	14.18	15.53
	8H	13.10	13.72	14.11	14.75	16.09	12.62	13.25	13.64	14.27	15.61
	12H	13.14	13.74	14.17	14.76	16.13	12.66	13.26	13.69	14.28	15.64
4H	2H	10.80	11.52	11.81	12.52	13.86	10.46	11.17	11.47	12.18	13.51
	3H	12.67	13.27	13.69	14.30	15.65	12.28	12.87	13.29	13.90	15.25
	4H	13.38	13.93	14.41	14.95	16.32	12.98	13.52	14.00	14.55	15.92
	6H	13.90	14.37	14.93	15.42	16.78	13.49	13.96	14.52	15.01	16.37
	8H	14.05	14.49	15.08	15.53	16.91	13.64	14.08	14.67	15.12	16.50
	12H	14.12	14.52	15.18	15.57	16.96	13.70	14.10	14.75	15.15	16.54
8H	4H	13.58	14.02	14.62	15.06	16.44	13.22	13.66	14.26	14.70	16.08
	6H	14.21	14.57	15.27	15.66	17.04	13.85	14.21	14.91	15.29	16.67
	8H	14.43	14.75	15.50	15.82	17.22	14.06	14.38	15.13	15.45	16.85
	12H	14.56	14.85	15.64	15.91	17.35	14.18	14.46	15.25	15.52	16.96
12H	4H	13.57	13.96	14.62	15.02	16.40	13.21	13.61	14.27	14.66	16.05
	6H	14.24	14.56	15.31	15.63	17.03	13.89	14.21	14.96	15.28	16.67
	8H	14.48	14.76	15.56	15.83	17.27	14.13	14.41	15.20	15.47	16.91