

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921910

Luminaire Tested: DFN2DIP-HX4F0-110D050US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921910
REPORT IS A COMBINATION OF REPORTS P899331 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D050US940-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13656.6 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 140.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921910
CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P921910

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	64	64	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	54	54	54	50
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	46	46	46	43
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	40	40	40	37
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	34	34	34	32
6	66	54	45	39	63	51	44	38	47	40	35	42	37	33	38	34	30	30	30	30	28
7	61	49	40	35	58	46	39	33	42	36	31	39	33	29	35	30	27	27	27	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	24	24	24	22
9	53	41	33	28	50	39	32	27	36	29	25	33	27	24	30	25	22	22	22	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2838	2838	2838
5°	2843	2799	2817
10°	2820	2761	2779
15°	2779	2716	2720
20°	2723	2653	2659
25°	2667	2578	2589
30°	2598	2508	2499
35°	2532	2425	2404
40°	2451	2342	2314
45°	2370	2258	2222
50°	2281	2171	2115
55°	2188	2069	2017
60°	2084	1948	1905
65°	1970	1824	1772
70°	1824	1672	1629
75°	1623	1490	1498
80°	1381	1258	1246
85°	1002	857	829

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2370 cd/sqm



TEST NUMBER: P921910

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	359.2	2.6
10°-20°	1010.7	7.4
20°-30°	1485.4	10.9
30°-40°	1725.2	12.6
40°-50°	1723.0	12.6
50°-60°	1502.4	11.0
60°-70°	1110.6	8.1
70°-80°	628.4	4.6
80°-90°	169.9	1.2
90°-100°	87.3	0.6
100°-110°	277.2	2.0
110°-120°	474.5	3.5
120°-130°	624.0	4.6
130°-140°	700.4	5.1
140°-150°	686.8	5.0
150°-160°	576.1	4.2
160°-170°	382.1	2.8
170°-180°	133.5	1.0
0°-30°	2855.3	20.9
0°-40°	4580.5	33.5
0°-60°	7805.9	57.2
0°-90°	9714.8	71.1
90°-120°	838.9	6.1
90°-150°	2850.1	20.9
90°-180°	3942.0	28.9
0°-180°	13656.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3817	3817	3817	3817	3817	
5°	3817	3802	3762	3791	3784	362
15°	3633	3611	3564	3578	3560	1023
25°	3288	3259	3197	3204	3197	1513
35°	2837	2800	2742	2719	2701	1772
45°	2309	2283	2228	2188	2173	1782
55°	1747	1725	1681	1637	1619	1562
65°	1178	1156	1120	1086	1068	1165
75°	616	609	591	569	576	658
85°	150	147	143	132	128	168
90°	1	15	42	39	40	13
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	



TEST NUMBER: P921910

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3816.7	3816.7	3816.7	3816.7	3816.7
2.5°	3838.8	3820.5	3780.0	3816.7	3809.7
5°	3816.7	3802.3	3761.8	3790.9	3784.0
7.5°	3790.9	3769.2	3728.7	3758.3	3750.9
10°	3750.9	3725.1	3681.2	3710.3	3699.4
12.5°	3695.6	3673.8	3629.8	3648.1	3640.7
15°	3633.3	3611.4	3563.5	3578.3	3560.1
17.5°	3556.1	3534.4	3486.5	3504.8	3486.5
20°	3471.7	3449.8	3398.5	3409.4	3395.0
22.5°	3387.6	3354.4	3306.6	3306.6	3299.1
25°	3288.3	3259.1	3196.8	3203.8	3196.8
27.5°	3178.1	3152.4	3104.8	3094.0	3075.7
30°	3068.3	3038.7	2983.8	2972.9	2958.1
32.5°	2950.7	2928.9	2870.1	2847.9	2833.1
35°	2837.0	2800.4	2741.6	2719.4	2701.1
37.5°	2708.5	2675.4	2616.6	2590.9	2572.6
40°	2576.5	2546.9	2488.1	2455.4	2440.6
42.5°	2448.0	2418.4	2360.0	2323.0	2301.2
45°	2308.6	2282.9	2227.6	2187.5	2172.7
47.5°	2172.7	2147.1	2088.2	2047.7	2025.9
50°	2029.4	2011.2	1959.7	1908.3	1890.1
52.5°	1890.1	1864.3	1816.9	1776.3	1750.6
55°	1747.1	1724.9	1681.0	1636.9	1618.6
57.5°	1603.8	1585.6	1537.7	1493.6	1478.8
60°	1460.5	1446.2	1394.7	1354.2	1343.4
62.5°	1321.2	1295.5	1258.8	1222.3	1207.5
65°	1178.2	1156.0	1119.5	1086.4	1068.1
67.5°	1031.4	1012.8	980.1	954.4	939.6
70°	895.5	880.7	847.7	822.0	807.5
72.5°	756.2	741.4	723.1	697.4	686.4
75°	616.4	609.4	590.7	568.9	576.3
77.5°	491.8	477.0	469.6	458.7	447.8
80°	367.2	363.3	355.9	345.0	337.6
82.5°	249.6	249.6	246.1	231.3	231.3
85°	150.3	146.8	143.3	132.0	128.5
87.5°	66.2	58.8	51.4	40.5	36.6
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4



TEST NUMBER: P921910

CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1



TEST NUMBER: P921910
 CATALOG NUMBER: DFN2DIP-HX4F0-110D050US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	13.74	13.40	14.52	15.45	12.22	13.31	12.97	14.08	15.02
	3H	14.33	15.31	15.10	16.09	17.06	13.86	14.84	14.62	15.62	16.58
	4H	14.93	15.85	15.71	16.65	17.62	14.45	15.38	15.24	16.17	17.15
	6H	15.34	16.19	16.14	17.00	17.98	14.86	15.72	15.66	16.52	17.51
	8H	15.45	16.27	16.26	17.09	18.08	14.98	15.79	15.78	16.61	17.60
	12H	15.51	16.28	16.32	17.10	18.12	15.03	15.80	15.84	16.62	17.63
4H	2H	13.14	14.07	13.93	14.86	15.83	12.80	13.72	13.58	14.51	15.49
	3H	15.03	15.80	15.83	16.63	17.62	14.64	15.41	15.43	16.23	17.23
	4H	15.75	16.46	16.57	17.28	18.30	15.35	16.05	16.16	16.88	17.90
	6H	16.28	16.89	17.11	17.74	18.77	15.87	16.48	16.70	17.33	18.36
	8H	16.44	17.01	17.27	17.85	18.89	16.03	16.59	16.86	17.44	18.48
	12H	16.52	17.03	17.38	17.90	18.94	16.10	16.61	16.95	17.48	18.52
8H	4H	15.97	16.54	16.80	17.38	18.42	15.61	16.18	16.44	17.02	18.06
	6H	16.61	17.08	17.47	17.97	19.01	16.25	16.72	17.11	17.61	18.65
	8H	16.83	17.25	17.71	18.14	19.19	16.47	16.88	17.34	17.77	18.82
	12H	16.98	17.35	17.85	18.22	19.33	16.59	16.96	17.47	17.84	18.95
12H	4H	15.97	16.48	16.82	17.34	18.39	15.61	16.13	16.47	16.99	18.04
	6H	16.64	17.06	17.52	17.95	19.00	16.29	16.71	17.16	17.59	18.65
	8H	16.90	17.27	17.77	18.14	19.25	16.54	16.91	17.42	17.78	18.89