

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921919

Luminaire Tested: DFN2DIP-HX4F0-110D090US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921919
REPORT IS A COMBINATION OF REPORTS P899404 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D090US940-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15440.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	60	55	51	51	47	45	43	40	38
4	76	66	58	52	71	62	55	49	53	48	44	46	42	39	39	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	38	43	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	26	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3014	3014	3014
5°	3019	2967	2986
10°	2990	2909	2889
15°	2949	2813	2739
20°	2895	2681	2554
25°	2839	2532	2377
30°	2765	2380	2151
35°	2692	2217	1953
40°	2617	2048	1725
45°	2531	1860	1519
50°	2441	1670	1318
55°	2348	1467	1125
60°	2240	1256	926
65°	2116	1040	834
70°	1966	839	755
75°	1777	740	687
80°	1503	622	596
85°	1051	416	449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2531 cd/sqm

TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	2.5
10°-20°	1043.0	6.8
20°-30°	1464.4	9.5
30°-40°	1596.2	10.3
40°-50°	1467.1	9.5
50°-60°	1152.2	7.5
60°-70°	750.0	4.9
70°-80°	386.0	2.5
80°-90°	105.8	0.7
90°-100°	157.1	1.0
100°-110°	499.0	3.2
110°-120°	854.0	5.5
120°-130°	1123.1	7.3
130°-140°	1260.7	8.2
140°-150°	1236.2	8.0
150°-160°	1037.0	6.7
160°-170°	687.7	4.5
170°-180°	240.4	1.6
0°-30°	2887.3	18.7
0°-40°	4483.6	29.0
0°-60°	7102.9	46.0
0°-90°	8344.7	54.0
90°-120°	1510.1	9.8
90°-150°	5130.1	33.2
90°-180°	7095.0	46.0
0°-180°	15440.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4054	4054	4054	4054	4054	
5°	4054	4036	3988	4021	4010	384
15°	3856	3815	3691	3621	3584	1087
25°	3500	3382	3140	2990	2935	1610
35°	3016	2829	2506	2275	2194	1888
45°	2466	2220	1834	1574	1486	1904
55°	1875	1588	1192	972	903	1675
65°	1266	968	638	514	502	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	181
90°	2	28	75	70	73	15
95°	112	133	137	137	133	124
105°	461	467	471	475	475	486
115°	857	869	865	863	857	848
125°	1246	1266	1260	1253	1250	1114
135°	1612	1636	1641	1638	1632	1246
145°	1957	1973	1985	1987	1979	1223
155°	2238	2244	2251	2262	2255	1030
165°	2435	2432	2432	2448	2437	687
175°	2534	2527	2523	2538	2525	241
180°	2538	2538	2538	2538	2538	

TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4054.0	4054.0	4054.0	4054.0	4054.0
2.5°	4072.3	4054.0	4013.5	4050.5	4043.1
5°	4054.0	4035.7	3987.8	4020.9	4010.0
7.5°	4020.9	3999.1	3947.7	3962.1	3943.8
10°	3976.9	3951.2	3878.0	3866.7	3845.0
12.5°	3922.0	3888.9	3789.7	3767.8	3727.3
15°	3855.8	3815.4	3690.8	3621.1	3584.5
17.5°	3778.8	3720.0	3565.9	3485.2	3426.5
20°	3690.8	3617.2	3433.9	3342.4	3261.4
22.5°	3595.5	3510.9	3298.1	3173.5	3118.6
25°	3500.1	3382.5	3140.4	2990.2	2934.9
27.5°	3386.4	3261.4	2993.7	2821.2	2736.7
30°	3265.4	3125.6	2832.2	2645.3	2546.0
32.5°	3147.8	2978.8	2678.3	2458.1	2366.2
35°	3015.9	2828.6	2506.0	2274.8	2193.8
37.5°	2887.4	2685.4	2344.4	2091.0	1999.6
40°	2751.6	2531.7	2175.5	1915.0	1819.7
42.5°	2612.2	2377.5	2007.0	1735.3	1643.8
45°	2465.5	2219.5	1834.5	1573.7	1485.8
47.5°	2326.1	2065.7	1669.5	1408.6	1328.1
50°	2171.9	1911.6	1508.0	1254.5	1177.9
52.5°	2021.3	1746.1	1353.8	1111.7	1042.0
55°	1874.6	1588.5	1192.2	972.3	902.7
57.5°	1724.4	1430.8	1049.4	843.9	785.1
60°	1570.2	1276.8	898.8	711.9	653.2
62.5°	1420.0	1126.5	770.3	594.4	565.2
65°	1265.8	968.4	638.4	513.8	502.5
67.5°	1119.1	821.7	513.8	451.1	440.2
70°	964.9	678.9	425.4	388.9	374.1
72.5°	818.1	546.5	355.8	326.5	319.1
75°	674.9	418.0	293.5	267.8	264.3
77.5°	532.1	297.0	231.2	216.4	209.0
80°	399.8	212.9	175.9	161.6	161.6
82.5°	278.7	143.2	121.1	113.7	113.7
85°	157.7	80.6	69.6	69.6	69.6
87.5°	58.8	29.2	29.2	25.7	25.7
90°	2.3	27.6	75.0	70.4	72.7
92.5°	47.4	64.3	66.6	68.8	68.8
95°	111.7	133.1	137.0	137.0	133.1
97.5°	185.9	205.8	214.3	214.3	214.3
100°	271.6	289.3	295.3	295.3	293.1
102.5°	361.9	375.0	383.3	385.7	383.3
105°	460.7	466.7	471.4	475.2	475.2
107.5°	558.6	567.8	567.8	569.3	558.6
110°	653.4	665.8	665.8	665.8	659.6

TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	756.0	769.0	766.7	760.6	756.0
115°	857.0	869.2	865.4	863.2	857.0
117.5°	957.3	974.1	963.4	957.3	951.1
120°	1058.3	1075.0	1058.3	1058.3	1051.3
122.5°	1150.0	1171.5	1160.8	1154.7	1150.0
125°	1246.5	1265.6	1259.5	1252.6	1250.4
127.5°	1340.6	1364.3	1355.9	1346.8	1340.6
130°	1428.6	1456.2	1452.3	1447.7	1439.3
132.5°	1527.3	1548.7	1550.2	1539.5	1533.5
135°	1612.2	1635.9	1640.6	1638.3	1632.2
137.5°	1707.1	1726.3	1730.1	1728.6	1719.4
140°	1790.6	1809.6	1820.3	1820.3	1812.0
142.5°	1876.2	1895.3	1901.5	1903.8	1895.3
145°	1957.4	1972.6	1984.9	1987.2	1978.8
147.5°	2030.1	2049.2	2058.3	2062.2	2053.8
150°	2105.1	2118.1	2126.5	2133.3	2126.5
152.5°	2171.6	2184.6	2195.3	2203.8	2195.3
155°	2238.2	2244.3	2251.2	2261.9	2255.0
157.5°	2295.5	2300.2	2304.0	2319.2	2308.5
160°	2346.8	2351.4	2353.8	2366.7	2357.5
162.5°	2394.2	2394.2	2396.6	2411.1	2400.4
165°	2434.8	2432.5	2432.5	2447.8	2437.1
167.5°	2471.6	2464.7	2464.7	2479.9	2469.2
170°	2499.1	2493.0	2490.7	2506.0	2493.0
172.5°	2518.2	2512.1	2509.8	2525.1	2512.1
175°	2533.5	2527.4	2522.8	2538.2	2525.1
177.5°	2541.9	2535.8	2531.2	2544.2	2531.2
180°	2538.2	2538.2	2538.2	2538.2	2538.2

TEST NUMBER: P921919

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.35	12.21	12.28	13.16	14.37	7.32	8.19	8.25	9.13	10.34
	3H	13.03	13.80	13.97	14.76	15.99	8.52	9.29	9.46	10.24	11.48
	4H	13.64	14.37	14.60	15.33	16.58	8.97	9.70	9.92	10.66	11.90
	6H	14.07	14.74	15.03	15.70	16.96	9.29	9.97	10.26	10.93	12.19
	8H	14.19	14.83	15.17	15.81	17.07	9.39	10.03	10.36	11.00	12.26
	12H	14.26	14.87	15.23	15.84	17.12	9.43	10.04	10.41	11.01	12.29
4H	2H	11.37	12.10	12.33	13.06	14.31	7.92	8.65	8.88	9.61	10.86
	3H	13.21	13.81	14.18	14.80	16.06	9.28	9.89	10.25	10.87	12.13
	4H	13.90	14.45	14.88	15.43	16.72	9.83	10.38	10.81	11.36	12.65
	6H	14.42	14.90	15.41	15.90	17.18	10.25	10.73	11.24	11.73	13.02
	8H	14.60	15.04	15.59	16.04	17.33	10.38	10.83	11.38	11.82	13.12
	12H	14.69	15.09	15.70	16.11	17.41	10.45	10.85	11.46	11.86	13.17
8H	4H	13.87	14.32	14.86	15.31	16.61	10.11	10.56	11.11	11.55	12.85
	6H	14.44	14.81	15.46	15.85	17.14	10.64	11.00	11.65	12.04	13.34
	8H	14.66	14.98	15.68	16.01	17.32	10.83	11.15	11.85	12.18	13.49
	12H	14.80	15.08	15.83	16.10	17.46	10.95	11.23	11.98	12.25	13.61
12H	4H	13.83	14.23	14.84	15.24	16.54	10.12	10.52	11.13	11.53	12.84
	6H	14.42	14.74	15.44	15.76	17.08	10.68	11.01	11.71	12.03	13.35
	8H	14.64	14.92	15.67	15.94	17.30	10.90	11.18	11.93	12.20	13.56

END OF REPORT