

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903090

Luminaire Tested: DFN2DIP-PN3F0-080D030US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903090
REPORT IS A COMBINATION OF REPORTS P899522 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D030US830-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8911.8 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3647	3583	3607
10°	3608	3510	3488
15°	3557	3391	3305
20°	3489	3229	3081
25°	3419	3048	2865
30°	3327	2862	2591
35°	3236	2662	2351
40°	3143	2456	2076
45°	3036	2227	1827
50°	2924	1997	1583
55°	2808	1751	1349
60°	2673	1495	1109
65°	2518	1234	996
70°	2330	991	899
75°	2093	868	815
80°	1750	720	701
85°	1189	468	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3036 cd/sqm

TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	3.3
10°-20°	801.8	9.0
20°-30°	1125.7	12.6
30°-40°	1227.1	13.8
40°-50°	1127.8	12.7
50°-60°	885.7	9.9
60°-70°	576.5	6.5
70°-80°	296.8	3.3
80°-90°	78.3	0.9
90°-100°	55.3	0.6
100°-110°	175.8	2.0
110°-120°	300.9	3.4
120°-130°	395.7	4.4
130°-140°	444.2	5.0
140°-150°	435.6	4.9
150°-160°	365.4	4.1
160°-170°	242.3	2.7
170°-180°	84.7	1.0
0°-30°	2219.6	24.9
0°-40°	3446.7	38.7
0°-60°	5460.2	61.3
0°-90°	6411.9	71.9
90°-120°	532.1	6.0
90°-150°	1807.5	20.3
90°-180°	2500.0	28.1
0°-180°	8911.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	1	10	26	25	26	9
95°	39	47	48	48	47	44
105°	162	164	166	167	167	171
115°	302	306	305	304	302	299
125°	439	446	444	441	440	392
135°	568	576	578	577	575	439
145°	690	695	699	700	697	431
155°	789	791	793	797	795	363
165°	858	857	857	862	859	242
175°	893	890	889	894	890	85
180°	894	894	894	894	894	



TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	0.8	9.7	26.4	24.8	25.6
92.5°	16.7	22.6	23.5	24.2	24.2
95°	39.4	46.9	48.3	48.3	46.9
97.5°	65.5	72.5	75.5	75.5	75.5
100°	95.7	101.9	104.1	104.1	103.3
102.5°	127.5	132.1	135.1	135.9	135.1
105°	162.3	164.5	166.1	167.4	167.4
107.5°	196.8	200.0	200.0	200.6	196.8
110°	230.3	234.6	234.6	234.6	232.4

TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.4	271.0	270.1	268.0	266.4
115°	302.0	306.2	304.9	304.2	302.0
117.5°	337.2	343.2	339.4	337.2	335.1
120°	372.9	378.8	372.9	372.9	370.4
122.5°	405.2	412.7	409.0	406.8	405.2
125°	439.2	445.9	443.7	441.3	440.5
127.5°	472.3	480.7	477.8	474.5	472.3
130°	503.3	513.0	511.7	510.1	507.1
132.5°	538.1	545.6	546.2	542.4	540.3
135°	568.1	576.4	578.1	577.2	575.0
137.5°	601.4	608.2	609.5	609.1	605.8
140°	630.8	637.6	641.4	641.4	638.4
142.5°	661.1	667.8	670.0	670.8	667.8
145°	689.7	695.0	699.4	700.1	697.2
147.5°	715.3	722.0	725.2	726.6	723.6
150°	741.7	746.3	749.2	751.7	749.2
152.5°	765.2	769.7	773.5	776.5	773.5
155°	788.6	790.7	793.1	796.9	794.6
157.5°	808.8	810.4	811.8	817.2	813.4
160°	826.9	828.5	829.3	833.9	830.7
162.5°	843.6	843.6	844.4	849.5	845.7
165°	857.9	857.1	857.1	862.4	858.7
167.5°	870.8	868.4	868.4	873.7	870.0
170°	880.5	878.4	877.6	883.0	878.4
172.5°	887.2	885.1	884.3	889.7	885.1
175°	892.7	890.5	888.9	894.3	889.7
177.5°	895.6	893.4	891.8	896.5	891.8
180°	894.3	894.3	894.3	894.3	894.3

TEST NUMBER: P903090

CATALOG NUMBER: DFN2DIP-PN3F0-080D030US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.44	14.49	14.19	15.26	16.18	9.41	10.46	10.16	11.22	12.15
	3H	15.13	16.07	15.89	16.85	17.80	10.61	11.55	11.37	12.32	13.28
	4H	15.75	16.63	16.53	17.41	18.38	11.06	11.95	11.85	12.73	13.70
	6H	16.17	16.99	16.97	17.78	18.76	11.39	12.21	12.19	13.00	13.98
	8H	16.30	17.08	17.11	17.89	18.87	11.48	12.26	12.29	13.07	14.05
	12H	16.37	17.11	17.18	17.91	18.92	11.53	12.27	12.34	13.08	14.08
4H	2H	13.49	14.37	14.27	15.15	16.12	10.03	10.91	10.81	11.70	12.66
	3H	15.33	16.06	16.12	16.88	17.86	11.39	12.12	12.19	12.94	13.93
	4H	16.02	16.69	16.83	17.51	18.52	11.94	12.61	12.75	13.43	14.44
	6H	16.54	17.12	17.37	17.96	18.98	12.37	12.94	13.19	13.78	14.80
	8H	16.72	17.26	17.55	18.10	19.12	12.50	13.03	13.33	13.87	14.90
	12H	16.82	17.30	17.67	18.16	19.20	12.57	13.05	13.42	13.91	14.94
8H	4H	16.01	16.54	16.84	17.38	18.41	12.23	12.77	13.07	13.61	14.64
	6H	16.57	17.02	17.43	17.90	18.93	12.75	13.20	13.61	14.08	15.11
	8H	16.79	17.18	17.66	18.06	19.10	12.94	13.33	13.81	14.21	15.26
	12H	16.93	17.28	17.80	18.14	19.24	13.06	13.41	13.94	14.28	15.38
12H	4H	15.97	16.45	16.82	17.31	18.34	12.25	12.73	13.10	13.59	14.62
	6H	16.55	16.94	17.42	17.82	18.86	12.80	13.19	13.67	14.07	15.12
	8H	16.77	17.12	17.65	17.99	19.09	13.02	13.36	13.89	14.23	15.33

END OF REPORT