

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929430

Luminaire Tested: DFN2DIP-HX4F0-120D040US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929430
REPORT IS A COMBINATION OF REPORTS P900836 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D040US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12630.7 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 156.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	68	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	54	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	50	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	34	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3290	3290	3290
5°	3295	3238	3258
10°	3263	3174	3152
15°	3218	3070	2989
20°	3159	2926	2788
25°	3098	2764	2593
30°	3017	2598	2347
35°	2937	2419	2131
40°	2856	2235	1883
45°	2762	2029	1658
50°	2664	1823	1439
55°	2562	1601	1227
60°	2445	1370	1011
65°	2309	1135	910
70°	2145	916	824
75°	1939	808	750
80°	1641	679	651
85°	1147	455	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2762 cd/sqm

TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.6	3.3
10°-20°	1138.2	9.0
20°-30°	1598.0	12.7
30°-40°	1741.9	13.8
40°-50°	1601.0	12.7
50°-60°	1257.3	10.0
60°-70°	818.4	6.5
70°-80°	421.3	3.3
80°-90°	109.7	0.9
90°-100°	39.7	0.3
100°-110°	148.0	1.2
110°-120°	392.6	3.1
120°-130°	651.1	5.2
130°-140°	691.6	5.5
140°-150°	642.8	5.1
150°-160°	516.8	4.1
160°-170°	333.0	2.6
170°-180°	114.6	0.9
0°-30°	3150.8	24.9
0°-40°	4892.8	38.7
0°-60°	7751.1	61.4
0°-90°	9100.5	72.1
90°-120°	580.3	4.6
90°-150°	2565.8	20.3
90°-180°	3530.0	27.9
0°-180°	12630.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4424	4424	4424	4424	4424	
5°	4424	4404	4352	4388	4376	419
15°	4208	4164	4028	3952	3912	1186
25°	3820	3691	3427	3263	3203	1757
35°	3291	3087	2735	2482	2394	2060
45°	2690	2422	2002	1717	1621	2078
55°	2046	1734	1301	1061	985	1828
65°	1381	1057	697	561	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	198
90°	1	10	17	22	24	12
95°	57	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	538	134	72	493
125°	708	720	736	742	745	632
135°	877	891	898	907	905	677
145°	1017	1016	1031	1037	1032	636
155°	1120	1112	1122	1128	1120	516
165°	1180	1175	1177	1183	1177	333
175°	1207	1201	1202	1208	1200	115
180°	1204	1204	1204	1204	1204	

TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4424.0	4424.0	4424.0	4424.0	4424.0
2.5°	4443.9	4424.0	4379.8	4420.1	4412.0
5°	4424.0	4404.0	4351.7	4387.8	4376.0
7.5°	4387.8	4364.0	4308.0	4323.7	4303.7
10°	4339.8	4311.8	4231.9	4219.6	4195.9
12.5°	4279.9	4243.9	4135.5	4111.8	4067.6
15°	4207.7	4163.6	4027.6	3951.6	3911.7
17.5°	4123.6	4059.5	3891.3	3803.4	3739.3
20°	4027.6	3947.4	3747.3	3647.5	3559.1
22.5°	3923.6	3831.4	3599.0	3463.1	3403.2
25°	3819.5	3691.2	3427.0	3263.0	3202.7
27.5°	3695.5	3559.1	3266.9	3078.7	2986.5
30°	3563.4	3410.9	3090.6	2886.7	2778.4
32.5°	3435.1	3250.7	2922.8	2682.4	2582.2
35°	3291.1	3086.8	2734.6	2482.3	2393.9
37.5°	3150.9	2930.5	2558.3	2281.8	2182.0
40°	3002.7	2762.7	2374.1	2089.9	1985.8
42.5°	2850.6	2594.5	2190.1	1893.6	1793.8
45°	2690.5	2422.0	2001.9	1717.4	1621.3
47.5°	2538.4	2254.3	1821.8	1537.3	1449.3
50°	2370.2	2086.0	1645.6	1369.0	1285.4
52.5°	2205.8	1905.5	1477.3	1213.1	1137.1
55°	2045.7	1733.5	1301.1	1061.0	985.0
57.5°	1881.7	1561.4	1145.1	920.9	856.8
60°	1713.5	1393.2	980.8	776.9	712.8
62.5°	1549.6	1229.3	840.6	648.7	616.7
65°	1381.4	1056.8	696.7	560.7	548.4
67.5°	1221.2	896.6	560.7	492.3	480.4
70°	1053.0	740.8	464.3	424.3	408.2
72.5°	892.9	596.4	388.2	356.4	348.3
75°	736.5	456.2	320.3	292.2	288.4
77.5°	580.7	324.1	252.3	236.2	228.1
80°	436.3	232.4	192.0	176.3	176.3
82.5°	304.2	156.3	132.1	124.0	124.0
85°	172.1	88.0	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	0.8	10.4	17.4	21.9	23.5
92.5°	21.9	18.3	20.9	22.7	23.5
95°	56.6	27.8	33.9	38.4	37.5
97.5°	102.0	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.6	58.3
102.5°	211.7	210.1	51.4	60.9	63.6
105°	264.8	291.1	53.2	62.7	66.2
107.5°	326.7	348.5	54.9	64.5	68.0
110°	386.1	404.3	152.5	65.4	68.8

TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.8	457.4	442.6	67.1	69.8
115°	500.9	515.8	537.6	134.2	71.5
117.5°	552.4	569.8	584.7	460.0	231.7
120°	609.9	623.0	638.7	649.2	531.5
122.5°	658.7	672.7	690.1	695.3	696.2
125°	708.3	719.8	736.3	742.4	745.0
127.5°	753.7	765.9	779.0	787.7	788.5
130°	796.4	810.4	819.8	829.5	828.7
132.5°	839.9	851.3	860.9	868.7	867.9
135°	876.6	890.6	898.3	907.1	905.4
137.5°	914.8	925.3	934.1	942.8	940.2
140°	952.3	959.3	968.9	976.7	972.4
142.5°	983.8	989.9	1001.2	1008.0	1003.8
145°	1016.9	1016.0	1030.7	1036.9	1032.5
147.5°	1045.5	1042.9	1057.7	1062.1	1058.7
150°	1073.4	1067.4	1081.4	1086.5	1082.2
152.5°	1097.0	1090.0	1103.0	1108.3	1102.2
155°	1119.6	1111.9	1122.3	1127.5	1120.5
157.5°	1137.9	1131.0	1138.9	1145.0	1137.9
160°	1153.6	1148.4	1153.6	1158.8	1152.7
162.5°	1167.5	1162.4	1166.7	1172.8	1165.0
165°	1179.8	1174.6	1177.2	1183.2	1177.2
167.5°	1189.4	1184.0	1186.8	1192.9	1185.0
170°	1197.2	1192.0	1193.7	1199.8	1192.0
172.5°	1202.4	1197.2	1199.0	1205.1	1197.2
175°	1206.7	1200.6	1202.4	1208.5	1199.8
177.5°	1208.5	1202.4	1203.3	1209.5	1201.6
180°	1204.2	1204.2	1204.2	1204.2	1204.2

TEST NUMBER: P929430

CATALOG NUMBER: DFN2DIP-HX4F0-120D040US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.19	13.89	14.95	15.87	9.11	10.16	9.86	10.92	11.84
	3H	14.83	15.77	15.59	16.55	17.50	10.32	11.26	11.08	12.03	12.98
	4H	15.45	16.34	16.23	17.12	18.08	10.78	11.66	11.56	12.45	13.41
	6H	15.88	16.70	16.68	17.49	18.47	11.11	11.93	11.90	12.72	13.70
	8H	16.02	16.79	16.82	17.60	18.58	11.21	11.98	12.01	12.80	13.77
	12H	16.09	16.83	16.89	17.63	18.63	11.26	12.00	12.07	12.80	13.81
4H	2H	13.18	14.07	13.97	14.85	15.81	9.73	10.62	10.52	11.40	12.36
	3H	15.03	15.77	15.83	16.59	17.56	11.10	11.84	11.90	12.66	13.64
	4H	15.73	16.40	16.54	17.22	18.23	11.66	12.33	12.47	13.15	14.15
	6H	16.26	16.84	17.09	17.68	18.69	12.09	12.67	12.92	13.51	14.53
	8H	16.44	16.98	17.27	17.82	18.84	12.23	12.77	13.06	13.60	14.63
	12H	16.55	17.03	17.40	17.89	18.92	12.30	12.79	13.16	13.65	14.68
8H	4H	15.72	16.25	16.55	17.09	18.12	11.96	12.50	12.79	13.33	14.36
	6H	16.29	16.74	17.15	17.62	18.64	12.49	12.93	13.35	13.81	14.84
	8H	16.51	16.90	17.38	17.78	18.82	12.68	13.07	13.55	13.95	14.99
	12H	16.66	17.01	17.53	17.87	18.97	12.81	13.16	13.68	14.02	15.12
12H	4H	15.68	16.16	16.53	17.02	18.05	11.97	12.46	12.82	13.32	14.35
	6H	16.27	16.66	17.14	17.54	18.58	12.54	12.93	13.41	13.81	14.85
	8H	16.50	16.85	17.37	17.71	18.81	12.76	13.11	13.63	13.97	15.07