

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903114

Luminaire Tested: DFN2DIP-PN3F0-080D090US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903114
REPORT IS A COMBINATION OF REPORTS P899606 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D090US830-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13916.7 lumens
Efficiency: N/A
Efficacy: 92.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 151.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	57	56	47	46	45
2	89	82	76	71	82	75	70	66	63	60	57	52	50	47	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3647	3583	3607
10°	3608	3510	3488
15°	3557	3391	3305
20°	3489	3229	3081
25°	3419	3048	2865
30°	3327	2862	2591
35°	3236	2662	2351
40°	3143	2456	2076
45°	3036	2227	1827
50°	2924	1997	1583
55°	2808	1751	1349
60°	2673	1495	1109
65°	2518	1234	996
70°	2330	991	899
75°	2093	868	815
80°	1750	720	701
85°	1189	468	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3036 cd/sqm

TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	2.1
10°-20°	801.8	5.8
20°-30°	1125.7	8.1
30°-40°	1227.1	8.8
40°-50°	1127.8	8.1
50°-60°	885.7	6.4
60°-70°	576.5	4.1
70°-80°	296.8	2.1
80°-90°	83.4	0.6
90°-100°	166.0	1.2
100°-110°	527.5	3.8
110°-120°	902.7	6.5
120°-130°	1187.2	8.5
130°-140°	1332.5	9.6
140°-150°	1306.7	9.4
150°-160°	1096.1	7.9
160°-170°	726.9	5.2
170°-180°	254.1	1.8
0°-30°	2219.6	15.9
0°-40°	3446.7	24.8
0°-60°	5460.2	39.2
0°-90°	6416.9	46.1
90°-120°	1596.2	11.5
90°-150°	5422.6	39.0
90°-180°	7500.0	53.9
0°-180°	13916.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	2	29	79	74	77	14
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2380	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2667	2683	2669	254
180°	2683	2683	2683	2683	2683	

TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.8	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2



TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.9	918.8	914.7	912.4	905.9
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.3
122.5°	1215.6	1238.3	1227.0	1220.5	1215.6
125°	1317.6	1337.8	1331.3	1324.0	1321.6
127.5°	1417.0	1442.1	1433.2	1423.5	1417.0
130°	1510.0	1539.2	1535.1	1530.2	1521.4
132.5°	1614.4	1637.0	1638.6	1627.3	1620.9
135°	1704.1	1729.2	1734.1	1731.6	1725.2
137.5°	1804.4	1824.7	1828.7	1827.1	1817.4
140°	1892.6	1912.8	1924.1	1924.1	1915.2
142.5°	1983.2	2003.4	2009.9	2012.3	2003.4
145°	2069.0	2085.1	2098.0	2100.5	2091.6
147.5°	2145.8	2166.0	2175.7	2179.7	2170.9
150°	2225.1	2238.8	2247.7	2254.9	2247.7
152.5°	2295.4	2309.1	2320.4	2329.4	2320.4
155°	2365.8	2372.2	2379.5	2390.9	2383.6
157.5°	2426.4	2431.3	2435.3	2451.5	2440.1
160°	2480.6	2485.5	2487.9	2501.6	2491.9
162.5°	2530.7	2530.7	2533.2	2548.5	2537.2
165°	2573.6	2571.2	2571.2	2587.4	2576.1
167.5°	2612.4	2605.2	2605.2	2621.3	2610.0
170°	2641.6	2635.1	2632.7	2648.8	2635.1
172.5°	2661.7	2655.3	2652.9	2669.1	2655.3
175°	2678.0	2671.4	2666.6	2682.9	2669.1
177.5°	2686.8	2680.4	2675.5	2689.3	2675.5
180°	2682.9	2682.9	2682.9	2682.9	2682.9

TEST NUMBER: P903114

CATALOG NUMBER: DFN2DIP-PN3F0-080D090US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.22	12.02	12.22	13.03	14.35	7.19	7.99	8.19	8.99	10.32
	3H	12.89	13.61	13.90	14.62	15.97	8.37	9.08	9.38	10.10	11.45
	4H	13.50	14.17	14.52	15.19	16.54	8.81	9.49	9.83	10.51	11.86
	6H	13.91	14.53	14.94	15.55	16.92	9.13	9.75	10.16	10.77	12.14
	8H	14.03	14.63	15.07	15.66	17.03	9.22	9.81	10.25	10.84	12.21
	12H	14.09	14.65	15.13	15.68	17.07	9.26	9.82	10.30	10.85	12.24
4H	2H	11.24	11.91	12.26	12.93	14.28	7.78	8.45	8.80	9.47	10.83
	3H	13.06	13.62	14.09	14.66	16.03	9.12	9.68	10.15	10.72	12.10
	4H	13.74	14.26	14.78	15.29	16.69	9.66	10.17	10.70	11.21	12.60
	6H	14.25	14.69	15.30	15.75	17.14	10.07	10.51	11.12	11.57	12.96
	8H	14.42	14.83	15.47	15.88	17.29	10.20	10.61	11.25	11.66	13.06
	12H	14.51	14.88	15.58	15.95	17.36	10.26	10.63	11.33	11.69	13.10
8H	4H	13.71	14.12	14.76	15.17	16.57	9.93	10.35	10.99	11.40	12.80
	6H	14.26	14.60	15.34	15.70	17.10	10.44	10.78	11.52	11.88	13.28
	8H	14.48	14.78	15.56	15.85	17.27	10.63	10.93	11.71	12.01	13.43
	12H	14.61	14.87	15.69	15.94	17.41	10.74	11.00	11.83	12.08	13.54
12H	4H	13.66	14.03	14.73	15.09	16.50	9.94	10.31	11.01	11.38	12.78
	6H	14.24	14.54	15.32	15.62	17.04	10.49	10.79	11.57	11.87	13.29
	8H	14.45	14.72	15.54	15.79	17.25	10.69	10.96	11.78	12.03	13.49