

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921930

Luminaire Tested: DFN2DIP-HX4F0-120D060US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921930
REPORT IS A COMBINATION OF REPORTS P899351 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D060US940-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15328.5 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 160.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94		83	83	83		74
1	102	98	94	90	96	92	89	86	83	80	77		74	71	70		65
2	93	85	79	74	88	81	75	70	72	68	64		65	61	58		57
3	85	75	67	61	80	71	64	59	64	58	54		57	53	49		51
4	78	67	58	52	73	63	56	50	57	51	46		51	46	42		46
5	71	59	51	45	67	56	49	43	51	45	40		46	41	37		41
6	66	53	45	39	62	51	43	38	46	40	35		41	36	32		37
7	61	48	40	34	58	46	39	33	42	36	31		38	33	29		34
8	57	44	36	31	54	42	35	30	38	32	28		35	29	26		31
9	53	40	33	27	50	39	31	26	35	29	25		32	27	23		29
10	50	37	30	25	47	36	29	24	32	27	22		30	25	21		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3096	3096	3096
5°	3101	3053	3073
10°	3076	3012	3032
15°	3031	2963	2967
20°	2970	2894	2901
25°	2910	2812	2824
30°	2834	2736	2726
35°	2762	2646	2623
40°	2673	2555	2525
45°	2585	2464	2424
50°	2488	2368	2307
55°	2387	2257	2200
60°	2273	2125	2078
65°	2149	1990	1933
70°	1990	1824	1777
75°	1770	1625	1634
80°	1506	1373	1359
85°	1093	935	904

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2585 cd/sqm

TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.9	2.6
10°-20°	1102.6	7.2
20°-30°	1620.4	10.6
30°-40°	1882.0	12.3
40°-50°	1879.7	12.3
50°-60°	1639.0	10.7
60°-70°	1211.6	7.9
70°-80°	685.5	4.5
80°-90°	185.7	1.2
90°-100°	104.7	0.7
100°-110°	332.7	2.2
110°-120°	569.3	3.7
120°-130°	748.8	4.9
130°-140°	840.5	5.5
140°-150°	824.2	5.4
150°-160°	691.4	4.5
160°-170°	458.5	3.0
170°-180°	160.3	1.0
0°-30°	3114.9	20.3
0°-40°	4996.9	32.6
0°-60°	8515.5	55.6
0°-90°	10598.3	69.1
90°-120°	1006.7	6.6
90°-150°	3420.1	22.3
90°-180°	4730.0	30.9
0°-180°	15328.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4164	4164	4164	4164	4164	
5°	4164	4148	4104	4136	4128	395
15°	3964	3940	3888	3904	3884	1116
25°	3587	3555	3487	3495	3487	1651
35°	3095	3055	2991	2967	2947	1933
45°	2518	2490	2430	2386	2370	1944
55°	1906	1882	1834	1786	1766	1704
65°	1285	1261	1221	1185	1165	1271
75°	672	665	644	621	629	718
85°	164	160	156	144	140	183
90°	2	18	50	47	48	15
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4163.7	4163.7	4163.7	4163.7	4163.7
2.5°	4187.8	4167.9	4123.7	4163.7	4156.0
5°	4163.7	4147.9	4103.7	4135.6	4127.9
7.5°	4135.6	4111.8	4067.6	4099.9	4091.9
10°	4091.9	4063.8	4015.8	4047.7	4035.8
12.5°	4031.5	4007.7	3959.7	3979.7	3971.6
15°	3963.6	3939.8	3887.5	3903.6	3883.7
17.5°	3879.5	3855.7	3803.4	3823.4	3803.4
20°	3787.3	3763.5	3707.5	3719.3	3703.6
22.5°	3695.5	3659.4	3607.1	3607.1	3599.1
25°	3587.2	3555.3	3487.4	3495.1	3487.4
27.5°	3467.0	3439.0	3387.2	3375.2	3355.3
30°	3347.2	3314.9	3255.0	3243.2	3227.0
32.5°	3218.9	3195.2	3131.0	3106.8	3090.7
35°	3094.9	3055.0	2990.8	2966.6	2946.7
37.5°	2954.7	2918.7	2854.5	2826.5	2806.5
40°	2810.8	2778.5	2714.3	2678.6	2662.5
42.5°	2670.6	2638.3	2574.5	2534.2	2510.4
45°	2518.5	2490.5	2430.1	2386.4	2370.3
47.5°	2370.3	2342.2	2278.1	2233.9	2210.1
50°	2213.9	2194.0	2137.9	2081.8	2061.8
52.5°	2061.8	2033.8	1982.0	1937.8	1909.8
55°	1905.9	1881.8	1833.7	1785.7	1765.8
57.5°	1749.6	1729.7	1677.4	1629.4	1613.3
60°	1593.3	1577.6	1521.5	1477.4	1465.4
62.5°	1441.3	1413.2	1373.3	1333.4	1317.2
65°	1285.4	1261.1	1221.2	1185.1	1165.2
67.5°	1125.2	1104.8	1069.2	1041.2	1025.0
70°	977.0	960.8	924.7	896.7	881.0
72.5°	824.9	808.8	788.8	760.8	748.9
75°	672.4	664.8	644.3	620.6	628.7
77.5°	536.5	520.3	512.3	500.3	488.5
80°	400.6	396.3	388.3	376.4	368.3
82.5°	272.2	272.2	268.5	252.4	252.4
85°	164.0	160.2	156.3	144.0	140.2
87.5°	72.2	64.1	56.1	44.1	39.9
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P921930

CATALOG NUMBER: DFN2DIP-HX4F0-120D060US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.80	13.87	13.58	14.66	15.63	12.37	13.43	13.14	14.23	15.20
	3H	14.48	15.43	15.26	16.24	17.24	14.00	14.96	14.79	15.77	16.77
	4H	15.08	15.98	15.88	16.79	17.80	14.60	15.50	15.41	16.32	17.33
	6H	15.49	16.32	16.30	17.14	18.17	15.01	15.84	15.83	16.67	17.69
	8H	15.60	16.39	16.42	17.23	18.26	15.12	15.92	15.95	16.76	17.78
	12H	15.65	16.41	16.48	17.24	18.30	15.17	15.93	16.00	16.76	17.81
4H	2H	13.29	14.19	14.10	15.00	16.01	12.94	13.85	13.75	14.66	15.67
	3H	15.17	15.93	15.99	16.78	17.80	14.78	15.53	15.60	16.38	17.41
	4H	15.90	16.58	16.73	17.43	18.48	15.49	16.18	16.32	17.02	18.08
	6H	16.42	17.02	17.27	17.89	18.95	16.01	16.61	16.86	17.48	18.54
	8H	16.58	17.13	17.43	18.00	19.07	16.17	16.72	17.02	17.59	18.66
	12H	16.66	17.16	17.54	18.05	19.13	16.24	16.74	17.11	17.63	18.70
8H	4H	16.11	16.67	16.96	17.53	18.60	15.75	16.30	16.60	17.17	18.24
	6H	16.75	17.21	17.63	18.12	19.19	16.39	16.85	17.27	17.76	18.83
	8H	16.97	17.38	17.87	18.28	19.37	16.61	17.01	17.50	17.92	19.00
	12H	17.12	17.48	18.01	18.37	19.51	16.73	17.09	17.63	17.99	19.13
12H	4H	16.11	16.61	16.98	17.49	18.57	15.75	16.25	16.63	17.14	18.22
	6H	16.78	17.19	17.68	18.09	19.18	16.43	16.84	17.32	17.74	18.83
	8H	17.04	17.40	17.93	18.29	19.43	16.68	17.04	17.57	17.93	19.07