

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929450

Luminaire Tested: DFN2DIP-HX4F0-120D090US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929450
REPORT IS A COMBINATION OF REPORTS P900926 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D090US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17046.1 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 194.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3290	3290	3290
5°	3295	3238	3258
10°	3263	3174	3152
15°	3218	3070	2989
20°	3159	2926	2788
25°	3098	2764	2593
30°	3017	2598	2347
35°	2937	2419	2131
40°	2856	2235	1883
45°	2762	2029	1658
50°	2664	1823	1439
55°	2562	1601	1227
60°	2445	1370	1011
65°	2309	1135	910
70°	2145	916	824
75°	1939	808	750
80°	1641	679	651
85°	1147	455	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2762 cd/sqm

TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	414.6	2.4
10°-20°	1138.2	6.7
20°-30°	1598.0	9.4
30°-40°	1741.9	10.2
40°-50°	1601.0	9.4
50°-60°	1257.3	7.4
60°-70°	818.4	4.8
70°-80°	421.3	2.5
80°-90°	112.3	0.7
90°-100°	89.3	0.5
100°-110°	333.0	2.0
110°-120°	883.3	5.2
120°-130°	1465.0	8.6
130°-140°	1556.2	9.1
140°-150°	1446.3	8.5
150°-160°	1162.8	6.8
160°-170°	749.2	4.4
170°-180°	257.9	1.5
0°-30°	3150.8	18.5
0°-40°	4892.8	28.7
0°-60°	7751.1	45.5
0°-90°	9103.2	53.4
90°-120°	1305.7	7.7
90°-150°	5773.1	33.9
90°-180°	7943.0	46.6
0°-180°	17046.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4424	4424	4424	4424	4424	
5°	4424	4404	4352	4388	4376	419
15°	4208	4164	4028	3952	3912	1186
25°	3820	3691	3427	3263	3203	1757
35°	3291	3087	2735	2482	2394	2060
45°	2690	2422	2002	1717	1621	2078
55°	2046	1734	1301	1061	985	1828
65°	1381	1057	697	561	548	1369
75°	736	456	320	292	288	779
85°	172	88	76	76	76	198
90°	2	24	39	49	53	16
95°	127	63	76	86	84	151
105°	596	655	120	141	149	637
115°	1127	1160	1210	302	161	1110
125°	1594	1619	1657	1670	1676	1421
135°	1972	2004	2021	2041	2037	1524
145°	2288	2286	2319	2333	2323	1431
155°	2519	2502	2525	2537	2521	1161
165°	2654	2643	2649	2662	2649	750
175°	2715	2701	2705	2719	2700	258
180°	2709	2709	2709	2709	2709	

TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4424.0	4424.0	4424.0	4424.0	4424.0
2.5°	4443.9	4424.0	4379.8	4420.1	4412.0
5°	4424.0	4404.0	4351.7	4387.8	4376.0
7.5°	4387.8	4364.0	4308.0	4323.7	4303.7
10°	4339.8	4311.8	4231.9	4219.6	4195.9
12.5°	4279.9	4243.9	4135.5	4111.8	4067.6
15°	4207.7	4163.6	4027.6	3951.6	3911.7
17.5°	4123.6	4059.5	3891.3	3803.4	3739.3
20°	4027.6	3947.4	3747.3	3647.5	3559.1
22.5°	3923.6	3831.4	3599.0	3463.1	3403.2
25°	3819.5	3691.2	3427.0	3263.0	3202.7
27.5°	3695.5	3559.1	3266.9	3078.7	2986.5
30°	3563.4	3410.9	3090.6	2886.7	2778.4
32.5°	3435.1	3250.7	2922.8	2682.4	2582.2
35°	3291.1	3086.8	2734.6	2482.3	2393.9
37.5°	3150.9	2930.5	2558.3	2281.8	2182.0
40°	3002.7	2762.7	2374.1	2089.9	1985.8
42.5°	2850.6	2594.5	2190.1	1893.6	1793.8
45°	2690.5	2422.0	2001.9	1717.4	1621.3
47.5°	2538.4	2254.3	1821.8	1537.3	1449.3
50°	2370.2	2086.0	1645.6	1369.0	1285.4
52.5°	2205.8	1905.5	1477.3	1213.1	1137.1
55°	2045.7	1733.5	1301.1	1061.0	985.0
57.5°	1881.7	1561.4	1145.1	920.9	856.8
60°	1713.5	1393.2	980.8	776.9	712.8
62.5°	1549.6	1229.3	840.6	648.7	616.7
65°	1381.4	1056.8	696.7	560.7	548.4
67.5°	1221.2	896.6	560.7	492.3	480.4
70°	1053.0	740.8	464.3	424.3	408.2
72.5°	892.9	596.4	388.2	356.4	348.3
75°	736.5	456.2	320.3	292.2	288.4
77.5°	580.7	324.1	252.3	236.2	228.1
80°	436.3	232.4	192.0	176.3	176.3
82.5°	304.2	156.3	132.1	124.0	124.0
85°	172.1	88.0	76.0	76.0	76.0
87.5°	64.1	31.8	31.8	28.0	28.0
90°	1.9	23.5	39.1	49.1	52.8
92.5°	49.1	41.2	47.0	51.0	52.8
95°	127.4	62.6	76.4	86.3	84.3
97.5°	229.3	68.7	99.9	105.9	107.8
100°	347.1	78.5	111.8	127.4	131.3
102.5°	476.3	472.6	115.7	137.1	143.2
105°	595.9	654.9	119.6	141.1	149.0
107.5°	735.2	784.1	123.6	145.0	153.0
110°	868.5	909.6	343.2	147.1	154.9

TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	994.0	1029.2	995.9	150.8	156.9
115°	1127.2	1160.5	1209.6	301.9	160.8
117.5°	1242.9	1282.1	1315.5	1035.1	521.5
120°	1372.3	1401.7	1437.1	1460.6	1195.9
122.5°	1482.1	1513.5	1552.8	1564.4	1566.5
125°	1593.7	1619.3	1656.6	1670.4	1676.2
127.5°	1695.7	1723.2	1752.8	1772.3	1774.2
130°	1791.8	1823.3	1844.7	1866.3	1864.5
132.5°	1889.9	1915.5	1936.9	1954.6	1952.8
135°	1972.3	2003.7	2021.2	2041.0	2037.1
137.5°	2058.5	2081.9	2101.7	2121.3	2115.5
140°	2142.7	2158.6	2180.0	2197.6	2187.9
142.5°	2213.5	2227.2	2252.6	2268.2	2258.5
145°	2288.0	2285.8	2319.2	2332.9	2323.1
147.5°	2352.5	2346.7	2379.9	2389.8	2382.0
150°	2415.4	2401.6	2433.0	2444.6	2434.9
152.5°	2468.2	2452.6	2481.9	2493.8	2480.0
155°	2519.2	2501.7	2525.2	2536.8	2521.2
157.5°	2560.4	2544.8	2562.4	2576.2	2560.4
160°	2595.7	2583.9	2595.7	2607.4	2593.7
162.5°	2626.9	2615.3	2625.1	2638.8	2621.1
165°	2654.4	2642.7	2648.6	2662.4	2648.6
167.5°	2676.1	2664.2	2670.2	2683.9	2666.3
170°	2693.8	2681.9	2685.8	2699.5	2681.9
172.5°	2705.4	2693.8	2697.7	2711.4	2693.8
175°	2715.2	2701.4	2705.4	2719.1	2699.5
177.5°	2719.1	2705.4	2707.5	2721.2	2703.6
180°	2709.4	2709.4	2709.4	2709.4	2709.4

TEST NUMBER: P929450

CATALOG NUMBER: DFN2DIP-HX4F0-120D090US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.60	12.46	12.53	13.40	14.63	7.57	8.43	8.51	9.38	10.60
	3H	13.28	14.05	14.22	15.00	16.25	8.76	9.53	9.71	10.49	11.74
	4H	13.89	14.61	14.85	15.57	16.83	9.22	9.94	10.18	10.90	12.16
	6H	14.31	14.98	15.28	15.95	17.22	9.54	10.21	10.51	11.17	12.44
	8H	14.44	15.08	15.42	16.06	17.33	9.63	10.27	10.61	11.25	12.52
	12H	14.50	15.11	15.49	16.08	17.38	9.68	10.28	10.66	11.26	12.55
4H	2H	11.62	12.35	12.59	13.31	14.56	8.17	8.90	9.14	9.86	11.11
	3H	13.45	14.06	14.43	15.05	16.32	9.53	10.13	10.50	11.12	12.39
	4H	14.15	14.70	15.13	15.68	16.98	10.08	10.63	11.06	11.61	12.91
	6H	14.66	15.14	15.66	16.15	17.44	10.50	10.97	11.49	11.98	13.27
	8H	14.84	15.28	15.84	16.28	17.59	10.63	11.07	11.63	12.07	13.38
	12H	14.94	15.34	15.95	16.35	17.67	10.70	11.09	11.71	12.11	13.42
8H	4H	14.12	14.56	15.11	15.56	16.87	10.36	10.80	11.36	11.80	13.11
	6H	14.69	15.05	15.71	16.09	17.40	10.88	11.24	11.90	12.29	13.59
	8H	14.90	15.22	15.93	16.25	17.58	11.07	11.39	12.10	12.42	13.75
	12H	15.04	15.33	16.08	16.35	17.72	11.19	11.48	12.23	12.50	13.87
12H	4H	14.07	14.47	15.09	15.49	16.80	10.36	10.76	11.38	11.78	13.09
	6H	14.66	14.98	15.69	16.01	17.34	10.93	11.25	11.96	12.28	13.61
	8H	14.88	15.17	15.92	16.19	17.56	11.14	11.43	12.18	12.45	13.82

END OF REPORT