

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924521

Luminaire Tested: DFN2DIP-HX4F0-040D090US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924521  
REPORT IS A COMBINATION OF REPORTS P899390 AND P896188  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-040D090US950-RLLFLL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10842.2 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 84.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924521  
CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P924521

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	38	30
1	94	89	86	83	84	80	77	75	64	62	60	48	47	46	34	33	32	34	33	32	26
2	85	78	73	68	76	71	66	62	56	53	50	43	40	38	30	29	28	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	27	25	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	20	18	16	13
7	56	44	37	31	50	40	33	29	32	27	24	25	22	19	18	16	14	18	16	14	12
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13	17	15	13	10
9	48	36	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11	14	12	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1173	1173	1173
5°	1175	1154	1162
10°	1163	1132	1124
15°	1147	1094	1065
20°	1126	1043	994
25°	1105	985	925
30°	1075	926	837
35°	1047	862	760
40°	1018	797	671
45°	985	724	591
50°	950	650	513
55°	914	571	438
60°	871	488	360
65°	823	405	324
70°	765	326	294
75°	691	288	267
80°	585	242	232
85°	409	162	175

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2048 cd/sqm



TEST NUMBER: P924521

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.8	1.4
10°-20°	405.8	3.7
20°-30°	569.7	5.3
30°-40°	621.0	5.7
40°-50°	570.8	5.3
50°-60°	448.2	4.1
60°-70°	291.8	2.7
70°-80°	150.2	1.4
80°-90°	46.1	0.4
90°-100°	168.0	1.5
100°-110°	533.9	4.9
110°-120°	913.7	8.4
120°-130°	1201.6	11.1
130°-140°	1348.7	12.4
140°-150°	1322.6	12.2
150°-160°	1109.5	10.2
160°-170°	735.8	6.8
170°-180°	257.2	2.4
0°-30°	1123.3	10.4
0°-40°	1744.3	16.1
0°-60°	2763.3	25.5
0°-90°	3251.3	30.0
90°-120°	1615.6	14.9
90°-150°	5488.5	50.6
90°-180°	7591.0	70.0
0°-180°	10842.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	2	30	80	75	78	11
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	



TEST NUMBER: P924521

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7



TEST NUMBER: P924521

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5



TEST NUMBER: P924521  
 CATALOG NUMBER: DFN2DIP-HX4F0-040D090US950-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.46	6.16	6.58	7.26	8.80	1.44	2.13	2.55	3.24	4.77
	3H	7.13	7.75	8.26	8.87	10.41	2.62	3.23	3.74	4.35	5.90
	4H	7.73	8.32	8.87	9.44	10.99	3.06	3.65	4.20	4.76	6.32
	6H	8.15	8.69	9.29	9.81	11.37	3.38	3.92	4.52	5.04	6.60
	8H	8.27	8.78	9.42	9.92	11.48	3.46	3.98	4.61	5.11	6.67
	12H	8.33	8.82	9.48	9.94	11.53	3.50	3.99	4.65	5.12	6.70
4H	2H	5.47	6.05	6.61	7.17	8.72	2.02	2.60	3.16	3.72	5.27
	3H	7.28	7.77	8.43	8.91	10.48	3.35	3.84	4.50	4.98	6.55
	4H	7.97	8.42	9.12	9.55	11.14	3.90	4.35	5.05	5.48	7.07
	6H	8.48	8.86	9.63	10.02	11.59	4.31	4.70	5.47	5.85	7.43
	8H	8.65	9.01	9.81	10.16	11.75	4.44	4.80	5.59	5.94	7.54
	12H	8.74	9.07	9.91	10.22	11.82	4.50	4.82	5.67	5.98	7.58
8H	4H	7.93	8.29	9.08	9.43	11.03	4.17	4.53	5.32	5.67	7.27
	6H	8.49	8.79	9.67	9.97	11.56	4.69	4.98	5.86	6.17	7.76
	8H	8.71	8.96	9.89	10.13	11.74	4.88	5.13	6.06	6.30	7.91
	12H	8.84	9.07	10.02	10.23	11.87	4.99	5.22	6.18	6.38	8.03
12H	4H	7.87	8.20	9.04	9.36	10.95	4.17	4.49	5.34	5.65	7.25
	6H	8.47	8.72	9.65	9.89	11.50	4.73	4.99	5.91	6.16	7.77
	8H	8.68	8.91	9.86	10.07	11.72	4.94	5.17	6.12	6.33	7.97