

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905685

Luminaire Tested: DFN2DIP-PN3F0-030D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905685
REPORT IS A COMBINATION OF REPORTS P901059 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D050US835-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 61.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905685
CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P905685

CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38	38	38	38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32	32	32	32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26	26	26	26
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	22	22	22	22
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19	19	19	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17	17	17	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15	15	15	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13	13	13	13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12	12	12	12
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13	11	11	11	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10	10	10	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1365	1365	1365
5°	1366	1345	1354
10°	1354	1326	1335
15°	1333	1303	1306
20°	1306	1271	1276
25°	1278	1234	1242
30°	1244	1200	1198
35°	1211	1159	1152
40°	1171	1118	1108
45°	1131	1076	1063
50°	1087	1033	1011
55°	1041	982	963
60°	989	923	908
65°	933	861	843
70°	860	786	772
75°	760	695	707
80°	639	579	584
85°	451	383	380

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1138 cd/sqm



TEST NUMBER: P905685

CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	1.4
10°-20°	309.1	3.9
20°-30°	454.3	5.7
30°-40°	527.6	6.7
40°-50°	527.0	6.7
50°-60°	459.5	5.8
60°-70°	339.7	4.3
70°-80°	192.2	2.4
80°-90°	53.7	0.7
90°-100°	55.7	0.7
100°-110°	207.4	2.6
110°-120°	550.1	6.9
120°-130°	912.4	11.5
130°-140°	969.2	12.2
140°-150°	900.8	11.4
150°-160°	724.2	9.1
160°-170°	466.6	5.9
170°-180°	160.6	2.0
0°-30°	873.3	11.0
0°-40°	1400.9	17.7
0°-60°	2387.4	30.1
0°-90°	2973.0	37.5
90°-120°	813.2	10.3
90°-150°	3595.6	45.4
90°-180°	4947.0	62.5
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	1	15	24	31	33	7
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P905685

CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P905685

CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P905685
 CATALOG NUMBER: DFN2DIP-PN3F0-030D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.04	7.80	8.09	8.86	10.30	6.60	7.36	7.66	8.42	9.86
	3H	8.68	9.36	9.75	10.43	11.89	8.20	8.88	9.27	9.95	11.41
	4H	9.26	9.91	10.34	10.98	12.44	8.78	9.42	9.86	10.49	11.96
	6H	9.65	10.25	10.74	11.32	12.80	9.16	9.76	10.25	10.83	12.31
	8H	9.75	10.32	10.84	11.41	12.88	9.26	9.83	10.35	10.92	12.39
	12H	9.79	10.33	10.89	11.42	12.91	9.30	9.84	10.39	10.92	12.41
4H	2H	7.48	8.13	8.57	9.20	10.66	7.13	7.78	8.22	8.85	10.31
	3H	9.33	9.87	10.42	10.97	12.45	8.93	9.47	10.02	10.57	12.04
	4H	10.04	10.53	11.13	11.62	13.12	9.62	10.12	10.72	11.20	12.70
	6H	10.54	10.97	11.65	12.08	13.57	10.12	10.54	11.22	11.65	13.15
	8H	10.69	11.08	11.79	12.19	13.69	10.26	10.65	11.36	11.76	13.27
	12H	10.75	11.11	11.87	12.23	13.74	10.31	10.67	11.44	11.79	13.30
8H	4H	10.22	10.62	11.33	11.72	13.23	9.85	10.25	10.96	11.35	12.86
	6H	10.84	11.17	11.97	12.31	13.82	10.47	10.79	11.59	11.94	13.44
	8H	11.06	11.34	12.19	12.47	13.99	10.67	10.96	11.81	12.09	13.61
	12H	11.18	11.43	12.32	12.55	14.11	10.78	11.03	11.92	12.15	13.72
12H	4H	10.20	10.56	11.32	11.68	13.19	9.84	10.20	10.96	11.32	12.83
	6H	10.87	11.16	12.00	12.28	13.81	10.50	10.79	11.64	11.92	13.44
	8H	11.10	11.35	12.24	12.48	14.04	10.73	10.98	11.87	12.10	13.67