

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924582

Luminaire Tested: DFN2DIP-HX4F0-080D040US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924582
REPORT IS A COMBINATION OF REPORTS P899307 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D040US950-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10932.8 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 100.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924582
CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P924582

CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58			
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49			
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41			
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35			
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31			
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27			
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26	24			
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22			
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19			
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2208	2208	2208
5°	2212	2178	2192
10°	2194	2148	2163
15°	2162	2113	2116
20°	2119	2064	2069
25°	2075	2006	2014
30°	2021	1951	1944
35°	1970	1887	1871
40°	1907	1822	1801
45°	1844	1757	1729
50°	1775	1689	1646
55°	1703	1610	1569
60°	1621	1516	1482
65°	1533	1419	1379
70°	1419	1301	1268
75°	1263	1159	1165
80°	1074	979	969
85°	780	667	645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1844 cd/sqm



TEST NUMBER: P924582

CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.6
10°-20°	786.4	7.2
20°-30°	1155.7	10.6
30°-40°	1342.3	12.3
40°-50°	1340.6	12.3
50°-60°	1169.0	10.7
60°-70°	864.1	7.9
70°-80°	488.9	4.5
80°-90°	132.5	1.2
90°-100°	74.7	0.7
100°-110°	237.3	2.2
110°-120°	406.1	3.7
120°-130°	534.0	4.9
130°-140°	599.4	5.5
140°-150°	587.8	5.4
150°-160°	493.1	4.5
160°-170°	327.0	3.0
170°-180°	114.3	1.0
0°-30°	2221.6	20.3
0°-40°	3563.9	32.6
0°-60°	6073.6	55.6
0°-90°	7559.1	69.1
90°-120°	718.0	6.6
90°-150°	2439.3	22.3
90°-180°	3374.0	30.9
0°-180°	10932.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	1	13	36	34	34	10
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P924582

CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7



TEST NUMBER: P924582

CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8



TEST NUMBER: P924582
 CATALOG NUMBER: DFN2DIP-HX4F0-080D040US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.63	12.69	12.40	13.49	14.46	11.20	12.26	11.97	13.06	14.02
	3H	13.30	14.26	14.09	15.07	16.06	12.83	13.79	13.62	14.59	15.59
	4H	13.90	14.80	14.71	15.62	16.63	13.43	14.33	14.23	15.14	16.15
	6H	14.31	15.15	15.13	15.97	16.99	13.84	14.67	14.65	15.49	16.52
	8H	14.42	15.22	15.25	16.06	17.08	13.95	14.74	14.77	15.58	16.61
	12H	14.48	15.24	15.31	16.07	17.12	14.00	14.75	14.83	15.59	16.64
4H	2H	12.11	13.02	12.92	13.83	14.84	11.77	12.67	12.58	13.49	14.50
	3H	14.00	14.75	14.82	15.60	16.63	13.61	14.36	14.43	15.21	16.23
	4H	14.72	15.41	15.56	16.26	17.31	14.32	15.00	15.15	15.85	16.90
	6H	15.25	15.84	16.10	16.71	17.77	14.84	15.43	15.69	16.31	17.36
	8H	15.41	15.96	16.26	16.83	17.90	14.99	15.55	15.85	16.41	17.48
	12H	15.49	15.99	16.36	16.87	17.95	15.07	15.57	15.94	16.45	17.53
8H	4H	14.94	15.49	15.79	16.36	17.43	14.58	15.13	15.43	16.00	17.07
	6H	15.58	16.04	16.46	16.94	18.02	15.21	15.67	16.10	16.58	17.65
	8H	15.80	16.21	16.69	17.11	18.20	15.43	15.84	16.32	16.74	17.83
	12H	15.94	16.30	16.84	17.20	18.34	15.56	15.92	16.45	16.81	17.95
12H	4H	14.93	15.43	15.81	16.32	17.39	14.58	15.08	15.45	15.97	17.04
	6H	15.61	16.02	16.50	16.92	18.01	15.26	15.67	16.15	16.57	17.66
	8H	15.86	16.22	16.76	17.12	18.26	15.50	15.86	16.40	16.76	17.90