

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905706

Luminaire Tested: DFN2DIP-PN3F0-040D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905706
REPORT IS A COMBINATION OF REPORTS P899514 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-040D030US835-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6055.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905706
CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P905706

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1933	1933	1933
5°	1935	1901	1913
10°	1914	1862	1850
15°	1887	1799	1753
20°	1851	1713	1634
25°	1814	1617	1520
30°	1765	1518	1375
35°	1717	1412	1247
40°	1667	1303	1101
45°	1610	1182	969
50°	1551	1059	840
55°	1490	929	716
60°	1418	793	588
65°	1336	655	528
70°	1236	526	477
75°	1110	461	432
80°	928	382	372
85°	631	248	275

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1610 cd/sqm



TEST NUMBER: P905706

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	2.6
10°-20°	425.3	7.0
20°-30°	597.2	9.9
30°-40°	650.9	10.8
40°-50°	598.3	9.9
50°-60°	469.9	7.8
60°-70°	305.8	5.1
70°-80°	157.4	2.6
80°-90°	42.9	0.7
90°-100°	58.7	1.0
100°-110°	186.5	3.1
110°-120°	319.2	5.3
120°-130°	419.8	6.9
130°-140°	471.2	7.8
140°-150°	462.1	7.6
150°-160°	387.7	6.4
160°-170°	257.1	4.2
170°-180°	89.9	1.5
0°-30°	1177.4	19.4
0°-40°	1828.4	30.2
0°-60°	2896.5	47.8
0°-90°	3402.7	56.2
90°-120°	564.5	9.3
90°-150°	1917.7	31.7
90°-180°	2652.0	43.8
0°-180°	6055.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	1	10	28	26	27	6
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	



TEST NUMBER: P905706

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P905706

CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8



TEST NUMBER: P905706
 CATALOG NUMBER: DFN2DIP-PN3F0-040D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.96	10.84	10.87	11.76	12.95	5.92	6.81	6.83	7.73	8.91
	3H	11.63	12.42	12.55	13.35	14.56	7.11	7.90	8.03	8.83	10.04
	4H	12.24	12.98	13.17	13.92	15.14	7.56	8.30	8.49	9.24	10.46
	6H	12.66	13.35	13.61	14.29	15.52	7.88	8.56	8.82	9.51	10.74
	8H	12.78	13.44	13.74	14.40	15.62	7.96	8.62	8.92	9.58	10.81
	12H	12.84	13.47	13.80	14.42	15.67	8.01	8.63	8.97	9.58	10.83
4H	2H	9.98	10.73	10.92	11.66	12.88	6.52	7.27	7.46	8.20	9.42
	3H	11.81	12.43	12.76	13.39	14.63	7.87	8.49	8.82	9.46	10.69
	4H	12.50	13.06	13.46	14.02	15.28	8.41	8.98	9.37	9.94	11.20
	6H	13.01	13.49	13.98	14.48	15.74	8.83	9.32	9.80	10.30	11.56
	8H	13.18	13.64	14.16	14.61	15.88	8.96	9.41	9.93	10.39	11.66
	12H	13.27	13.68	14.27	14.68	15.95	9.02	9.43	10.01	10.43	11.70
8H	4H	12.47	12.92	13.44	13.90	15.17	8.69	9.15	9.67	10.13	11.40
	6H	13.03	13.40	14.03	14.42	15.69	9.21	9.58	10.21	10.60	11.87
	8H	13.24	13.57	14.25	14.58	15.87	9.39	9.72	10.40	10.73	12.02
	12H	13.38	13.67	14.39	14.67	16.00	9.51	9.80	10.52	10.80	12.14
12H	4H	12.42	12.83	13.41	13.83	15.10	8.70	9.11	9.69	10.11	11.38
	6H	13.00	13.33	14.01	14.34	15.63	9.25	9.59	10.26	10.59	11.88
	8H	13.22	13.51	14.23	14.51	15.85	9.46	9.75	10.47	10.76	12.09