

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924599

Luminaire Tested: DFN2DIP-HX4F0-080D120US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924599
REPORT IS A COMBINATION OF REPORTS P899452 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D120US950-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16618.7 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 149.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924599
CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P924599
 CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39			
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34			
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29			
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25			
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22			
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19			
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17			
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15			
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14			
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12			
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2345	2345	2345
5°	2349	2308	2323
10°	2326	2263	2248
15°	2294	2189	2131
20°	2252	2086	1988
25°	2209	1970	1849
30°	2151	1852	1674
35°	2094	1725	1519
40°	2036	1593	1342
45°	1969	1447	1182
50°	1899	1300	1026
55°	1827	1142	875
60°	1743	977	721
65°	1646	809	648
70°	1529	653	587
75°	1383	576	535
80°	1169	484	464
85°	818	324	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2730 cd/sqm



TEST NUMBER: P924599

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	1.8
10°-20°	811.5	4.9
20°-30°	1139.4	6.9
30°-40°	1242.0	7.5
40°-50°	1141.5	6.9
50°-60°	896.5	5.4
60°-70°	583.5	3.5
70°-80°	300.4	1.8
80°-90°	87.0	0.5
90°-100°	224.0	1.3
100°-110°	711.8	4.3
110°-120°	1218.2	7.3
120°-130°	1602.1	9.6
130°-140°	1798.3	10.8
140°-150°	1763.5	10.6
150°-160°	1479.3	8.9
160°-170°	981.0	5.9
170°-180°	342.9	2.1
0°-30°	2246.6	13.5
0°-40°	3488.6	21.0
0°-60°	5526.6	33.3
0°-90°	6497.5	39.1
90°-120°	2154.1	13.0
90°-150°	7318.0	44.0
90°-180°	10121.0	60.9
0°-180°	16618.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	3	39	107	100	104	16
95°	159	190	195	195	190	177
105°	657	666	672	678	678	693
115°	1222	1240	1234	1231	1222	1209
125°	1778	1805	1797	1787	1784	1589
135°	2300	2334	2340	2337	2328	1778
145°	2792	2814	2831	2835	2823	1745
155°	3193	3201	3211	3226	3217	1470
165°	3473	3470	3470	3492	3476	980
175°	3614	3605	3599	3620	3602	343
180°	3620	3620	3620	3620	3620	



TEST NUMBER: P924599

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	3.2	39.3	106.9	100.5	103.7
92.5°	67.6	91.7	94.9	98.3	98.3
95°	159.3	189.9	195.4	195.4	189.9
97.5°	265.2	293.6	305.7	305.7	305.7
100°	387.5	412.6	421.3	421.3	418.0
102.5°	516.3	534.8	546.8	550.2	546.8
105°	657.1	665.8	672.4	677.8	677.8
107.5°	796.8	809.9	809.9	812.0	796.8
110°	932.2	949.6	949.6	949.6	940.9



TEST NUMBER: P924599

CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1078.4	1097.0	1093.7	1085.0	1078.4
115°	1222.5	1240.0	1234.5	1231.2	1222.5
117.5°	1365.5	1389.5	1374.2	1365.5	1356.8
120°	1509.6	1533.6	1509.6	1509.6	1499.8
122.5°	1640.6	1671.1	1655.9	1647.1	1640.6
125°	1778.1	1805.3	1796.7	1786.8	1783.5
127.5°	1912.4	1946.2	1934.1	1921.1	1912.4
130°	2037.8	2077.1	2071.7	2065.1	2053.1
132.5°	2178.6	2209.3	2211.4	2196.1	2187.4
135°	2299.8	2333.7	2340.3	2336.9	2328.2
137.5°	2435.2	2462.5	2467.9	2465.7	2452.6
140°	2554.1	2581.4	2596.7	2596.7	2584.7
142.5°	2676.4	2703.7	2712.4	2715.7	2703.7
145°	2792.1	2813.9	2831.4	2834.7	2822.7
147.5°	2895.8	2923.1	2936.2	2941.7	2929.6
150°	3002.8	3021.3	3033.3	3043.2	3033.3
152.5°	3097.7	3116.2	3131.6	3143.6	3131.6
155°	3192.7	3201.4	3211.3	3226.5	3216.7
157.5°	3274.6	3281.1	3286.5	3308.4	3293.1
160°	3347.7	3354.3	3357.5	3376.1	3362.9
162.5°	3415.3	3415.3	3418.7	3439.4	3424.1
165°	3473.2	3470.0	3470.0	3491.7	3476.5
167.5°	3525.6	3515.8	3515.8	3537.6	3522.4
170°	3564.9	3556.1	3552.9	3574.7	3556.1
172.5°	3592.2	3583.4	3580.2	3602.0	3583.4
175°	3614.0	3605.3	3598.8	3620.5	3602.0
177.5°	3626.1	3617.3	3610.7	3629.3	3610.7
180°	3620.5	3620.5	3620.5	3620.5	3620.5



TEST NUMBER: P924599
 CATALOG NUMBER: DFN2DIP-HX4F0-080D120US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.00	9.75	10.05	10.80	12.22	4.97	5.72	6.02	6.77	8.19
	3H	10.67	11.34	11.73	12.40	13.84	6.15	6.82	7.21	7.88	9.32
	4H	11.27	11.91	12.35	12.97	14.42	6.60	7.24	7.67	8.30	9.75
	6H	11.69	12.28	12.77	13.34	14.80	6.92	7.50	8.00	8.57	10.03
	8H	11.82	12.37	12.90	13.45	14.91	7.01	7.56	8.10	8.65	10.10
	12H	11.88	12.40	12.97	13.48	14.95	7.05	7.58	8.14	8.65	10.13
4H	2H	9.00	9.64	10.08	10.70	12.15	5.56	6.19	6.63	7.25	8.70
	3H	10.83	11.36	11.91	12.45	13.90	6.90	7.43	7.99	8.52	9.98
	4H	11.52	12.00	12.61	13.08	14.56	7.45	7.93	8.54	9.01	10.49
	6H	12.03	12.44	13.13	13.55	15.02	7.86	8.28	8.96	9.38	10.86
	8H	12.20	12.59	13.30	13.69	15.18	7.99	8.38	9.09	9.47	10.96
	12H	12.30	12.65	13.41	13.75	15.25	8.05	8.40	9.17	9.51	11.01
8H	4H	11.48	11.87	12.58	12.96	14.45	7.72	8.11	8.82	9.20	10.69
	6H	12.04	12.36	13.17	13.50	14.99	8.24	8.56	9.36	9.70	11.18
	8H	12.26	12.54	13.39	13.66	15.17	8.43	8.71	9.56	9.83	11.34
	12H	12.40	12.64	13.53	13.76	15.30	8.55	8.79	9.68	9.91	11.45
12H	4H	11.43	11.78	12.54	12.89	14.38	7.72	8.07	8.84	9.18	10.68
	6H	12.02	12.30	13.15	13.42	14.93	8.29	8.57	9.42	9.69	11.19
	8H	12.24	12.48	13.37	13.60	15.14	8.50	8.74	9.63	9.86	11.40