

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902859

Luminaire Tested: DFN2DIP-PN2F0-020D040US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902859
REPORT IS A COMBINATION OF REPORTS P901002 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D040US830-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5334.8 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1687	1687	1687
5°	1687	1657	1669
10°	1668	1621	1612
15°	1642	1564	1526
20°	1609	1487	1421
25°	1575	1401	1320
30°	1531	1313	1192
35°	1487	1219	1080
40°	1442	1122	952
45°	1390	1016	836
50°	1337	908	723
55°	1280	793	614
60°	1215	674	504
65°	1140	554	451
70°	1048	441	404
75°	933	382	363
80°	767	310	307
85°	502	193	218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1390 cd/sqm

TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.4
10°-20°	200.4	3.8
20°-30°	281.4	5.3
30°-40°	306.8	5.8
40°-50°	282.0	5.3
50°-60°	221.4	4.2
60°-70°	144.1	2.7
70°-80°	74.2	1.4
80°-90°	21.2	0.4
90°-100°	41.9	0.8
100°-110°	156.4	2.9
110°-120°	414.8	7.8
120°-130°	688.0	12.9
130°-140°	730.8	13.7
140°-150°	679.2	12.7
150°-160°	546.1	10.2
160°-170°	351.9	6.6
170°-180°	121.1	2.3
0°-30°	554.9	10.4
0°-40°	861.7	16.2
0°-60°	1365.1	25.6
0°-90°	1604.6	30.1
90°-120°	613.2	11.5
90°-150°	2711.2	50.8
90°-180°	3730.0	69.9
0°-180°	5334.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	11	18	23	25	5
95°	60	29	36	40	40	71
105°	280	308	56	66	70	299
115°	529	545	568	142	76	521
125°	748	760	778	784	787	668
135°	926	941	949	958	957	715
145°	1074	1074	1089	1096	1091	672
155°	1183	1175	1186	1191	1184	545
165°	1247	1241	1244	1250	1244	352
175°	1275	1269	1270	1277	1268	121
180°	1272	1272	1272	1272	1272	

TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	0.8	11.0	18.4	23.1	24.8
92.5°	23.1	19.3	22.1	23.9	24.8
95°	59.8	29.4	35.8	40.5	39.6
97.5°	107.7	32.2	46.9	49.8	50.6
100°	163.0	36.9	52.5	59.8	61.6
102.5°	223.7	222.0	54.3	64.4	67.2
105°	279.8	307.6	56.2	66.3	69.9
107.5°	345.3	368.3	58.1	68.1	71.8
110°	407.9	427.2	161.2	69.1	72.7

TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	466.8	483.3	467.7	70.9	73.7
115°	529.3	545.0	568.1	141.8	75.6
117.5°	583.7	602.1	617.8	486.1	244.9
120°	644.5	658.3	674.9	686.0	561.7
122.5°	696.0	710.8	729.2	734.7	735.7
125°	748.5	760.5	778.0	784.5	787.2
127.5°	796.4	809.3	823.1	832.4	833.2
130°	841.5	856.3	866.3	876.5	875.6
132.5°	887.5	899.6	909.6	917.9	917.1
135°	926.2	941.0	949.2	958.5	956.7
137.5°	966.7	977.7	987.0	996.2	993.4
140°	1006.3	1013.7	1023.8	1032.1	1027.5
142.5°	1039.5	1045.9	1057.9	1065.2	1060.6
145°	1074.5	1073.6	1089.1	1095.6	1091.0
147.5°	1104.8	1102.0	1117.7	1122.3	1118.7
150°	1134.3	1127.8	1142.6	1148.1	1143.5
152.5°	1159.1	1151.8	1165.5	1171.1	1164.7
155°	1183.1	1174.9	1185.9	1191.4	1184.0
157.5°	1202.4	1195.0	1203.4	1209.8	1202.4
160°	1219.0	1213.4	1219.0	1224.5	1218.0
162.5°	1233.7	1228.2	1232.8	1239.3	1231.0
165°	1246.6	1241.1	1243.9	1250.3	1243.9
167.5°	1256.8	1251.1	1254.1	1260.5	1252.2
170°	1265.1	1259.5	1261.3	1267.8	1259.5
172.5°	1270.5	1265.1	1267.0	1273.4	1265.1
175°	1275.1	1268.7	1270.5	1277.0	1267.8
177.5°	1277.0	1270.5	1271.5	1278.0	1269.7
180°	1272.4	1272.4	1272.4	1272.4	1272.4

TEST NUMBER: P902859

CATALOG NUMBER: DFN2DIP-PN2F0-020D040US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.63	7.32	7.74	8.42	9.95	2.60	3.29	3.71	4.39	5.93
	3H	8.27	8.89	9.40	10.00	11.55	3.76	4.37	4.88	5.49	7.04
	4H	8.86	9.45	9.99	10.56	12.12	4.19	4.77	5.32	5.89	7.44
	6H	9.26	9.80	10.40	10.92	12.48	4.49	5.03	5.63	6.14	7.71
	8H	9.37	9.88	10.52	11.02	12.58	4.57	5.08	5.71	6.21	7.77
	12H	9.42	9.91	10.57	11.03	12.61	4.60	5.08	5.75	6.21	7.79
4H	2H	6.62	7.21	7.76	8.32	9.88	3.16	3.75	4.30	4.86	6.42
	3H	8.42	8.90	9.56	10.04	11.61	4.48	4.97	5.63	6.11	7.68
	4H	9.09	9.53	10.24	10.66	12.25	5.01	5.46	6.16	6.59	8.17
	6H	9.57	9.96	10.73	11.11	12.69	5.40	5.78	6.56	6.94	8.52
	8H	9.73	10.09	10.89	11.24	12.83	5.52	5.88	6.67	7.02	8.61
	12H	9.81	10.14	10.98	11.29	12.89	5.57	5.89	6.74	7.05	8.65
8H	4H	9.04	9.40	10.19	10.54	12.14	5.27	5.62	6.42	6.77	8.36
	6H	9.58	9.87	10.75	11.06	12.65	5.76	6.05	6.93	7.24	8.83
	8H	9.78	10.04	10.96	11.20	12.81	5.93	6.19	7.11	7.36	8.97
	12H	9.90	10.12	11.08	11.29	12.93	6.03	6.26	7.22	7.42	9.07
12H	4H	8.98	9.31	10.15	10.46	12.06	5.26	5.58	6.43	6.74	8.34
	6H	9.55	9.81	10.73	10.98	12.58	5.80	6.06	6.98	7.22	8.83
	8H	9.75	9.98	10.93	11.14	12.78	5.99	6.21	7.17	7.38	9.02

END OF REPORT