

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902862

Luminaire Tested: DFN2DIP-PN2F0-020D050US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902862
REPORT IS A COMBINATION OF REPORTS P899492 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D050US830-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5773.1 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 57.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		71	71	71		53	53	53		36	36	36
1	93	89	85	82		83	80	77	74		62	60	59		47	45	44		32	31	31
2	85	78	72	67		76	70	65	61		55	52	49		41	39	37		28	27	26
3	78	69	62	56		69	62	56	51		49	45	41		37	34	32		25	24	23
4	71	61	53	48		63	55	48	44		43	39	35		33	30	27		23	21	20
5	65	54	47	41		58	49	42	37		39	34	31		29	26	24		21	19	17
6	60	49	41	35		54	44	37	32		35	30	27		27	23	21		19	17	15
7	55	44	36	31		50	40	33	28		32	27	23		24	21	19		17	15	14
8	51	40	32	27		46	36	30	25		29	24	21		22	19	16		16	14	12
9	48	36	29	24		43	33	27	22		26	22	19		20	17	15		15	13	11
10	45	33	26	22		40	30	24	20		24	20	17		19	16	13		14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1687	1687	1687
5°	1687	1657	1669
10°	1668	1621	1612
15°	1642	1564	1526
20°	1609	1487	1421
25°	1575	1401	1320
30°	1531	1313	1192
35°	1487	1219	1080
40°	1442	1122	952
45°	1390	1016	836
50°	1337	908	723
55°	1280	793	614
60°	1215	674	504
65°	1140	554	451
70°	1048	441	404
75°	933	382	363
80°	767	310	307
85°	502	193	218

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2011 cd/sqm

TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.3
10°-20°	200.4	3.5
20°-30°	281.4	4.9
30°-40°	306.8	5.3
40°-50°	282.0	4.9
50°-60°	221.4	3.8
60°-70°	144.1	2.5
70°-80°	74.2	1.3
80°-90°	23.2	0.4
90°-100°	92.2	1.6
100°-110°	293.0	5.1
110°-120°	501.5	8.7
120°-130°	659.5	11.4
130°-140°	740.3	12.8
140°-150°	725.9	12.6
150°-160°	609.0	10.5
160°-170°	403.9	7.0
170°-180°	141.2	2.4
0°-30°	554.9	9.6
0°-40°	861.7	14.9
0°-60°	1365.1	23.6
0°-90°	1606.6	27.8
90°-120°	886.7	15.4
90°-150°	3012.5	52.2
90°-180°	4167.0	72.2
0°-180°	5773.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	779	779	779	779	779	
5°	779	776	766	773	771	74
15°	741	733	709	696	689	209
25°	673	650	604	575	564	309
35°	580	544	482	437	422	363
45°	474	426	353	302	286	366
55°	360	305	229	187	173	322
65°	243	186	123	99	97	241
75°	130	80	56	52	51	137
85°	30	16	13	13	13	35
90°	1	16	44	41	43	6
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1438	1431	403
175°	1488	1484	1482	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	779.1	779.1	779.1	779.1	779.1
2.5°	782.6	779.1	771.3	778.4	777.0
5°	779.1	775.6	766.4	772.8	770.6
7.5°	772.8	768.5	758.7	761.5	757.9
10°	764.3	759.3	745.3	743.1	739.0
12.5°	753.8	747.3	728.3	724.2	716.3
15°	741.0	733.2	709.3	695.9	688.9
17.5°	726.2	714.9	685.3	669.8	658.6
20°	709.3	695.1	660.0	642.3	626.8
22.5°	691.0	674.8	633.9	609.9	599.4
25°	672.7	650.1	603.5	574.7	564.0
27.5°	650.8	626.8	575.3	542.2	525.9
30°	627.5	600.7	544.3	508.4	489.3
32.5°	604.9	572.5	514.7	472.4	454.8
35°	579.6	543.7	481.6	437.2	421.6
37.5°	554.9	516.0	450.5	401.9	384.3
40°	528.8	486.5	418.1	368.1	349.7
42.5°	502.0	456.9	385.7	333.5	315.9
45°	473.8	426.5	352.6	302.5	285.5
47.5°	447.0	397.0	320.8	270.7	255.2
50°	417.5	367.4	289.8	241.1	226.4
52.5°	388.4	335.5	260.1	213.7	200.3
55°	360.2	305.3	229.1	186.9	173.4
57.5°	331.4	274.9	201.7	162.2	150.9
60°	301.8	245.3	172.8	136.9	125.5
62.5°	272.9	216.5	148.1	114.2	108.6
65°	243.3	186.2	122.7	98.8	96.6
67.5°	215.1	157.9	98.8	86.7	84.6
70°	185.4	130.4	81.7	74.7	71.9
72.5°	157.2	105.0	68.3	62.8	61.4
75°	129.7	80.3	56.4	51.5	50.8
77.5°	102.3	57.1	44.4	41.6	40.2
80°	76.8	40.9	33.8	31.0	31.0
82.5°	53.5	27.5	23.3	21.9	21.9
85°	30.3	15.5	13.4	13.4	13.4
87.5°	11.3	5.7	5.7	4.9	4.9
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	391.0	391.0	391.0	387.3

TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.3	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.6
120°	621.4	631.3	621.4	621.4	617.4
122.5°	675.3	688.0	681.6	678.1	675.3
125°	732.0	743.2	739.6	735.6	734.2
127.5°	787.2	801.2	796.3	790.8	787.2
130°	839.0	855.1	852.8	850.2	845.2
132.5°	896.9	909.5	910.4	904.1	900.5
135°	946.8	960.6	963.4	962.1	958.5
137.5°	1002.5	1013.7	1016.0	1015.0	1009.7
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.4	1165.5	1167.0	1162.0
147.5°	1192.1	1203.3	1208.7	1211.0	1206.0
150°	1236.1	1243.8	1248.7	1252.7	1248.7
152.5°	1275.3	1282.9	1289.1	1294.1	1289.1
155°	1314.3	1317.9	1321.9	1328.2	1324.2
157.5°	1348.0	1350.7	1352.9	1362.0	1355.7
160°	1378.1	1380.8	1382.1	1389.8	1384.4
162.5°	1406.0	1406.0	1407.3	1415.9	1409.6
165°	1429.8	1428.4	1428.4	1437.5	1431.2
167.5°	1451.3	1447.3	1447.3	1456.3	1450.0
170°	1467.5	1464.0	1462.6	1471.6	1464.0
172.5°	1478.8	1475.2	1473.9	1482.8	1475.2
175°	1487.8	1484.1	1481.5	1490.4	1482.8
177.5°	1492.7	1489.1	1486.4	1494.0	1486.4
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P902862

CATALOG NUMBER: DFN2DIP-PN2F0-020D050US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.30	6.98	7.43	8.10	9.66	2.27	2.95	3.41	4.07	5.63
	3H	7.95	8.55	9.09	9.68	11.26	3.43	4.04	4.57	5.17	6.74
	4H	8.54	9.11	9.68	10.24	11.82	3.86	4.44	5.01	5.57	7.15
	6H	8.93	9.46	10.09	10.59	12.18	4.16	4.69	5.32	5.82	7.41
	8H	9.05	9.55	10.21	10.70	12.28	4.24	4.74	5.40	5.89	7.47
	12H	9.10	9.57	10.26	10.71	12.32	4.27	4.75	5.44	5.89	7.49
4H	2H	6.30	6.87	7.45	8.00	9.58	2.84	3.41	4.00	4.54	6.12
	3H	8.09	8.57	9.25	9.72	11.31	4.15	4.63	5.32	5.79	7.38
	4H	8.76	9.20	9.92	10.34	11.95	4.68	5.12	5.85	6.27	7.88
	6H	9.25	9.62	10.42	10.79	12.39	5.07	5.45	6.24	6.62	8.22
	8H	9.41	9.76	10.58	10.92	12.53	5.19	5.54	6.36	6.70	8.32
	12H	9.48	9.80	10.67	10.97	12.59	5.24	5.56	6.42	6.73	8.35
8H	4H	8.71	9.06	9.88	10.22	11.84	4.94	5.29	6.11	6.45	8.06
	6H	9.25	9.54	10.44	10.74	12.35	5.43	5.72	6.62	6.92	8.53
	8H	9.45	9.70	10.64	10.88	12.52	5.61	5.86	6.80	7.04	8.67
	12H	9.57	9.79	10.77	10.97	12.63	5.70	5.93	6.90	7.10	8.77
12H	4H	8.66	8.97	9.84	10.14	11.76	4.93	5.25	6.12	6.42	8.04
	6H	9.22	9.48	10.42	10.65	12.29	5.47	5.72	6.66	6.90	8.54
	8H	9.42	9.64	10.62	10.82	12.49	5.66	5.88	6.86	7.06	8.72

END OF REPORT