

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902895

Luminaire Tested: DFN2DIP-PN2F0-040D030US830-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P902895  
REPORT IS A COMBINATION OF REPORTS P900996 AND P897905  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-PN2F0-040D030US830-RLONL  
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6004.0 lumens  
Efficiency: N/A  
Efficacy: 103.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 58.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9613  
Total Harmonic Distortion (THDi): 0.083  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P902895  
CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P902895  
 CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53	53	53	53
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	39	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34	34	34	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	30	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	19	19	19	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3375	3375	3375
5°	3375	3314	3338
10°	3336	3242	3224
15°	3285	3128	3052
20°	3218	2973	2842
25°	3151	2802	2639
30°	3062	2626	2384
35°	2974	2438	2160
40°	2884	2245	1904
45°	2781	2031	1672
50°	2673	1816	1446
55°	2561	1587	1229
60°	2430	1348	1007
65°	2279	1107	901
70°	2097	882	808
75°	1866	763	726
80°	1535	620	614
85°	1004	386	437

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2781 cd/sqm



TEST NUMBER: P902895

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	146.0	2.4
10°-20°	400.9	6.7
20°-30°	562.8	9.4
30°-40°	613.5	10.2
40°-50°	563.9	9.4
50°-60°	442.9	7.4
60°-70°	288.3	4.8
70°-80°	148.4	2.5
80°-90°	39.6	0.7
90°-100°	31.5	0.5
100°-110°	117.3	2.0
110°-120°	311.1	5.2
120°-130°	516.0	8.6
130°-140°	548.1	9.1
140°-150°	509.4	8.5
150°-160°	409.6	6.8
160°-170°	263.9	4.4
170°-180°	90.8	1.5
0°-30°	1109.8	18.5
0°-40°	1723.3	28.7
0°-60°	2730.1	45.5
0°-90°	3206.3	53.4
90°-120°	459.9	7.7
90°-150°	2033.4	33.9
90°-180°	2798.0	46.6
0°-180°	6004.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	1	8	14	17	19	6
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	



TEST NUMBER: P902895

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6



TEST NUMBER: P902895

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3



TEST NUMBER: P902895  
 CATALOG NUMBER: DFN2DIP-PN2F0-040D030US830-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.57	12.43	12.50	13.38	14.60	7.54	8.39	8.47	9.34	10.57
	3H	13.23	14.00	14.17	14.95	16.20	8.71	9.48	9.66	10.43	11.68
	4H	13.82	14.55	14.79	15.51	16.77	9.15	9.88	10.11	10.84	12.09
	6H	14.23	14.90	15.20	15.87	17.13	9.46	10.13	10.43	11.09	12.36
	8H	14.35	14.98	15.33	15.97	17.23	9.54	10.18	10.52	11.16	12.43
	12H	14.40	15.01	15.39	15.98	17.28	9.58	10.18	10.56	11.16	12.45
4H	2H	11.59	12.31	12.55	13.27	14.53	8.12	8.85	9.09	9.81	11.07
	3H	13.40	14.00	14.37	14.99	16.26	9.46	10.06	10.43	11.05	12.32
	4H	14.07	14.62	15.06	15.61	16.90	9.99	10.54	10.98	11.53	12.82
	6H	14.57	15.04	15.57	16.05	17.34	10.39	10.87	11.39	11.87	13.17
	8H	14.73	15.18	15.73	16.18	17.48	10.51	10.96	11.51	11.96	13.26
	12H	14.82	15.22	15.83	16.23	17.55	10.57	10.97	11.59	11.99	13.30
8H	4H	14.04	14.48	15.04	15.48	16.79	10.26	10.70	11.26	11.70	13.01
	6H	14.58	14.95	15.60	15.99	17.30	10.76	11.12	11.78	12.17	13.47
	8H	14.79	15.11	15.82	16.14	17.46	10.94	11.26	11.97	12.29	13.61
	12H	14.91	15.19	15.94	16.22	17.59	11.04	11.32	12.08	12.35	13.72
12H	4H	13.99	14.39	15.01	15.41	16.72	10.26	10.66	11.28	11.68	12.99
	6H	14.56	14.88	15.59	15.91	17.23	10.80	11.12	11.83	12.15	13.48
	8H	14.76	15.05	15.80	16.07	17.44	11.00	11.28	12.03	12.30	13.67