

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905870

Luminaire Tested: DFN2DIP-PN3F0-090D090US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905870
REPORT IS A COMBINATION OF REPORTS P899608 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D090US835-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15615.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4348	4348	4348
5°	4353	4276	4305
10°	4307	4189	4163
15°	4245	4048	3945
20°	4164	3854	3677
25°	4081	3638	3419
30°	3971	3416	3093
35°	3862	3178	2806
40°	3752	2931	2478
45°	3623	2659	2180
50°	3491	2384	1889
55°	3352	2090	1610
60°	3191	1784	1324
65°	3005	1473	1189
70°	2781	1183	1073
75°	2498	1036	973
80°	2089	859	837
85°	1418	559	618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3623 cd/sqm

TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	2.2
10°-20°	957.0	6.1
20°-30°	1343.6	8.6
30°-40°	1464.6	9.4
40°-50°	1346.2	8.6
50°-60°	1057.2	6.8
60°-70°	688.1	4.4
70°-80°	354.2	2.3
80°-90°	98.5	0.6
90°-100°	176.1	1.1
100°-110°	559.6	3.6
110°-120°	957.7	6.1
120°-130°	1259.5	8.1
130°-140°	1413.8	9.1
140°-150°	1386.4	8.9
150°-160°	1163.0	7.4
160°-170°	771.2	4.9
170°-180°	269.6	1.7
0°-30°	2649.2	17.0
0°-40°	4113.9	26.3
0°-60°	6517.2	41.7
0°-90°	7658.1	49.0
90°-120°	1693.5	10.8
90°-150°	5753.1	36.8
90°-180°	7957.0	51.0
0°-180°	15615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	3	31	84	79	82	15
95°	125	149	154	154	149	139
105°	517	523	529	533	533	545
115°	961	975	970	968	961	951
125°	1398	1419	1412	1405	1402	1249
135°	1808	1835	1840	1837	1830	1398
145°	2195	2212	2226	2228	2219	1372
155°	2510	2517	2525	2537	2529	1155
165°	2730	2728	2728	2745	2733	770
175°	2841	2834	2829	2846	2832	270
180°	2846	2846	2846	2846	2846	

TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	2.6	30.9	84.1	78.9	81.5
92.5°	53.2	72.1	74.7	77.2	77.2
95°	125.3	149.3	153.6	153.6	149.3
97.5°	208.5	230.8	240.3	240.3	240.3
100°	304.6	324.4	331.2	331.2	328.7
102.5°	405.9	420.5	429.9	432.5	429.9
105°	516.6	523.4	528.6	532.9	532.9
107.5°	626.4	636.7	636.7	638.4	626.4
110°	732.8	746.6	746.6	746.6	739.7



TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	847.8	862.4	859.8	853.0	847.8
115°	961.1	974.8	970.5	968.0	961.1
117.5°	1073.5	1092.4	1080.4	1073.5	1066.6
120°	1186.8	1205.6	1186.8	1186.8	1179.0
122.5°	1289.7	1313.8	1301.8	1294.9	1289.7
125°	1397.9	1419.3	1412.5	1404.7	1402.2
127.5°	1503.4	1530.0	1520.6	1510.3	1503.4
130°	1602.1	1633.0	1628.7	1623.5	1614.1
132.5°	1712.8	1736.8	1738.5	1726.5	1719.7
135°	1808.0	1834.6	1839.8	1837.2	1830.4
137.5°	1914.4	1935.9	1940.2	1938.5	1928.2
140°	2008.0	2029.4	2041.4	2041.4	2032.0
142.5°	2104.1	2125.5	2132.4	2135.0	2125.5
145°	2195.1	2212.2	2225.9	2228.5	2219.1
147.5°	2276.6	2298.0	2308.3	2312.6	2303.2
150°	2360.7	2375.3	2384.7	2392.4	2384.7
152.5°	2435.3	2449.9	2461.9	2471.4	2461.9
155°	2510.0	2516.8	2524.6	2536.6	2528.9
157.5°	2574.3	2579.5	2583.8	2600.9	2588.9
160°	2631.8	2637.0	2639.6	2654.1	2643.8
162.5°	2685.0	2685.0	2687.6	2703.9	2691.9
165°	2730.5	2727.9	2727.9	2745.1	2733.1
167.5°	2771.7	2764.0	2764.0	2781.1	2769.1
170°	2802.6	2795.7	2793.2	2810.3	2795.7
172.5°	2824.0	2817.2	2814.6	2831.8	2817.2
175°	2841.2	2834.3	2829.2	2846.4	2831.8
177.5°	2850.6	2843.8	2838.6	2853.2	2838.6
180°	2846.4	2846.4	2846.4	2846.4	2846.4

TEST NUMBER: P905870

CATALOG NUMBER: DFN2DIP-PN3F0-090D090US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.12	12.95	13.09	13.93	15.21	8.09	8.91	9.06	9.89	11.18
	3H	13.79	14.53	14.78	15.52	16.83	9.27	10.01	10.25	11.00	12.31
	4H	14.40	15.09	15.39	16.09	17.41	9.72	10.41	10.71	11.41	12.72
	6H	14.81	15.45	15.82	16.45	17.78	10.03	10.67	11.04	11.67	13.00
	8H	14.94	15.55	15.95	16.56	17.89	10.12	10.73	11.13	11.74	13.07
	12H	15.00	15.58	16.01	16.58	17.93	10.16	10.74	11.18	11.75	13.10
4H	2H	12.14	12.83	13.14	13.83	15.15	8.68	9.38	9.68	10.37	11.69
	3H	13.96	14.54	14.97	15.56	16.89	10.02	10.60	11.03	11.62	12.95
	4H	14.65	15.18	15.67	16.19	17.55	10.57	11.09	11.58	12.11	13.46
	6H	15.16	15.61	16.19	16.65	18.00	10.98	11.43	12.01	12.47	13.82
	8H	15.33	15.75	16.36	16.78	18.15	11.10	11.53	12.13	12.56	13.92
	12H	15.42	15.80	16.47	16.85	18.22	11.16	11.55	12.21	12.59	13.96
8H	4H	14.61	15.04	15.64	16.07	17.43	10.84	11.26	11.87	12.30	13.66
	6H	15.17	15.52	16.23	16.60	17.96	11.35	11.70	12.41	12.77	14.14
	8H	15.38	15.69	16.45	16.75	18.13	11.54	11.84	12.60	12.90	14.29
	12H	15.52	15.79	16.58	16.84	18.27	11.65	11.92	12.72	12.97	14.40
12H	4H	14.56	14.95	15.61	15.99	17.36	10.84	11.23	11.89	12.27	13.64
	6H	15.15	15.45	16.21	16.51	17.90	11.40	11.71	12.46	12.77	14.15
	8H	15.36	15.63	16.43	16.69	18.11	11.60	11.87	12.67	12.93	14.35