

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908404

Luminaire Tested: DFN2DIP-PN3F0-030D030US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908404
REPORT IS A COMBINATION OF REPORTS P899511 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-030D030US840-FLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5680.5 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59
1	98	94	90	87	91	87	84	81	74	72	70		63	61	59		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	50		46
3	82	72	65	59	75	67	61	55	58	53	49		49	45	42		41
4	75	64	56	50	69	60	52	47	51	46	41		43	39	36		36
5	69	57	49	43	63	53	46	40	46	40	36		39	35	31		33
6	63	51	43	37	58	48	40	35	41	36	31		35	31	27		30
7	59	46	38	33	54	43	36	31	37	32	28		32	28	24		27
8	54	42	34	29	50	39	32	27	34	29	24		29	25	22		25
9	51	38	31	26	47	36	29	24	31	26	22		27	23	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1378	1378	1378
5°	1379	1358	1367
10°	1367	1339	1348
15°	1347	1316	1319
20°	1319	1284	1288
25°	1291	1246	1254
30°	1256	1211	1210
35°	1223	1170	1163
40°	1183	1129	1119
45°	1142	1087	1073
50°	1098	1043	1021
55°	1052	992	972
60°	999	932	917
65°	942	870	851
70°	869	794	780
75°	768	702	714
80°	646	585	589
85°	456	387	384

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1142 cd/sqm

TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	2.0
10°-20°	312.2	5.5
20°-30°	458.8	8.1
30°-40°	532.8	9.4
40°-50°	532.2	9.4
50°-60°	464.1	8.2
60°-70°	343.1	6.0
70°-80°	194.1	3.4
80°-90°	53.9	0.9
90°-100°	59.3	1.0
100°-110°	188.4	3.3
110°-120°	322.4	5.7
120°-130°	424.0	7.5
130°-140°	475.9	8.4
140°-150°	466.7	8.2
150°-160°	391.5	6.9
160°-170°	259.6	4.6
170°-180°	90.7	1.6
0°-30°	881.9	15.5
0°-40°	1414.7	24.9
0°-60°	2411.0	42.4
0°-90°	3002.1	52.8
90°-120°	570.1	10.0
90°-150°	1936.6	34.1
90°-180°	2678.0	47.1
0°-180°	5680.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	1	10	28	27	28	5
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P908404

CATALOG NUMBER: DFN2DIP-PN3F0-030D030US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.60	9.49	9.54	10.44	11.67	8.17	9.05	9.10	10.00	11.23
	3H	10.26	11.06	11.21	12.02	13.27	9.78	10.58	10.72	11.53	12.79
	4H	10.85	11.60	11.80	12.56	13.83	10.36	11.11	11.32	12.08	13.34
	6H	11.24	11.94	12.21	12.91	14.18	10.75	11.45	11.72	12.42	13.69
	8H	11.35	12.01	12.32	12.99	14.27	10.86	11.52	11.83	12.50	13.78
	12H	11.39	12.02	12.37	13.00	14.30	10.90	11.53	11.88	12.51	13.80
4H	2H	9.07	9.82	10.03	10.78	12.05	8.72	9.47	9.68	10.43	11.69
	3H	10.93	11.56	11.90	12.55	13.83	10.53	11.15	11.50	12.15	13.42
	4H	11.64	12.21	12.62	13.20	14.50	11.22	11.80	12.20	12.78	14.08
	6H	12.15	12.64	13.14	13.65	14.95	11.73	12.22	12.72	13.23	14.53
	8H	12.30	12.76	13.29	13.76	15.08	11.87	12.33	12.87	13.34	14.65
	12H	12.37	12.79	13.38	13.81	15.12	11.93	12.35	12.95	13.37	14.69
8H	4H	11.83	12.30	12.83	13.30	14.61	11.46	11.93	12.46	12.93	14.24
	6H	12.46	12.84	13.48	13.89	15.20	12.08	12.47	13.10	13.51	14.82
	8H	12.67	13.01	13.70	14.04	15.37	12.29	12.63	13.32	13.66	14.99
	12H	12.80	13.10	13.84	14.13	15.50	12.40	12.70	13.44	13.73	15.10
12H	4H	11.82	12.24	12.83	13.26	14.57	11.46	11.87	12.47	12.89	14.21
	6H	12.49	12.82	13.52	13.86	15.19	12.12	12.46	13.15	13.49	14.82
	8H	12.72	13.02	13.76	14.05	15.42	12.35	12.65	13.39	13.68	15.05