

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905582

Luminaire Tested: DFN2DIP-PN2F0-020D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905582
REPORT IS A COMBINATION OF REPORTS P899472 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D030US835-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4355.0 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 35.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1790	1790	1790
5°	1790	1758	1770
10°	1770	1720	1710
15°	1742	1659	1619
20°	1707	1577	1508
25°	1671	1486	1400
30°	1624	1393	1265
35°	1577	1294	1146
40°	1530	1191	1010
45°	1475	1077	887
50°	1418	963	767
55°	1358	842	652
60°	1289	715	534
65°	1209	587	478
70°	1112	468	429
75°	990	405	385
80°	814	329	325
85°	532	205	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1475 cd/sqm

TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	1.8
10°-20°	212.7	4.9
20°-30°	298.6	6.9
30°-40°	325.5	7.5
40°-50°	299.1	6.9
50°-60°	234.9	5.4
60°-70°	152.9	3.5
70°-80°	78.7	1.8
80°-90°	22.8	0.5
90°-100°	58.7	1.3
100°-110°	186.5	4.3
110°-120°	319.2	7.3
120°-130°	419.8	9.6
130°-140°	471.2	10.8
140°-150°	462.1	10.6
150°-160°	387.7	8.9
160°-170°	257.1	5.9
170°-180°	89.9	2.1
0°-30°	588.7	13.5
0°-40°	914.2	21.0
0°-60°	1448.3	33.3
0°-90°	1702.7	39.1
90°-120°	564.5	13.0
90°-150°	1917.7	44.0
90°-180°	2652.0	60.9
0°-180°	4355.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	827	823	813	820	818	78
15°	786	778	752	738	731	222
25°	714	690	640	610	598	328
35°	615	577	511	464	447	385
45°	503	452	374	321	303	388
55°	382	324	243	198	184	342
65°	258	198	130	105	102	256
75°	138	85	60	55	54	146
85°	32	16	14	14	14	37
90°	1	10	28	26	27	4
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	

TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	826.6	826.6	826.6	826.6	826.6
2.5°	830.3	826.6	818.3	825.9	824.4
5°	826.6	822.9	813.1	819.9	817.6
7.5°	819.9	815.4	804.9	807.9	804.1
10°	810.9	805.6	790.7	788.4	784.0
12.5°	799.7	792.9	772.7	768.3	760.0
15°	786.2	777.9	752.5	738.3	730.9
17.5°	770.5	758.5	727.1	710.6	698.7
20°	752.5	737.5	700.2	681.5	665.0
22.5°	733.1	715.9	672.5	647.1	635.9
25°	713.7	689.7	640.3	609.7	598.4
27.5°	690.5	665.0	610.4	575.2	558.0
30°	665.8	637.3	577.5	539.4	519.1
32.5°	641.8	607.4	546.1	501.2	482.5
35°	614.9	576.8	511.0	463.8	447.3
37.5°	588.7	547.5	478.0	426.4	407.7
40°	561.0	516.2	443.6	390.5	371.0
42.5°	532.6	484.8	409.2	353.8	335.2
45°	502.7	452.5	374.1	320.9	302.9
47.5°	474.3	421.2	340.4	287.2	270.8
50°	442.9	389.8	307.5	255.8	240.2
52.5°	412.1	356.0	276.0	226.7	212.5
55°	382.2	323.9	243.1	198.3	184.0
57.5°	351.6	291.7	214.0	172.1	160.1
60°	320.2	260.3	183.3	145.2	133.2
62.5°	289.5	229.7	157.1	121.2	115.2
65°	258.1	197.5	130.2	104.8	102.5
67.5°	228.2	167.5	104.8	92.0	89.8
70°	196.7	138.4	86.7	79.3	76.3
72.5°	166.8	111.4	72.5	66.6	65.1
75°	137.6	85.2	59.8	54.6	53.9
77.5°	108.5	60.6	47.1	44.1	42.6
80°	81.5	43.4	35.9	32.9	32.9
82.5°	56.8	29.2	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6

TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8

TEST NUMBER: P905582

CATALOG NUMBER: DFN2DIP-PN2F0-020D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.94	8.69	8.99	9.74	11.16	3.91	4.66	4.96	5.71	7.13
	3H	9.59	10.26	10.65	11.32	12.76	5.08	5.74	6.14	6.81	8.25
	4H	10.18	10.82	11.25	11.88	13.33	5.51	6.14	6.58	7.21	8.65
	6H	10.58	11.17	11.66	12.23	13.69	5.81	6.39	6.89	7.46	8.92
	8H	10.70	11.25	11.78	12.33	13.79	5.89	6.45	6.98	7.53	8.98
	12H	10.75	11.28	11.84	12.35	13.83	5.92	6.45	7.02	7.53	9.00
4H	2H	7.94	8.58	9.02	9.64	11.09	4.48	5.12	5.56	6.18	7.63
	3H	9.74	10.27	10.83	11.36	12.82	5.81	6.33	6.89	7.42	8.88
	4H	10.41	10.90	11.51	11.98	13.46	6.34	6.82	7.43	7.90	9.38
	6H	10.91	11.32	12.01	12.42	13.90	6.73	7.15	7.83	8.25	9.73
	8H	11.07	11.46	12.17	12.55	14.04	6.85	7.24	7.95	8.33	9.82
	12H	11.15	11.50	12.26	12.61	14.10	6.90	7.25	8.02	8.36	9.86
8H	4H	10.37	10.76	11.47	11.85	13.34	6.60	6.99	7.70	8.08	9.57
	6H	10.91	11.23	12.03	12.37	13.86	7.09	7.41	8.21	8.55	10.03
	8H	11.12	11.40	12.24	12.51	14.02	7.27	7.55	8.40	8.67	10.17
	12H	11.24	11.48	12.37	12.60	14.14	7.37	7.62	8.50	8.73	10.27
12H	4H	10.32	10.67	11.44	11.78	13.27	6.60	6.95	7.71	8.05	9.55
	6H	10.89	11.17	12.01	12.29	13.79	7.13	7.41	8.26	8.53	10.04
	8H	11.09	11.33	12.22	12.45	13.99	7.33	7.57	8.46	8.69	10.23