

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P905618

Luminaire Tested: DFN2DIP-PN2F0-040D020US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P905618
REPORT IS A COMBINATION OF REPORTS P899466 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D020US835-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5170.0 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 55.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3581	3581	3581
5°	3581	3516	3541
10°	3539	3439	3421
15°	3485	3318	3238
20°	3415	3155	3015
25°	3343	2972	2800
30°	3248	2786	2530
35°	3155	2587	2292
40°	3060	2382	2020
45°	2950	2155	1774
50°	2836	1926	1534
55°	2717	1683	1304
60°	2578	1430	1069
65°	2419	1174	956
70°	2224	936	857
75°	1980	810	770
80°	1629	658	652
85°	1065	409	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2950 cd/sqm

TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	3.0
10°-20°	425.3	8.2
20°-30°	597.2	11.6
30°-40°	650.9	12.6
40°-50°	598.3	11.6
50°-60°	469.9	9.1
60°-70°	305.8	5.9
70°-80°	157.4	3.0
80°-90°	42.0	0.8
90°-100°	39.1	0.8
100°-110°	124.4	2.4
110°-120°	212.8	4.1
120°-130°	279.9	5.4
130°-140°	314.2	6.1
140°-150°	308.1	6.0
150°-160°	258.4	5.0
160°-170°	171.4	3.3
170°-180°	59.9	1.2
0°-30°	1177.4	22.8
0°-40°	1828.4	35.4
0°-60°	2896.5	56.0
0°-90°	3401.8	65.8
90°-120°	376.3	7.3
90°-150°	1278.5	24.7
90°-180°	1768.0	34.2
0°-180°	5170.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	1	7	19	18	18	5
95°	28	33	34	34	33	31
105°	115	116	118	118	118	121
115°	214	217	216	215	214	211
125°	311	315	314	312	312	278
135°	402	408	409	408	407	311
145°	488	492	495	495	493	305
155°	558	559	561	564	562	257
165°	607	606	606	610	607	171
175°	631	630	629	632	629	60
180°	632	632	632	632	632	

TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.6	6.9	18.7	17.5	18.1
92.5°	11.8	16.0	16.6	17.2	17.2
95°	27.8	33.2	34.1	34.1	33.2
97.5°	46.3	51.3	53.4	53.4	53.4
100°	67.7	72.1	73.6	73.6	73.0
102.5°	90.2	93.4	95.5	96.1	95.5
105°	114.8	116.3	117.5	118.4	118.4
107.5°	139.2	141.5	141.5	141.9	139.2
110°	162.9	165.9	165.9	165.9	164.4

TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	188.4	191.6	191.1	189.5	188.4
115°	213.6	216.6	215.7	215.1	213.6
117.5°	238.6	242.8	240.1	238.6	237.0
120°	263.7	267.9	263.7	263.7	262.0
122.5°	286.6	291.9	289.3	287.8	286.6
125°	310.6	315.4	313.9	312.2	311.6
127.5°	334.1	340.0	337.9	335.6	334.1
130°	356.0	362.9	361.9	360.8	358.7
132.5°	380.6	386.0	386.3	383.7	382.1
135°	401.8	407.7	408.8	408.3	406.7
137.5°	425.4	430.2	431.2	430.8	428.5
140°	446.2	451.0	453.7	453.7	451.6
142.5°	467.6	472.3	473.9	474.4	472.3
145°	487.8	491.6	494.7	495.2	493.1
147.5°	505.9	510.7	513.0	513.9	511.8
150°	524.6	527.8	529.9	531.6	529.9
152.5°	541.2	544.4	547.1	549.2	547.1
155°	557.8	559.3	561.0	563.7	562.0
157.5°	572.1	573.2	574.2	578.0	575.3
160°	584.9	586.0	586.6	589.8	587.5
162.5°	596.7	596.7	597.2	600.9	598.2
165°	606.8	606.2	606.2	610.0	607.4
167.5°	615.9	614.2	614.2	618.0	615.4
170°	622.8	621.3	620.7	624.5	621.3
172.5°	627.6	626.0	625.5	629.3	626.0
175°	631.4	629.9	628.7	632.5	629.3
177.5°	633.5	632.0	630.8	634.0	630.8
180°	632.5	632.5	632.5	632.5	632.5

TEST NUMBER: P905618

CATALOG NUMBER: DFN2DIP-PN2F0-040D020US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.82	13.80	13.64	14.63	15.66	8.79	9.77	9.61	10.60	11.63
	3H	14.49	15.37	15.32	16.21	17.27	9.97	10.85	10.80	11.69	12.75
	4H	15.09	15.92	15.94	16.77	17.84	10.42	11.24	11.26	12.09	13.16
	6H	15.50	16.26	16.36	17.12	18.20	10.73	11.49	11.59	12.35	13.43
	8H	15.63	16.35	16.49	17.23	18.31	10.82	11.54	11.69	12.42	13.50
	12H	15.68	16.37	16.56	17.24	18.35	10.86	11.55	11.73	12.42	13.52
4H	2H	12.85	13.68	13.70	14.53	15.60	9.39	10.22	10.24	11.07	12.14
	3H	14.67	15.36	15.53	16.24	17.33	10.74	11.42	11.60	12.30	13.39
	4H	15.36	15.98	16.23	16.86	17.97	11.28	11.90	12.15	12.78	13.89
	6H	15.86	16.40	16.75	17.30	18.41	11.68	12.22	12.57	13.13	14.24
	8H	16.03	16.53	16.92	17.43	18.55	11.81	12.31	12.70	13.21	14.33
	12H	16.12	16.57	17.03	17.49	18.62	11.87	12.32	12.78	13.24	14.37
8H	4H	15.33	15.83	16.22	16.73	17.86	11.55	12.06	12.45	12.95	14.08
	6H	15.88	16.29	16.80	17.23	18.36	12.06	12.47	12.97	13.41	14.54
	8H	16.08	16.45	17.01	17.38	18.53	12.23	12.60	13.16	13.53	14.68
	12H	16.21	16.54	17.14	17.46	18.66	12.34	12.67	13.28	13.59	14.79
12H	4H	15.29	15.74	16.20	16.66	17.79	11.56	12.01	12.47	12.93	14.06
	6H	15.85	16.22	16.78	17.15	18.30	12.10	12.47	13.03	13.40	14.54
	8H	16.07	16.39	17.00	17.31	18.51	12.30	12.62	13.23	13.55	14.74