

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908323

Luminaire Tested: DFN2DIP-PN2F0-020D060US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908323
REPORT IS A COMBINATION OF REPORTS P901022 AND P897905
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-020D060US840-RLLONL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7715.4 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 69
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26
2	84	77	71	66	74	68	64	60	52	49	47	38	36	34	24	23	22
3	76	68	61	55	68	60	55	50	46	43	39	34	31	29	22	20	19
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17
5	64	53	46	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	35	52	43	36	31	33	29	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	10
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	12	11	9
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1808	1775	1788
10°	1787	1737	1727
15°	1760	1675	1635
20°	1724	1593	1522
25°	1688	1501	1414
30°	1640	1407	1277
35°	1593	1306	1157
40°	1545	1203	1020
45°	1490	1088	896
50°	1432	973	775
55°	1372	850	658
60°	1302	722	540
65°	1221	593	483
70°	1123	472	433
75°	1000	409	389
80°	822	333	328
85°	537	206	233

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1879 cd/sqm

TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	1.0
10°-20°	214.8	2.8
20°-30°	301.5	3.9
30°-40°	328.7	4.3
40°-50°	302.1	3.9
50°-60°	237.3	3.1
60°-70°	154.4	2.0
70°-80°	79.5	1.0
80°-90°	23.9	0.3
90°-100°	67.4	0.9
100°-110°	251.4	3.3
110°-120°	666.7	8.6
120°-130°	1105.7	14.3
130°-140°	1174.5	15.2
140°-150°	1091.6	14.1
150°-160°	877.6	11.4
160°-170°	565.5	7.3
170°-180°	194.6	2.5
0°-30°	594.5	7.7
0°-40°	923.2	12.0
0°-60°	1462.6	19.0
0°-90°	1720.4	22.3
90°-120°	985.5	12.8
90°-150°	4357.2	56.5
90°-180°	5995.0	77.7
0°-180°	7715.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	835	835	835	835	835	
5°	835	831	821	828	826	79
15°	794	786	760	746	738	224
25°	721	696	647	616	604	331
35°	621	582	516	468	452	389
45°	508	457	378	324	306	392
55°	386	327	246	200	186	345
65°	261	199	132	106	104	258
75°	139	86	60	55	54	147
85°	32	17	14	14	14	37
90°	1	18	30	37	40	7
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	834.8	834.8	834.8	834.8	834.8
2.5°	838.5	834.8	826.4	834.0	832.5
5°	834.8	831.0	821.1	828.0	825.7
7.5°	828.0	823.4	812.8	815.9	812.0
10°	818.9	813.5	798.5	796.2	791.7
12.5°	807.6	800.7	780.3	775.9	767.5
15°	794.0	785.6	759.9	745.6	738.1
17.5°	778.1	766.0	734.3	717.6	705.6
20°	759.9	744.8	707.1	688.2	671.6
22.5°	740.3	723.0	679.1	653.5	642.2
25°	720.7	696.5	646.6	615.7	604.3
27.5°	697.3	671.6	616.4	580.9	563.5
30°	672.4	643.6	583.2	544.7	524.2
32.5°	648.1	613.4	551.5	506.1	487.3
35°	621.0	582.5	516.0	468.4	451.7
37.5°	594.5	552.9	482.7	430.6	411.7
40°	566.5	521.3	448.0	394.4	374.7
42.5°	537.9	489.6	413.2	357.3	338.5
45°	507.7	457.0	377.8	324.1	305.9
47.5°	479.0	425.4	343.8	290.0	273.5
50°	447.3	393.6	310.5	258.3	242.6
52.5°	416.2	359.5	278.7	228.9	214.6
55°	386.0	327.1	245.5	200.3	185.8
57.5°	355.1	294.6	216.1	173.8	161.7
60°	323.4	262.9	185.1	146.6	134.5
62.5°	292.4	232.0	158.6	122.4	116.3
65°	260.6	199.4	131.5	105.8	103.5
67.5°	230.5	169.2	105.8	92.9	90.7
70°	198.6	139.8	87.6	80.1	77.1
72.5°	168.4	112.5	73.2	67.3	65.7
75°	139.0	86.0	60.4	55.1	54.4
77.5°	109.6	61.2	47.6	44.5	43.0
80°	82.3	43.8	36.3	33.2	33.2
82.5°	57.4	29.5	24.9	23.4	23.4
85°	32.4	16.6	14.3	14.3	14.3
87.5°	12.1	6.1	6.1	5.3	5.3
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9

TEST NUMBER: P908323

CATALOG NUMBER: DFN2DIP-PN2F0-020D060US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.66	6.31	6.83	7.46	9.08	1.63	2.28	2.80	3.43	5.05
	3H	7.31	7.88	8.48	9.04	10.68	2.79	3.37	3.96	4.53	6.16
	4H	7.89	8.44	9.07	9.60	11.24	3.22	3.77	4.40	4.93	6.56
	6H	8.29	8.79	9.48	9.95	11.60	3.51	4.02	4.70	5.18	6.83
	8H	8.40	8.88	9.59	10.05	11.69	3.59	4.07	4.78	5.25	6.89
	12H	8.45	8.90	9.64	10.07	11.73	3.62	4.08	4.82	5.24	6.91
4H	2H	5.65	6.20	6.84	7.36	9.00	2.19	2.74	3.38	3.90	5.54
	3H	7.44	7.90	8.64	9.08	10.73	3.51	3.96	4.70	5.15	6.80
	4H	8.11	8.53	9.31	9.70	11.37	4.03	4.45	5.23	5.62	7.29
	6H	8.60	8.96	9.80	10.15	11.81	4.42	4.78	5.62	5.97	7.63
	8H	8.76	9.09	9.95	10.28	11.95	4.54	4.87	5.73	6.06	7.73
	12H	8.83	9.14	10.04	10.33	12.01	4.58	4.89	5.80	6.08	7.76
8H	4H	8.06	8.40	9.26	9.58	11.26	4.29	4.62	5.48	5.81	7.48
	6H	8.60	8.87	9.81	10.10	11.77	4.77	5.05	5.99	6.28	7.95
	8H	8.80	9.04	10.02	10.24	11.94	4.95	5.19	6.17	6.39	8.09
	12H	8.92	9.13	10.14	10.33	12.05	5.05	5.26	6.27	6.46	8.18
12H	4H	8.00	8.31	9.22	9.50	11.18	4.28	4.58	5.49	5.78	7.46
	6H	8.57	8.81	9.79	10.01	11.71	4.82	5.06	6.04	6.26	7.95
	8H	8.77	8.98	9.99	10.18	11.90	5.00	5.21	6.23	6.42	8.14

END OF REPORT