

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908561

Luminaire Tested: DFN2DIP-PN3F0-080D070US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908561
REPORT IS A COMBINATION OF REPORTS P901097 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-080D070US840-FLLONL
Description: 3 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14996.6 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3675	3675	3675
5°	3678	3621	3646
10°	3647	3570	3596
15°	3591	3508	3517
20°	3516	3424	3436
25°	3442	3324	3343
30°	3349	3230	3226
35°	3261	3121	3101
40°	3153	3009	2983
45°	3046	2898	2862
50°	2928	2781	2721
55°	2804	2646	2592
60°	2664	2485	2444
65°	2511	2318	2269
70°	2316	2115	2080
75°	2048	1872	1904
80°	1722	1561	1570
85°	1214	1033	1024

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3046 cd/sqm

TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.9	2.0
10°-20°	832.5	5.6
20°-30°	1223.4	8.2
30°-40°	1420.9	9.5
40°-50°	1419.1	9.5
50°-60°	1237.5	8.3
60°-70°	914.7	6.1
70°-80°	517.6	3.5
80°-90°	140.8	0.9
90°-100°	78.7	0.5
100°-110°	293.3	2.0
110°-120°	777.8	5.2
120°-130°	1290.0	8.6
130°-140°	1370.3	9.1
140°-150°	1273.5	8.5
150°-160°	1023.9	6.8
160°-170°	659.7	4.4
170°-180°	227.1	1.5
0°-30°	2351.8	15.7
0°-40°	3772.7	25.2
0°-60°	6429.3	42.9
0°-90°	8002.4	53.4
90°-120°	1149.7	7.7
90°-150°	5083.5	33.9
90°-180°	6994.0	46.6
0°-180°	14996.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3144	3144	3144	3144	3144	
5°	3144	3132	3098	3122	3117	298
15°	2992	2975	2935	2947	2932	843
25°	2708	2684	2633	2639	2633	1246
35°	2337	2306	2258	2240	2225	1459
45°	1902	1880	1835	1802	1790	1467
55°	1439	1421	1384	1348	1333	1287
65°	970	952	922	895	880	959
75°	508	502	487	469	475	542
85°	124	121	118	109	106	138
90°	2	21	34	43	47	14
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3143.5	3143.5	3143.5	3143.5	3143.5
2.5°	3161.8	3146.7	3113.4	3143.5	3137.8
5°	3143.5	3131.7	3098.4	3122.4	3116.6
7.5°	3122.4	3104.4	3071.1	3095.4	3089.4
10°	3089.4	3068.2	3031.9	3056.0	3047.1
12.5°	3043.8	3025.9	2989.6	3004.7	2998.6
15°	2992.5	2974.6	2935.1	2947.3	2932.2
17.5°	2929.0	2911.0	2871.6	2886.7	2871.6
20°	2859.4	2841.5	2799.1	2808.1	2796.2
22.5°	2790.2	2762.9	2723.4	2723.4	2717.3
25°	2708.4	2684.3	2633.0	2638.8	2633.0
27.5°	2617.6	2596.5	2557.3	2548.3	2533.2
30°	2527.2	2502.7	2457.6	2448.6	2436.4
32.5°	2430.3	2412.4	2363.9	2345.6	2333.5
35°	2336.6	2306.5	2258.1	2239.8	2224.7
37.5°	2230.8	2203.5	2155.2	2133.9	2118.9
40°	2122.1	2097.7	2049.3	2022.4	2010.1
42.5°	2016.3	1991.9	1943.8	1913.3	1895.4
45°	1901.5	1880.3	1834.7	1801.7	1789.6
47.5°	1789.6	1768.4	1719.9	1686.6	1668.6
50°	1671.5	1656.5	1614.1	1571.8	1556.7
52.5°	1556.7	1535.5	1496.4	1463.1	1441.9
55°	1439.0	1420.7	1384.5	1348.3	1333.1
57.5°	1321.0	1306.0	1266.5	1230.2	1218.0
60°	1203.0	1191.1	1148.7	1115.4	1106.4
62.5°	1088.1	1067.0	1036.8	1006.7	994.5
65°	970.5	952.2	922.0	894.7	879.7
67.5°	849.5	834.1	807.2	786.1	773.9
70°	737.6	725.4	698.2	677.0	665.1
72.5°	622.8	610.7	595.5	574.4	565.4
75°	507.7	501.9	486.6	468.6	474.6
77.5°	405.1	392.8	386.8	377.8	368.8
80°	302.5	299.2	293.2	284.2	278.0
82.5°	205.6	205.6	202.7	190.5	190.5
85°	123.8	120.9	118.1	108.8	105.8
87.5°	54.5	48.5	42.3	33.3	30.2
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P908561

CATALOG NUMBER: DFN2DIP-PN3F0-080D070US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.06	12.95	12.99	13.90	15.12	11.62	12.51	12.55	13.46	14.68
	3H	13.72	14.52	14.66	15.47	16.72	13.23	14.03	14.17	14.99	16.24
	4H	14.30	15.06	15.26	16.02	17.27	13.82	14.57	14.77	15.53	16.79
	6H	14.70	15.40	15.66	16.36	17.63	14.21	14.91	15.17	15.87	17.14
	8H	14.80	15.47	15.77	16.45	17.71	14.31	14.98	15.28	15.96	17.22
	12H	14.85	15.48	15.83	16.46	17.75	14.35	14.98	15.33	15.96	17.25
4H	2H	12.52	13.28	13.48	14.24	15.49	12.17	12.93	13.13	13.89	15.14
	3H	14.38	15.02	15.35	16.00	17.27	13.98	14.61	14.95	15.60	16.87
	4H	15.09	15.67	16.07	16.65	17.95	14.68	15.26	15.66	16.24	17.53
	6H	15.61	16.10	16.60	17.11	18.40	15.18	15.68	16.17	16.69	17.98
	8H	15.75	16.22	16.75	17.22	18.52	15.33	15.79	16.32	16.79	18.10
	12H	15.82	16.24	16.84	17.26	18.57	15.39	15.81	16.40	16.82	18.13
8H	4H	15.29	15.75	16.28	16.75	18.06	14.92	15.38	15.91	16.38	17.69
	6H	15.91	16.30	16.93	17.34	18.64	15.54	15.92	16.56	16.97	18.27
	8H	16.13	16.47	17.16	17.50	18.82	15.75	16.09	16.77	17.12	18.44
	12H	16.26	16.56	17.29	17.58	18.95	15.86	16.16	16.89	17.18	18.55
12H	4H	15.28	15.70	16.29	16.71	18.02	14.91	15.33	15.92	16.35	17.66
	6H	15.94	16.28	16.97	17.31	18.63	15.58	15.92	16.60	16.95	18.27
	8H	16.18	16.48	17.21	17.50	18.87	15.81	16.11	16.84	17.13	18.50