

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908330

Luminaire Tested: DFN2DIP-PN2F0-030D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908330
REPORT IS A COMBINATION OF REPORTS P899474 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-030D030US840-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5256.3 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2712	2712	2712
5°	2712	2663	2682
10°	2681	2605	2591
15°	2639	2513	2452
20°	2586	2389	2283
25°	2532	2251	2121
30°	2460	2110	1916
35°	2390	1959	1736
40°	2318	1804	1530
45°	2235	1632	1344
50°	2149	1459	1162
55°	2058	1275	988
60°	1953	1083	810
65°	1831	889	724
70°	1685	709	649
75°	1499	614	583
80°	1234	498	494
85°	807	310	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2235 cd/sqm

TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.2
10°-20°	322.1	6.1
20°-30°	452.3	8.6
30°-40°	493.0	9.4
40°-50°	453.1	8.6
50°-60°	355.9	6.8
60°-70°	231.6	4.4
70°-80°	119.2	2.3
80°-90°	33.2	0.6
90°-100°	59.3	1.1
100°-110°	188.4	3.6
110°-120°	322.4	6.1
120°-130°	424.0	8.1
130°-140°	475.9	9.1
140°-150°	466.7	8.9
150°-160°	391.5	7.4
160°-170°	259.6	4.9
170°-180°	90.7	1.7
0°-30°	891.8	17.0
0°-40°	1384.8	26.3
0°-60°	2193.8	41.7
0°-90°	2577.8	49.0
90°-120°	570.1	10.8
90°-150°	1936.6	36.8
90°-180°	2678.0	50.9
0°-180°	5256.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	1	10	28	27	28	5
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0

TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P908330

CATALOG NUMBER: DFN2DIP-PN2F0-030D030US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.40	11.23	11.38	12.21	13.50	6.37	7.19	7.34	8.18	9.46
	3H	12.06	12.80	13.04	13.79	15.10	7.54	8.28	8.53	9.27	10.58
	4H	12.66	13.35	13.65	14.34	15.66	7.98	8.68	8.98	9.67	10.99
	6H	13.06	13.70	14.07	14.70	16.03	8.29	8.93	9.29	9.93	11.26
	8H	13.18	13.79	14.19	14.80	16.13	8.37	8.98	9.38	9.99	11.32
	12H	13.23	13.81	14.25	14.82	16.17	8.40	8.98	9.42	9.99	11.34
4H	2H	10.42	11.11	11.42	12.11	13.42	6.95	7.65	7.96	8.64	9.96
	3H	12.22	12.80	13.23	13.82	15.15	8.28	8.86	9.30	9.89	11.22
	4H	12.90	13.43	13.92	14.44	15.80	8.82	9.35	9.84	10.36	11.72
	6H	13.39	13.85	14.42	14.89	16.24	9.22	9.67	10.25	10.71	12.06
	8H	13.56	13.98	14.59	15.01	16.38	9.34	9.76	10.37	10.79	12.16
	12H	13.64	14.02	14.69	15.07	16.44	9.39	9.77	10.44	10.82	12.19
8H	4H	12.86	13.29	13.89	14.32	15.68	9.09	9.51	10.12	10.54	11.91
	6H	13.40	13.75	14.46	14.83	16.19	9.58	9.93	10.63	11.00	12.37
	8H	13.61	13.91	14.67	14.97	16.36	9.76	10.07	10.82	11.12	12.51
	12H	13.73	14.00	14.80	15.05	16.48	9.86	10.13	10.93	11.19	12.61
12H	4H	12.81	13.19	13.86	14.24	15.61	9.09	9.47	10.14	10.52	11.89
	6H	13.38	13.69	14.44	14.74	16.13	9.62	9.93	10.69	10.99	12.37
	8H	13.58	13.85	14.65	14.91	16.33	9.82	10.09	10.88	11.14	12.57

END OF REPORT