

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908350

Luminaire Tested: DFN2DIP-PN2F0-040D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908350
REPORT IS A COMBINATION OF REPORTS P899476 AND P896349
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN2F0-040D030US840-RLLFLL
Description: 2 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6114.7 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.17' x L: 2.29' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 58.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3616	3616	3616
5°	3616	3551	3576
10°	3574	3473	3455
15°	3519	3351	3270
20°	3448	3186	3045
25°	3376	3002	2828
30°	3280	2814	2554
35°	3186	2613	2314
40°	3090	2405	2040
45°	2980	2176	1792
50°	2864	1945	1549
55°	2744	1700	1317
60°	2604	1444	1079
65°	2442	1186	965
70°	2247	945	866
75°	1999	818	778
80°	1645	664	659
85°	1075	413	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2980 cd/sqm

TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	2.6
10°-20°	429.5	7.0
20°-30°	603.0	9.9
30°-40°	657.4	10.8
40°-50°	604.2	9.9
50°-60°	474.5	7.8
60°-70°	308.9	5.1
70°-80°	159.0	2.6
80°-90°	43.3	0.7
90°-100°	59.3	1.0
100°-110°	188.4	3.1
110°-120°	322.4	5.3
120°-130°	424.0	6.9
130°-140°	475.9	7.8
140°-150°	466.7	7.6
150°-160°	391.5	6.4
160°-170°	259.6	4.2
170°-180°	90.7	1.5
0°-30°	1189.0	19.4
0°-40°	1846.4	30.2
0°-60°	2925.1	47.8
0°-90°	3436.3	56.2
90°-120°	570.1	9.3
90°-150°	1936.6	31.7
90°-180°	2678.0	43.8
0°-180°	6114.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	1	10	28	27	28	6
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0

TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P908350

CATALOG NUMBER: DFN2DIP-PN2F0-040D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.06	12.94	12.96	13.86	15.04	8.02	8.91	8.93	9.83	11.01
	3H	13.72	14.51	14.64	15.44	16.65	9.20	9.99	10.12	10.92	12.13
	4H	14.31	15.06	15.25	16.00	17.21	9.64	10.39	10.58	11.32	12.54
	6H	14.72	15.41	15.67	16.35	17.58	9.95	10.64	10.90	11.58	12.81
	8H	14.84	15.49	15.79	16.45	17.68	10.03	10.69	10.99	11.65	12.87
	12H	14.90	15.52	15.85	16.47	17.72	10.07	10.69	11.03	11.65	12.90
4H	2H	12.08	12.82	13.02	13.76	14.98	8.61	9.36	9.56	10.30	11.51
	3H	13.89	14.51	14.84	15.47	16.71	9.95	10.57	10.90	11.54	12.77
	4H	14.56	15.13	15.53	16.09	17.35	10.49	11.05	11.45	12.01	13.27
	6H	15.06	15.55	16.04	16.54	17.79	10.89	11.38	11.86	12.36	13.62
	8H	15.23	15.68	16.20	16.66	17.93	11.01	11.46	11.98	12.44	13.71
	12H	15.31	15.72	16.31	16.72	17.99	11.07	11.48	12.06	12.47	13.75
8H	4H	14.53	14.99	15.51	15.97	17.23	10.76	11.21	11.73	12.19	13.46
	6H	15.08	15.45	16.08	16.47	17.74	11.25	11.63	12.25	12.65	13.92
	8H	15.28	15.61	16.29	16.62	17.91	11.43	11.76	12.44	12.77	14.06
	12H	15.41	15.70	16.42	16.70	18.03	11.54	11.83	12.55	12.83	14.17
12H	4H	14.49	14.89	15.48	15.89	17.17	10.76	11.17	11.75	12.17	13.44
	6H	15.05	15.38	16.06	16.39	17.68	11.30	11.63	12.31	12.64	13.92
	8H	15.26	15.55	16.27	16.55	17.89	11.50	11.79	12.51	12.79	14.12

END OF REPORT